




Item	Part No.	Description
1	AK467DXP.01	FILTER SCREEN
2	AK467DXP.02	RESERVOIR
3	AK467DXP.03	SCREEN HANDLE
4	AK467DXP.04	HANDLE
5	AK467DXP.05	HANDLE GRIP
6	AK467DXP.06	PUMP HOSE (LONG)
7	AK467DXP.07	HOSE CLAMP (AK467DXP only)
8	AK467DXP.08	HOSE FITTING (AK467DXP only)
9	AK467DXP.09	PUMP (AK467DXP only)
10	AK467DXP.10	PUMP HOSE (SHORT) (AK467DXP only)
11	AK467DXP.11	HOSE FITTING (AK467DXP only)
12	AK467DXP.12	BUSHING (AK467DXP only)
13	AK467DXP.13	CONNECTING PLATE (AK467DXP only)
14	SCB640.SB	SOCKET HEAD CAP SCREW M6x40 BLACK (AK467DXP only)
15	SS816.S	HEX HEAD SET SCREW M8x16mm SINGLE
16	TP112.V2-C	WHEEL,CASTOR (75x9x25x100)

Item	Part No.	Description
17	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)
18	FWM12.S	FLAT WASHER M12 SINGLE
19	AK467DXP.19	BOLT M8X45
20	NLN8.S	NYLOC NUT M8 ZINC DIN 985 (SINGLE)
21	HHB12110.S	HEX HEAD BOLT M12x110mm SINGLE
22	FWM12.S	FLAT WASHER M12 SINGLE
23	AK467DXP.23	PLASTIC NEEDLE BEARING
24	AK467DXP.24	RETAINING RING
25	AK467DXP.25	WHEEL, FIXED (123x19x34)
26	NLN12.S	NYLOC NUT M12 ZINC DIN 985 (SINGLE)
27	SWM6.SB	SPRING WASHER M6 BLACK(SINGLE) (AK467DXP only)
28	SWM8.SB	SPRING WASHER M8 BLACK(SINGLE) (AK467DXP only)
--	AK467D.29	OUTLET VALVE (AK467D only 'not shown')
--	AK467D.30	RESERVOIR (AK467D only 'not shown')

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk