



Super Glu Liquid

CYANOACRYLATE ADHESIVE IN A TUBE

Date: 29 October 2015

Fact Sheet No.: TDS00484

YOUR SMART ADVANTAGES

- High strength
- Bonds in seconds
- For home and office use

USES

Bostik Super Glu Liquid is a single part, fast curing adhesive which bonds in seconds without the need for heat or hardener. It is extremely economical in use and provides very strong bonds of high tensile strength.

Bostik Super Glu Liquid is suitable for bonding porcelain, many rubbers, most common metals, some types of jewellery and most plastics.

PRODUCT CHARACTERISTICS

Colour	Clear
Form	Thin liquid
Specific Gravity	1.1 approx.
Composition	Cyanoacrylate
Product Code	30813340 3g tube 1 x 12 Blister
Solids Content	100%
Storage/Shelf Life	Store for up to 12 months from date of manufacture when stored in the original, unopened packaging under dry conditions within the temperature range of +5°C to +25°C and away from direct sunlight. Protect from frost.
Odour	Pungent

TYPICAL PERFORMANCE DATA (Approx.)

Application Temperature	+10°C to +35°C
Temperature Resistance	-20°C to +80°C. Will withstand temperatures up to +100°C for short periods.
Water Resistance	Good. After a few weeks the shear strength decreases gradually.
Petrol Resistance	Good

DIRECTIONS FOR USE

IMPORTANT: Before using Bostik Super Glu Liquid refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.

PREPARATION

1. Work on a protected surface as any spillages are very difficult to remove, particularly from sensitive surfaces like fabrics and skin.
2. Make sure all surfaces to be bonded are close fitting, clean and dry.
3. Ensure that the tube is held upright and pointing away from you.

APPLICATION

4. Unscrew the nozzle and cap and remove the safety collar. Replace the nozzle and cap and screw down to puncture the seal. Remove the cap and leave the nozzle in place.
5. Very carefully apply a small amount of Bostik Super Glu Liquid to one surface only (typically apply one drop of adhesive for each 6cm² of substrate to be bonded).
6. Bring the surfaces together and hold firmly for approximately 30 seconds. (Full strength is achieved in approximately 12 hours).



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk

Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

7. Replace the cap firmly after use, taking care not to leave Bostik Super Glu Liquid between the cap and the nozzle. Store upright. The tube is purposely only part full as the air above the adhesive stabilizes it. This air space in the tube reduces the chance of accidental spillages.

CLEANING

8. Bostik Super Glu Liquid has good resistance to most oils and solvents and can be very difficult to remove.
9. Bostik Super Glu Liquid bonds to skin very quickly and easily. Should this happen, please do not panic. Do not attempt to pull apart as this may damage the skin. If left the bond will loosen within 60 minutes without doing anything. Hot soapy water and gentle peeling will part the bond, this can take 10 minutes.
10. Acetone will very slowly soften set super glue. Before attempting to use, check that it is safe to use a highly flammable solvent and that the surfaces to which the super glue is adhered are not damaged by the solvent. Do not use acetone or solvents on the skin.
11. Always test before using any solvent.

PRECAUTIONS IN USE

Do not use Bostik Super Glu Liquid on polyethylene, polypropylene. Unsuitable for use on absorbent surfaces such as fabric, card and paper. Do not use acetone or solvents on the skin. Do not use for repairing containers that hold hot liquid food or drinks. Unsuitable for bonding windscreen rear-view mirrors. Unsuitable for bonding large areas.

For any application not covered please contact Technical Services on +44 (0)1785 272625, or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for Bostik Super Glu Liquid, available at www.bostik.co.uk.

BOSTIK HOTLINE

Smart help +44 (0) 1785 272625



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk

Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Sales	Tel: 0844 371 1192	Fax: 01785 241818	customer.service@bostik.com
Technical Advice	Tel: 0844 371 1197	Fax: 01785 272867	technical.service@bostik.com
Technical Data & COSHH (MSDS) Data Sheets	Tel: 01785 272625	Fax: 01785 212962	stafford.gatehouse@bostik.com



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk
Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.