



INSTRUCTIONS FOR 3 DRAWER UNIT FOR AP10 AND AP30 SERIES WORKBENCHES

MODEL NO: **AP3**

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to instructions

1. SAFETY

- WARNING!** Ensure Health & Safety, local authority, and general workshop practice regulations are adhered to when using this drawer unit.
- ✓ Locate bench with drawer unit in a suitable working area.
- ✓ Keep the work area clean, uncluttered and ensure there is adequate lighting.
- WARNING!** Use bench with drawer unit on level and solid ground, preferably concrete.
- ✓ Keep bench and drawer unit clean and tidy in accordance with good workshop practice.
- ✓ Keep children and unauthorised persons away from the working area.
- WARNING!** Neither the drawer unit or bench to which it is fitted are electrically insulated and neither is therefore suitable for electrical repairs of any sort.
- ✓ **DO NOT** use bench or drawer unit for any purpose other than that for which it is designed.
- ✓ **DO NOT** use a bench with drawer unit fitted outside.
- ✓ **DO NOT** get bench or drawer unit wet, or use in damp or wet locations or areas where there is condensation.
- ✓ **DO NOT** clean bench or drawer unit with any solvents which may damage the paint surface.
- WARNING!** Workbenches with drawer units are heavy and assistance should be obtained before moving them.

2. INTRODUCTION


Optional unit for added drawer space on any of the AP120 and AP30 series workbenches. Manufactured in steel plate for industrial durability and finished in red gloss to prevent corrosion. Lockable drawers, which can be installed on the left or the right of the workbench.

3. SPECIFICATION

Model no: AP3
Overall size (W x D x H): 400 x 575 x 535mm
Drawer size (W x D x H): 340 x 525 x 120mm

4. ASSEMBLY

- 4.1. On the wider benches with alternative runner positions, decide whether the drawer unit is to be placed on the left or on the right.
- 4.2. Lift the drawer unit and slide the outward turned flanges at the top of the unit sides onto the inwards turned flanges of the runners beneath the bench top, see Fig.1A.
- 4.3. Push the unit fully in until it stops. Screw the drawer unit retaining plate into position on the back of the drawer unit using the holes and self tapping screws provided.
- 4.4. Ensure that the flange at the top of the retaining plate faces inwards and bears against the ends of the runners, see Fig.1B.





Environmental Protection

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain off any fluids (if applicable) into approved containers and dispose of the product and the fluids according to local regulations.

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of this product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.



Sole UK Distributor, Sealey Group.
Kempson Way, Suffolk Business Park,
Bury St. Edmunds, Suffolk.
IP32 7AR



01284 757500



01284 703534



www.sealey.co.uk



sales@sealey.co.uk