

PrimeTest 50

Basic Pass/Fail handled unit for testing earth continuity and insulation resistance of appliances.

The PrimeTest 50 is lightweight and portable and features a greatly simplified range of tests. Simply choose the test you need – either earthed appliance, double-insulated appliance or mains cord testing. Its easy-to-read display is simple and registers PASS or FAIL. Connect the PrimeTest 50 to a power outlet and it will automatically check the socket wiring and mains voltage. It doesn't get much simpler.

Unlock extra features with our free and easy-to-use mobile app, PATMobile. Available for use on both Android and iOS devices, the handy app works with the PrimeTest 50 to enable the digital input and storage of pass/fail results alongside barcode scanning, label printing* and photo tagging.

The PrimeTest 50 is an obvious choice if you're looking for a reliable, portable safety tester that's effortless to use.

*Print label feature only available for Android devices

Key Features

- Simple to use push button operation
- Easy-to-read display with LCD display – shows simple pass/fail indication
- Accurate and reliable earth continuity testing
- Handheld and battery powered
- Compatible with free PATMobile app – enables you to log results, export your data, tag photos and print results*

Electrical/Analysis Test Functions

- Mains supply check
- IEC lead test
- Earth continuity (200mA)
- Insulation resistance (500V)

Ideal for

- Basic, low-volume testing



Get more from your manual PAT tester with our free and powerful mobile app.

Scan QR code to watch video



www.seaward.co.uk/PrimeTest50

Tel: +44 (0) 191 587 8741

Email: sales@seaward.co.uk

Optional Accessory Kits Available	Part Number
PATBag Kit <ul style="list-style-type: none"> ■ Online PAT testing training course with exam ■ 30 day free trial of PATGuard Elements software ■ Durable, purpose-made PATBag with compartments for all of your PAT accessories and labels ■ 110V adaptor ■ 500 pass + 500 fail labels ■ Seaward Guide to PAT Testing ■ PAT reference look-up card ■ PAT logbook ■ Quick start video guide ■ PAT business builder CD-ROM and booklet Includes PrimeTest 50 PAT tester	345A929
PATBag Kit + PATGuard Elements software <p>The PATBag can optionally include PATGuard Elements manual data entry software – ideal for those who would like to keep an electronic register of assets and results including pass/fail results and retest dates.</p>	345A930

Technical Specifications

Earth Continuity

Test Current	+/- 200mA DC
PASS/FAIL Threshold	0.2Ω

Insulation Resistance

Test Voltages	500VDC
PASS/FAIL Threshold	2MΩ

IEC Lead Test

Tests Performed	Earth continuity Insulation resistance Live, neutral continuity and polarity
-----------------	--

Power Socket Test

Input Voltage Range	230V +10%, -15% AC
Indicators	Phase to earth voltage Phase to neutral voltage Neutral to earth

General Specifications

Dimensions	260 x 100 x 55mm (h x w x d)
Weight	800g
Power Source	6 x AA Batteries

Standard Accessories (supplied with PrimeTest 50)

0.5m extension adaptor	Earth bond lead
6 x AA batteries	Carry case

Optional Accessories

PATGuard Elements software (387A910)
 Test n Tag Pro Bluetooth/Serial printer with small (52 x 25mm) labels (compatible via PATMobile app, Android version only) (339A987)
 Roll of small labels (approx. 350 off 52x25mm labels) (339A947)
 110V to IEC adaptor (344A050)
 230 to 110V adaptor (270A076)
 3 phase adaptor – 16A 4 pin 415V (for Rpe & IR) (209A910)
 3 phase adaptor – 16A 5 pin 415V (for Rpe & IR) (209A911)
 3 phase adaptor – 32A 4 pin 415V (for Rpe & IR) (209A912)
 3 phase adaptor – 32A 5 pin 415V (for Rpe & IR) (209A913)
 PAT checkbox (227A910)
 PowerCheck 1557 (369A910)
 1000 x Pass labels (91B038)
 1000 x Fail labels (91B311)
 100 x Rhinotags (91B309)
 250 x Barcode appliance no. labels (compatible via PATMobile app, Android version only) (194A307)
 Rechargeable batteries and charger (339A950)

Training

Seaward offer a range of PAT testing courses, including City & Guilds. Go to www.seaward.co.uk/training for more information.

Services

1 year warranty subject to product registration with Seaward, visit www.seaward.co.uk/register-product

Service and calibration by Calibrationhouse.

Go to www.calibrationhouse.com for more information.

Part Numbers

PrimeTest 50	347A910
PrimeTest 50 PATbag kit	345A929
PrimeTest 50 PATbag kit + PATGuard Elements	345A930

Also Available in this Range

PrimeTest 100	344A910
PrimeTest 250+	403A910