




Parts Information:
Reciprocating Saw 850W/230V
Model No: SRS850



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk



Parts Information:
Reciprocating Saw 850W/230V
Model No: SRS850

Item	Part No.	Description
1	SRS850.01	Arbor Holder
2	SRS850.02	Retaining Ring 16mm for Shaft
3	SRS850.03	Lock Cap
4	SRS850.04	Tool Rod Holder
5	SRS850.05	Torsion Spring
6	SRS850.06	Spring Clamp
7	SRS850.07	Arbor Pin
8	SB-5.0	Steel Ball 5.0mm
9	SRS850.09	Arbor
10	SCB56.SB	Socket Head Cap Screw M5x6 Black
11	SRS850.11	Spring
12	SRS850.12	Arbor Holder Bottom Plate
13	FWM6.S	Flat washer m6 single
14	B/608ZZ	Bearing 608zz
15	SRS850.15	Gearbox
16	B/6000	Bearing 6000
17	SRS850.17	Armature
18	SRS850.18	Stator
19	SCB435.SB	Socket Head Cap Screw M4x35 Black
20	SRS850.20	Arbor Block
21	SRS850.21	Plastic Lock Cap Sleeve
22	SRS850.22	Arbor Block Plate (Punch)
23	MSC512.S	Csk Phillips Machine Screw M5x12 (Single)
24	MSP512.S	Machine Screw Pan Head Phillips M5x12mm (Single)
25	SRS850.25	Indicator Cover
26	MSP418.S	Machine Screw Pan Head Phillips M4x18mm (Single)
27	SRS850.27	Cylindrical Pin M8x40
28	SRS850.28	Gear
29	SRS850.29	Cylindrical Pin 5.9x15.5mm

Item	Part No.	Description
30	SRS850.30	Cylindrical Pin Sleeve
31	SRS850.31	Middle Cover (Punch)
32	SRS850.32	Cover Plate (Punch)
33	SRS850.33	Lock Button
34	SRS850.34	Housing Complete
35	SRS850.35	Carbon Brush Holder (Pair)
36	SRS850.36	Carbon Brush (Pair)
37	SRS850.37	Carbon Brush Cover (Pair)
38	MSC48.SB	Csk Phillips Machine Screw M4x8 Black
39	SRS850.39	Handle
40	SCB46.SB	Socket Head Cap Screw M4x6 Black
41	SRS850.41	Rotary Lock Button
42	SRS850.42	Rotary Lock Button Spring
43	SRS850.43	PCB (c/w indicator Light)
44	SRS850.44	Switch (Black)
45	MSC414.S	Csk Phillips Machine Screw M4x14 (Single)
46	SRS850.46	Cable Grip
47	SRS850.47	Cable Sleeve
48	SRS850.48	Main Cable
49	SN6.S	Steel Nut M6 Zinc Din934 (Single)
50	SRS850.50	Dust Protection
51	SRS850.51	Dust Protection Bush
52	SRS850.52	Anti-vibration foot 4x8.5mm
53	FWM8.S	Flat washer M8 Single
54	SRS850.54	Csk Phillips Machine Screw M4x57
55	SRS850.55	Wind Guard
56	SRS850.56	Plastic Cap
57	SRS850.57	Wood Cutting Blade
58	SRS850.58	Metal Cutting Blade

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk