



3W COB LED WORKLIGHT WITH CLAMP

MODEL NO: **LED100C**

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to instructions

1. SAFETY

1.1. GENERAL SAFETY

- x **DO NOT** shine directly into your, another person's or an animal's eyes.
- x **DO NOT** allow children to use the torch.
- x **DO NOT** use the torch if you suspect that the battery or the torch casing is damaged.
- x **DO NOT** leave batteries in a discharged state. Before storage remove batteries and dispose of in the correct manner.

1.2. BATTERY SAFETY

- WARNING!** To reduce the risk of burns or fire:
 - x **DO NOT** attempt to open the batteries.
 - x **DO NOT** crush, puncture, short contacts or dispose of in fire or water.
 - x **DO NOT** expose to temperatures above 60°C (140°F).
 - ✓ Replace only with the batteries designed for this product.
 - ✓ Recycle or dispose of used batteries as stipulated by local regulation.
 - ✓ If the electrolyte in the batteries gets on your skin, thoroughly wash with soap and water. If it gets in your eyes, rinse thoroughly with cool water and seek immediate medical attention.

2. INTRODUCTION

3W COB LED that produces up to 250lm. Made from tough ABS plastic with a moulded grip and a soft finish. Clamp opens up to 3 inches. Lamp can be separated from the grip and used as a small hand held torch or mounted to any magnetic surface. Features 360 degree rotating ball joint to allow for greater coverage. Requires 3 x AA batteries (not Included)

3. SPECIFICATION

Model No.:..... **LED100C**
Batteries:..... 3 x AA (not included)
LED qty.: 1 x 3 W COB
Lumen output:..... 250 lm
Operating time: 5 hrs

4. OPERATION

4.1. REMOVING LAMP FROM CLAMP

- 4.1.1. The lamp can be removed from the clamp mount by depressing the small tab on the underside of the lamp mounting base and sliding the lamp upwards and away from the tab.

4.2. BATTERY

- 4.2.1. To insert or replace batteries, twist and separate the light housing and light mounting base in opposite directions to expose the battery compartment.
- 4.2.2. Insert the new batteries according to the polarity markings in the base and reassemble the unit.

4.3. ON / OFF SWITCH

- 4.3.1. To turn the light on depress the button (fig.1). One further press of the button will turn the light off.

NOTE: When the lamp is separated from the clamp it can be mounted to any magnetic surface or used as a small hand held torch.





ENVIRONMENT PROTECTION

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.



WEEE REGULATIONS

Dispose of this product at the end of its working life in compliance with the EU Directive on Waste Electrical and Electronic Equipment (WEEE). When the product is no longer required, it must be disposed of in an environmentally protective way. Contact your local solid waste authority for recycling information.



BATTERY REMOVAL

Under the Waste Batteries and Accumulators Regulations 2009, Jack Sealey Ltd are required to inform potential purchasers of products containing batteries (as defined within these regulations), that they are registered with Valpak's registered compliance scheme. Jack Sealey Ltd Batteries Producer Registration Number (BPRN) is BPRN00705.

Note: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

Important: No Liability is accepted for incorrect use of this product.

Warranty: Guarantee is 12 months from purchase date, proof of which is required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk