


PARTS FOR:

CORDLESS OSCILLATING MULTI-TOOL 18V

MODEL: CPMT18V



ITEM	PART NO	DESCRIPTION	ITEM	PART NO	DESCRIPTION
1	CPMT18V.01	SCREW (M5x16)	18	CPMT18V.18	PUSH BUTTON SWITCH
2	CPMT18V.02	WASHER	19	CPMT18V.19	TOGGLE SWITCH
3	SMTA1	MULTI-TOOL BLADE SET 3pc	20	CPMT18V.20	SPEED CONTROL BOARD
4	CPMT18V.04	DRIVE SHAFT	21	CPMT18V.21	INSERT FRAME
5	CPMT18V.05	DIAL	22	CPMT18V.22	INSERT COVER
6	CPMT18V.06	BEARING (6900Z)	23	CP5418VBP	CORDLESS POWER TOOL BATTERY 18V
7	CPMT18V.07	FIXED BLOCK	24	CPMT18V.24	HOUSING (LEFT)
8	CPMT18V.08	NEEDLE BEARING (HK0808)	25	CPMT18V.25	HOUSING (RIGHT)
9	CPMT18V.09	NEEDLE BEARING (HK0509)	26	CPMT18V.26	SCREW (ST3x14)
10	CPMT18V.10	ROLLER BEARING			
11	CPMT18V.11	CONNECTING SHAFT	<u>ACCESSORIES</u>		
12	CPMT18V.12	BEARING (6901Z)		SMTA2	MULTI-TOOL HALF-MOON CUTTING BLADE
13	CPMT18V.13	RUBBER SLEEVE		SMTA3	MULTI-TOOL CARBIDE TIPPED HALF-MOON CUTTING BLADE
14	CPMT18V.14	SCREW (M4x6)		SMTA4	MULTI-TOOL DIAMOND CUTTING BLADE
15	CPMT18V.15	MOTOR FIXED PLATE		SMTA5	MULTI-TOOL SANDING SHEET SET 20pc
16	CPMT18V.16	MOTOR GEAR		SMTA6	MULTI-TOOL 75mm TRIANGLE SANDING PAD
17	CPMT18V.17	MOTOR		0.11.10	MOETI 100E 70MM TRANSEE OF MONOTING

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. **IMPORTANT**: No liability is accepted for incorrect use of product.

Sole UK Distributor,

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

INFORMATION: For a copy of our latest catalogue and promotions call us on 01284 757525 and leave your full name and address, including postcode.







