



**9203 OVER-SPECTACLES,  
9208, 9209, 9212 SPORTS STYLE SAFETY GLASSES  
9213 9214 9215 ZANTE STYLE SAFETY GLASSES**



Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.



**REFER TO INSTRUCTIONS**

**IMPORTANT:** PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.

## 1. INTRODUCTION

<b>9203</b>	Over-Spectacles	Fits over most prescription glasses. Clear lightweight polycarbonate design. Ideal for visitors use.
<b>9208</b>	Sports Style Clear Safety Glasses with Adjustable Arms	Clear polycarbonate lens. Adjustable arms to fit all head sizes. Wraparound design for increased protection. Soft, comfortable nose bridge.
<b>9209</b>	Sports Style Shaded Safety Specs with Adjustable Arms	UV 400 shaded lens protects from sun rays. Adjustable arms to fit all head sizes. Wraparound design for increased protection. Soft, comfortable nose bridge.
<b>9212</b>	Sports Style High-Vision Safety Glasses with Adjustable Arms	Yellow lens improves vision in low light conditions. Adjustable arms to fit all head sizes. Wraparound design offers increased protection. Soft, comfortable nose bridge.
<b>9213</b>	Zante Style Clear Safety Glasses with Flexi Arms	Clear polycarbonate lens. Sports style, soft durable flexi arms. Soft, comfortable nose bridge.
<b>9214</b>	Zante Style Smoke Lens Safety Glasses with Flexi Arms	Offers protection against sun glare. Polycarbonate lens. Zante style, soft durable flexi arms. Soft, comfortable nose bridge.
<b>9215</b>	Zante Style Amber Lens Safety Glasses with Flexi Arms	Yellow lens, suitable for indoor/outdoor use. Improves vision in low light conditions. Polycarbonate lens. Zante style, soft durable flexi arms. Soft, comfortable nose bridge.

## 2. SAFETY

- ✓ This product is designed for eye protection against high speed particles of low energy impact. They are designed to be lightweight and comfortable to wear.
- ✓ The product protects against high speed particles, but may transmit impacts, thus creating a hazard to the wearer.
- ✓ Avoid liquids as small particles can splash into the eyes.
- ✓ Inspect the glasses frequently as a pitted or scratched face shield reduces vision and should be replaced immediately.
- ✗ **DO NOT** use if any part of the glasses is cracked or broken.
- ✗ **DO NOT** place this product on a hot surface.
- ✗ **DO NOT** use these glasses for protection against short circuit electric spark, fine dust, gas, ultra violet or infra red radiation, ionising radiation, liquids under pressure or other severe hazards.
- ✗ **DO NOT** use these against heavy impact hazards.

## 3. SPECIFICATION

This product meets the requirements of the standard BS EN 166.

- 3.1. **OPTICAL CLASS** - 1 - suitable for work with high vision requirements for permanent use.
- 3.2. **MECHANICAL RESISTANCE** - F - Low Energy Impact

## 4. MAINTENANCE

### 4.1. CLEANING

- ✗ **DO NOT** use abrasive materials.
- ✓ Using a soft and clean brush or cloth, use warm suds to wash and clean. Ensure hands are clean (without grease).
- ✓ Materials which may come into contact with the wearer's skin could cause allergic reactions to susceptible individuals. The contact areas should be disinfected regularly.

### 4.2. STORAGE

- ✓ Store in a bag or case out of direct sunlight, away from chemicals and abrasive substances, in a clean dust free environment.
- ✓ Use original bag for transportation if possible.

## 5. EXPIRY DATE

- 5.1. Product shelf life/expiry date is 5 years from date of manufacture, after which the product should be replaced.

This document has been drawn up according to Regulation (EU) 2016/425 as amended to apply to GB for Personal Protective Equipment. The declaration of conformity can be accessed at [www.sealey.co.uk](http://www.sealey.co.uk).



**ENVIRONMENT PROTECTION**

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.



REGISTER YOUR PURCHASE HERE

**Note:** It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

**Important:** No Liability is accepted for incorrect use of this product.

**Warranty:** Guarantee is 12 months from purchase date, proof of which is required for any claim.

EU | Sealey EU Ltd, Farney Street, Carrickmacross, Co. Monaghan, A81 PK68 Ireland

UK | Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



[sales@sealey.co.uk](mailto:sales@sealey.co.uk)



[www.sealey.co.uk](http://www.sealey.co.uk)