



This worksheet is copyright © 2009 New Wave Concepts Limited. All rights reserved. It may be photocopied for classroom or non-commercial use. **www.genieonline.com** 

Page 1 of 7 • F214 GENIE C14 Project Board.pdf • Version 1.0 (June 2009)



Switch on the soldering iron. It will only take a few minutes for the iron to reach operating temperature. Once the soldering iron is hot, clean the soldering iron tip with a moist sponge.

Melt some solder at the chamfered end of the soldering iron tip. This is called 'tinning' and it will aid the flow of solder from the soldering iron to the copper track on the printed circuit board and component pins.



#### Magic Ingredients!

This is what you will need:

Component	Quantity
GENIE C14 microcontroller	1
GENIE C14 project board (PCB2	14) 1
Download (3.5mm stereo) socke	
14-pin DIL socket	1
Battery clip	1
3 or 4 x AA battery holder	1
MPSA14 transistor	2
1N4001 diode	2
1N4148 diode	1
220uF electrolytic capacitor	1
100nF capacitor	1
Green LED	1
330 ohm resistor	1
(orange, orange, br	
1k ohm resistor	2
(brown, black	
10k ohm resistor (brown, black, ol	5 
22k ohm resistor	1
(red, red, o	range, gold)
100k ohm resistor (brown, black, y	1 ellow, gold)

# Making the GENIE 2 $\uparrow$

EN

Fit each component onto the board. When fitting components such as resistors, you should use long-nosed pliers to bend the legs through 90 degrees. This will make them easier to fit.

Some of the components need to be fitted the correct way around:

- The GENIE microcontroller should be positioned so that the notch points towards the download socket and the dot next to pin 1 is at the same corner as the '1' shown on the board.
- The green LED should be fitted so that the flat edge of the LED lines up with the flat edge shown on the board.
- Diodes should be positioned so that the stripe on the diode matches the stripe on the board.
- The flat side of the transistors must match the flat sides shown on the board.
- When fitting the electrolytic capacitor, you need to ensure that the positive side of the capacitor (the side without the stripe) is nearest to the '+' sign on the board.

To solder a pin, hold the soldering iron onto the board for a few seconds, then quickly touch the tip with a small amount of solder.

You should always remember to replace the soldering iron back into the stand after soldering and repeat cleaning the tip of the iron with the moist sponge before the start of each soldering operation.

Finally, cut off any excess wire or component legs for a tidy finish.







This worksheet is copyright © 2009 New Wave Concepts Limited. All rights reserved. It may be photocopied for classroom or non-commercial use. **www.genieonline.com** 

Page 2 of 7 • F214 GENIE C14 Project Board.pdf • Version 1.0 (June 2009)







## Telling the GENIE your wishes 3

For your project to work, you need to tell the GENIE microcontroller what it should do.

This involves writing a sequence of commands in a **flowchart**. Your flowchart is then sent down the cable and stored on the GENIE chip. By changing the flowchart, you can vary how the GENIE behaves.

First of all, you need to tell GENIE which type of chip you are using. To do this, Run Live click on the Microcontroller button on the toolbar and choose Program Settings. F5 💥 Debug Live Shift+F5 Select a GENIE C14 chip. Control Device Choose the type of microcontroller you wish to use in your flowchart program: Ok y Calibrate Sensor The inputs and output signals for this type CORE Cancel GENIE C14 of microcontroller are fixed, so click on **OK** View: 💽 Signals C Device Help 💐 Program Check when you are ready to continue. This microcontroller has the following signals: Program Settings.. Outputs Inputs A0 (shared) DO < < < < < QŨ D1 Q1 > > > > >D2 Q2 Gallery x D3 Q3 🔄 Flowchart Symbols • A4 (shared) D4 04 05 \* Assistant Program Control -A GENIE microcontroller can be made to perform different tasks by connecting together flowchart commands. Each command will be run in turn. 6 Gallery Start Start Start the flowchart program. 品 Stop Stop Stop this flowchart Program program. Magical Effects! Digital These are the input and output Digital Test the inputs with a signals available in your flowchart: given pattern. Outputs Outputs Description Set the outputs to a Input given signal pattern. Analogue or digital A/D0 <u>High</u> High Set an output signal to Digital D1 to D3 high (logic 1). Analogue or digital A/D4 Description Output Green LED You can now decide which commands you 00 Low-power Q1 to Q3 want your GENIE to perform. To do this, Medium-power drag commands from the Gallery. Q4 and Q5 See the next worksheet for flowchart ideas.



This worksheet is copyright © 2009 New Wave Concepts Limited. All rights reserved. It may be photocopied for classroom or non-commercial use. **www.genieonline.com** Page 3 of 7 ◆ **F214** GENIE C14 Project Board.pdf ◆ Version 1.0 (June 2009)







### Telling the GENIE your wishes

Making sounds or playing tunes

#### Turning outputs on and off

You can use GENIE to turn outputs on and off.

High	7
Low	7
Outputs	7


Use the **HIGH** command to turn a single output on.

Use the **LOW** command to turn a single output off.

Use the **OUTPUTS** command to control several outputs.

There are six outputs on the project board, a green LED on output **Q0**, three low-power outputs (on **Q1**, **Q2** and **Q3**) and two medium-power outputs (on **Q4** and **Q5**).


Double-clicking on an output command allows you to control these signals, for example:




This will light the green LED.

In addition to changing the output, you can also add a delay (GENIE programs run very quickly and without a wait, sometimes signals change too fast for you to see!).

The flowchart on the right uses the HIGH and LOW commands to turn the green LED on output Q0 on and off.



It loops back to make the flashing repeat.





Use the **SOUND** command to play a single note.


Use the **TUNE** command to play a whole musical tune.

To make a sound, you should connect up a sounder or loudspeaker to an output (Q1 to Q5) and then use the SOUND command as follows:

Sound Properties	×
Generate a sound output signal:	ОК
Type: O Music O Value	Cancel
Note: 5 C (middle C)	Help
Time: 1 seconds	
Signal: Q 4 💌 on IC pin 9	
Caption:	

This would play the note middle C for one second.

By playing two different notes (one after the other, as shown on the right), you can create an alarm. In this flowchart, the green LED is also flashed to give a visible as well as audible alarm.



You can use the TUNE command to play a whole tune such as a mobile telephone ring tone (see the GENIE CO8 jukebox kit to learn how you can play 2-channel polyphonic music).



This worksheet is copyright © 2009 New Wave Concepts Limited. All rights reserved. It may be photocopied for classroom or non-commercial use. **www.genieonline.com** Page 4 of 7 ◆ **F214** GENIE C14 Project Board.pdf ◆ Version 1.0 (June 2009)







### Telling the GENIE your wishes

#### Responding to digital signals

Some types of input signal, such as push switches, can only be either on or off. These are known as **digital** signals.




Use the **DIGITAL** command to respond to a digital signals.


The DIGITAL command allows you to make a decision based on whether a digital signal is either on or off.

When a digital signal is on, it has the value '1' whereas when it is off, it has the value '0'.

Double-click on the command to select which digital inputs you wish to check. GENIE will follow the 'Y' (yes) path when the digital signal matches the chosen pattern, otherwise it will follow the 'N' (no) path.



The above pattern will test if, for example, a push switch on digital input D0 is on (pressed). You can see below how to light the green LED on output Q0 whenever the switch is pressed:





This worksheet is copyright © 2009 New Wave Concepts Limited. All rights reserved. It may be photocopied for classroom or non-commercial use. www.genieonline.com

Responding to analogue signals

Other types of input signal, such as temperature or light, can be at a number of different levels. These are known as **analogue** signals.



Use the **ANALOGUE** command to respond to analogue signals.

The ANALOGUE command allows you to check if a signal lies within a given range.


With GENIE, analogue levels can vary between **0** (the lowest level) and **255** (the highest).

Double-click on the command to select a sensor to check and a range. GENIE will follow the ' $\mathbf{Y}$ ' (yes) path when the signal is in range, otherwise it will follow the ' $\mathbf{N}$ ' (no) path.

For example, to test if a light sensor on analogue signal A0 is between 0 and 100, you should enter the following:

	×
A0 💌	OK
	Cancel
	Help
to 100 ÷	<u></u>

In a flowchart, this would look like:





Page 5 of 7 • F214 GENIE C14 Project Board.pdf • Version 1.0 (June 2009)





Bringing the GENIE to life - | | × | \_ 8 × Running Live Istan (c) 20 Cancel a microcontroller our GENIE C14 program has been What would you like to do? With your program now running on the microcontroller, you can operate any switches or sensors on or connected to the circuit board. While running, the microcontroller will not talk to the computer or update any of the monitoring panels. Click on the Cancel button to finish. About this microcontroller - 🗆 × This microcontroller is based on a Microchip® PIC16F684 device Click <u>here</u> for more information. - 8 × MICROCHIP ۲ (b) Assistant Downloading -50% 3 💁 🔍 100% \* 🕮 USB 🔺 Ready Gallery Cancel As soon as the program has been downloaded you will see the Downloading program Please wait while your program is downloaded to the microcontrolle above screen (c) and GENIE will start running your flowchart. Your GENIE project is now ready

The green status LED on the project board will flash as the download takes place. It tells you everything is OK!



to go! You can disconnect the cable and use your GENIE board

away from the computer.



This worksheet is copyright © 2009 New Wave Concepts Limited. All rights reserved. It may be photocopied for classroom or non-commercial use. **www.genieonline.com** 

Page 6 of 7 • F214 GENIE C14 Project Board.pdf • Version 1.0 (June 2009)


AS

Once you have written your flowchart program, you need to store it on the GENIE chip. Here's how you do it:

- 1 Wire-up the built GENIE circuit board and connect up a suitable battery power supply.
- **2** Plug the GENIE cable into the download socket on the GENIE circuit board.
- 3 Once done, the Program panel in Circuit Wizard or GENIE Design Studio will then show a 'Connected' message (see picture a).
- 4 Click on the **Run Live** option. Your flowchart will be transferred onto the GENIE chip—this is known as **downloading** (see picture b).

- 0 ×

- 8 ×






The technical bit... it's only needed if you

want to learn more!



More information

This is the circuit diagram. It shows how all of the components in the circuit are connected. You can compare it to the layout of the components on the actual circuit board (shown below it).



Page 7 of 7 • F214 GENIE C14 Project Board.pdf • Version 1.0 (June 2009)