## according to Regulation (EC) No. 1907/2006 (REACH)

according to Regulation (EU) No 453/2010

Article No.: 114XXX000 PERFIX

Print date 01.11.2016 Revision date 01.11.2016 EN Version 1.0 Issue date 01.11.2016 Page 1 / 7

## 1. Identification of the substance/mixture and of the company/undertaking

## 1.1. Product identifiers

Article No. (manufacturer/supplier): 114XXX000 Identification of the substance or mixture PERFIX

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.3. Details of the supplier of the safety data sheet

## Supplier (manufacturer/importer/downstream user/distributor):

Daler-Rowney Ltd

Peacock Lane Telephone: +44 (0) 1344 461083
Bracknell, RG12 8SS Telefax: +44 (0) 1344 486511

**ENGLAND** 

Dept. responsible for information:

E-mail Philip.Gray@daler-rowney.com

1.4. Emergency telephone number

Emergency telephone: +44 (0) 1344 461000

### 2. Hazards identification

### 2.1. Classification of the substance or mixture

## Classification according to Regulation (EC) No. 1272/2008 [CLP]

This mixture is classified as hazardous according to regulation (EC) No. 1272/2008 [CLP].

Flam. Liq. 3 / H226 flammable liquids Flammable liquid and vapour.

STOT SE 3 / H336 Specific target organ toxicity (single May cause drowsiness or dizziness.

exposure)

#### 2.2. Label elements

The product is classified and labelled according to EC directives or corresponding national laws.

## Labelling according to Regulation (EC) No. 1272/2008 [CLP]

#### Hazard pictograms





## Warning

## **Hazard statements**

H226 Flammable liquid and vapour.
H336 May cause drowsiness or dizziness.

## **Precautionary statements**

P301 + P330 + P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.

P102 Keep out of reach of children. P103 Read label before use.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P233 Keep container tightly closed.

P243 Take precautionary measures against static discharge.
P261 Avoid breathing dust/fume/gas/mist/vapours/spray.
P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P303 + P361 + P353 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with

water/shower.

P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P312 Call a POISON CENTER or doctor/physician if you feel unwell.

P370 + P378 In case of fire: Use foam to extinguish.

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

P403 + P235 Store in a well-ventilated place. Keep cool.

P501 Dispose of contents/container in accordance with local legislation.

contains:

1-methoxy-2-propanol

### Supplemental Hazard information (EU)

## according to Regulation (EC) No. 1907/2006 (REACH)

according to Regulation (EU) No 453/2010

Article No.: 114XXX000 PERFIX

 Print date
 01.11.2016
 Revision date 01.11.2016
 EN

 Version
 1.0
 Issue date 01.11.2016
 Page 2 / 7

n.a.

#### 2.3. Other hazards

### 3. Composition / Information on ingredients

#### 3.2. Mixtures

## Product description / chemical characterization

**Description** Medium for watercolors

## Hazardous ingredients

Classification according to Regulation (EC) No. 1272/2008 [CLP]

EC No.	REACH No.		
CAS No.	Chemical name	Wt %	
INDEX No.	classification:	Remark	
203-539-1			
107-98-2	1-methoxy-2-propanol	50 - 100	
603-064-00-3	Flam. Liq. 3 H226 / STOT SE 3 H336		
216-455-5			
1589-47-5	2-methoxypropanol	< 0,5	
603-106-00-0	Flam. Lig. 3 H226 / Repr. 1B H360 / STOT SE 3 H335 / Skin Irrit. 2 H315		
	/ Eye Dam. 1 H318		

#### Additional information

Full text of classification: see section 16

### 4. First-aid measures

### 4.1. Description of first aid measures

#### **General information**

In all cases of doubt, or when symptoms persist, seek medical advice. In case of unconsciousness give nothing by mouth, place in recovery position and seek medical advice.

#### In case of inhalation

Remove casualty to fresh air and keep warm and at rest. In case of irregular breathing or respiratory arrest provide artificial respiration.

### Following skin contact

Remove contaminated, saturated clothing immediately. After contact with molten product, cool skin area rapidly with cold water. Allow stiffening. Take up mechanically. When in doubt or if symptoms are observed, get medical advice.

#### After eye contact

Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Seek medical advice immediately.

### After ingestion

If swallowed, rinse mouth with water (only if the person is conscious). When in doubt or if symptoms are observed, get medical advice.

## 4.2. Most important symptoms and effects, both acute and delayed

In all cases of doubt, or when symptoms persist, seek medical advice.

## 4.3. Indication of any immediate medical attention and special treatment needed

## 5. Firefighting measures

### 5.1. Extinguishing media

### Suitable extinguishing media

alcohol resistant foam, carbon dioxide, Powder, spray mist, (water)

## Extinguishing media which must not be used for safety reasons:

strong water jet

# 5.2. Special exposure hazards arising from the substance or preparation itself, its combustion products or from resulting gases:

Dense black smoke occurs during fire. Inhaling hazardous decomposing products can cause serious health damage.

## 5.3. Special protective equipment for firefighters:

Provide a conveniently located respiratory protective device.

## according to Regulation (EC) No. 1907/2006 (REACH)

according to Regulation (EU) No 453/2010

Article No.: 114XXX000 PERFIX

Print date 01.11.2016 Revision date 01.11.2016 EN Version 1.0 Issue date 01.11.2016 Page 3 / 7

## **Additional information**

Cool closed containers that are near the source of the fire. Do not allow water used to extinguish fire to enter drains, ground or waterways. Treat runoff as hazardous.

### 6. Accidental release measures

## 6.1. Personal precautions, protective equipment and emergency procedures

See protective measures under point 7 and 8.

#### 6.2. Environmental precautions

Do not allow to enter into surface water or drains. If the product contaminates lakes, rivers or sewages, inform competent authorities in accordance with local regulations.

#### 6.3. Methods and material for containment and cleaning up

Take up mechanically, placing in appropriate containers for disposal. Clean using cleansing agents. Do not use solvents.

### 6.4. Reference to other sections

Observe protective provisions (see chapter 7 and 8).

## 7. Handling and storage

#### 7.1. Precautions for safe handling

#### Advices on safe handling

Follow the legal protection and safety regulations.

#### Precautions against fire and explosion:

Usual measures for fire prevention.

#### 7.2. Conditions for safe storage, including any incompatibilities

## Requirements for storage rooms and vessels

Storage in accordance with the Ordinance on Industrial Safety and Health (BetrSiVO). Keep container tightly closed.

## Further information on storage conditions

Take care of instructions on label. Store in a well-ventilated and dry room at temperatures between 15 °C and 30 °C. Protect from heat and direct sunlight. Keep container tightly closed.

### 7.3. Specific end use(s)

Observe technical data sheet. Observe instructions for use.

## 8. Exposure controls / Personal protection

## 8.1. Control parameters

### Occupational exposure limit values:

1-methoxy-2-propanol

INDEX No. 603-064-00-3 / EC No. 203-539-1 / CAS No. 107-98-2

TWA: 375 mg/m3; 100 ppm STEL: 560 mg/m3; 150 ppm

#### **Additional information**

TWA : long-term occupational exposure limit value STEL : short-term occupational exposure limit value

Ceiling: peak limitation

#### **DNEL:**

1-methoxy-2-propanol

INDEX No. 603-064-00-3 / EC No. 203-539-1 / CAS No. 107-98-2

DNEL long-term dermal (systemic), Workers: 50,6 mg/kg

DNEL acute inhalative (local), Workers: 553,5 mg/m³

DNEL long-term inhalative (systemic), Workers: 369 mg/m<sup>3</sup>

DNEL long-term dermal (systemic), Consumer: 18,1 mg/kg

DNEL long-term inhalative (systemic), Consumer: 43,9 mg/m³

## PNEC:

1-methoxy-2-propanol

INDEX No. 603-064-00-3 / EC No. 203-539-1 / CAS No. 107-98-2

PNEC aquatic, freshwater: 10 mg/L PNEC aquatic, marine water: 1 mg/L

## according to Regulation (EC) No. 1907/2006 (REACH)

according to Regulation (EU) No 453/2010

Article No.: 114XXX000 PERFIX

 Print date
 01.11.2016
 Revision date 01.11.2016
 EN

 Version
 1.0
 Issue date 01.11.2016
 Page 4 / 7

PNEC sediment, freshwater: 41,6 mg/kg PNEC sediment, marine water: 4,17 mg/kg PNEC sewage treatment plant (STP): 100 mg/L

### 8.2. Exposure controls

Provide good ventilation. This can be achieved with local or room suction. If this should not be sufficient to keep aerosol and solvent vapour concentration below the exposure limit values, a suitable respiratory protection must be used.

### Occupational exposure controls

### Respiratory protection

If concentration of solvents is beyond the occupational exposure limit values, approved and suitable respiratory protection must be used. Observe the wear time limits according GefStoffV in combination with the rules for using respiratory protection apparatus (BGR 190). Use only respiratory protection equipment with CE-symbol including four digit test number.

#### Hand protection

For prolonged or repeated handling the following glove material must be used: NBR (Nitrile rubber)

Thickness of the glove material > 0,4 mm; Breakthrough time (maximum wearing time) > 480 min.

Observe the instructions and details for use, storage, maintenance and replacement provided by the protective glove manufacturer. Penetration time of glove material depending on intensity and duration of exposure to skin. Recommended glove articles DIN EN 374

Barrier creams can help protecting exposed skin areas. In no case should they be used after contact.

## Eye protection

Wear closely fitting protective glasses in case of splashes.

#### Protective clothing

Wear antistatic clothing of natural fibers (cotton) or heat resistant synthetic fibers.

#### Protective measures

After contact clean skin thoroughly with water and soap or use appropriate cleanser.

## **Environmental exposure controls**

Do not allow to enter into surface water or drains. See chapter 7. No additional measures necessary.

## 9. Physical and chemical properties

## 9.1. Information on basic physical and chemical properties

Appearance:

Physical state liquid
Colour refer to label
Odour characteristic

Safety relevant basis data		Unit	Method	Remark
Flash point (°C)	< 60	°C	DIN 53213	
Ignition temperature in °C:	270	°C		
Lower explosion limit	3,0	Vol-%		
Upper explosion limit	12,0	Vol-%		
Vapour pressure at 20 °C:	11,30	mbar		
Density at 20 °C:	1,00	g/cm³		
Water solubility (g/L)	completely miscible			
pH at 20 °C:	50,00	7,0		
Viscosity at 20 °C	< 10	mPa·s		
Solvent separation test (%)	< 3	%		
Solid content (%):	0,00	Wt %		
solvent content:				
Organic solvents::	85	Wt %		
Water:	0	Wt %		
Other information.				

## 9.2. Other information:

## 10. Stability and reactivity

## 10.1. Reactivity

## 10.2. Chemical stability

Stable when applying the recommended regulations for storage and handling. Further information on correct storage: refer to chapter 7.

## 10.3. Possibility of hazardous reactions

## according to Regulation (EC) No. 1907/2006 (REACH)

## according to Regulation (EU) No 453/2010

Article No.: 114XXX000 PERFIX

Print date 01.11.2016 Revision date 01.11.2016 EN Version 1.0 Issue date 01.11.2016 Page 5 / 7

Keep away from strong acids, strong bases and strong oxidizing agents to avoid exothermic reactions.

#### 10.4. Conditions to avoid

Stable when applying the recommended regulations for storage and handling. Further information on correct storage: refer to chapter 7. Hazardous decomposition byproducts may form with exposure to high temperatures.

#### 10.5. Incompatible materials

#### 10.6. Hazardous decomposition products

Hazardous decomposition byproducts may form with exposure to high temperatures, e.g.: carbon dioxide, carbon monoxide, smoke. Decomposition takes place from temperatures above: at 160 °C

### 11. Toxicological information

Classification according to Regulation (EC) No. 1272/2008 [CLP]

No data on preparation itself available.

### 11.1. Information on toxicological effects

#### **Acute toxicity**

1-methoxy-2-propanol oral, LD50, Rat: 4016 mg/kg dermal, LD50, Rabbit: 2000 mg/kg

### skin corrosion/irritation; Serious eye damage/eye irritation

Toxicological data are not available.

#### Respiratory or skin sensitisation

Toxicological data are not available.

## CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Toxicological data are not available.

## Specific target organ toxicity

Toxicological data are not available.

## **Aspiration hazard**

Toxicological data are not available.

### Practical experience/human evidence

Other observations:

## **Overall Assessment on CMR properties**

EC No.	Chemical name	Classification according to	
CAS No.		Regulation (EC) No. 1272/2008	
		[CLP]	
216-455-5	2-methoxypropanol	Repr. 1B	
1589-47-5	• •	·	

## Remark

There is no information available on the preparation itself.

## 12. Ecological information

## overall evaluation

Classification according to Regulation (EC) No. 1272/2008 [CLP]

There is no information available on the preparation itself.

Do not allow to enter into surface water or drains.

## 12.1. Toxicity

1-methoxy-2-propanol

Fish toxicity, LC50, Leuciscus idus (golden orfe): 6812 mg/L (96 h)

Daphnia toxicity, EC50, Daphnia magna (Big water flea): 23300 mg/L (48 h)

#### Long-term Ecotoxicity

Toxicological data are not available.

## 12.2. Persistence and degradability

Toxicological data are not available.

#### 12.3. Bioaccumulative potential

## according to Regulation (EC) No. 1907/2006 (REACH)

according to Regulation (EU) No 453/2010

Article No.: 114XXX000 PERFIX

 Print date
 01.11.2016
 Revision date 01.11.2016
 EN

 Version
 1.0
 Issue date 01.11.2016
 Page 6 / 7

1-methoxy-2-propanol

Distribution coefficient (n-octanol / water) (log P O/W): -0,44

Method: Log KOC

### **Bioconcentration factor (BCF)**

Toxicological data are not available.

#### 12.4. Mobility in soil

Toxicological data are not available.

#### 12.5. Results of PBT assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

#### 12.6. Other adverse effects

## 13. Disposal considerations

#### 13.1. Waste treatment methods

#### Appropriate disposal / Product

#### Recommendation

Do not allow to enter into surface water or drains. This material and its container must be disposed of in a safe way. Waste disposal according to directive 2008/98/EC, covering waste and dangerous waste.

## List of proposed waste codes/waste designations in accordance with EWC

140603 other solvents and solvent mixtures

packaging

#### Recommendation

Non-contaminated packages may be recycled. Vessels not properly emptied are special waste.

## 14. Transport information

14.1. UN number

UN 1993

14.2. UN proper shipping name

Land transport (ADR/RID): Flammable liquid, n.o.s.

(1-methoxy-2-propanole)

Sea transport (IMDG): FLAMMABLE LIQUID, N.O.S.

(1-methoxy-2-propanole)

Air transport (ICAO-TI / IATA-DGR): Flammable liquid, n.o.s.

(1-methoxy-2-propanole)

14.3. Transport hazard class(es)

3

14.4. Packing group

Ш

14.5. **Environmental hazards** 

Land transport (ADR/RID) n.a.

Marine pollutant n.a.

### 14.6. Special precautions for user

Transport always in closed, upright and safe containers. Make sure that persons transporting the product know what to do in case of an accident or leakage.

Advices on safe handling: see parts 6 - 8

## **Additional information**

## Land transport (ADR/RID)

tunnel restriction code D/E

Sea transport (IMDG)

EmS-No. F-E. S-E

## 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

not applicable

## according to Regulation (EC) No. 1907/2006 (REACH) according to Regulation (EU) No 453/2010

Article No .: 114XXX000 **PFRFIX** 

Print date 01.11.2016 Revision date 01.11.2016 ΕN Page 7 / 7 Version Issue date 01.11.2016

#### 15. Regulatory information

## 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### **EU** legislation

Information according to 1999/13/EC about limitation of emissions of volatile organic compounds (VOC-guideline).

VOC-value (in g/L) ISO 11890-2: 935 VOC-value (in g/L) ASTM D 2369: 935

## **National regulations**

## **Restrictions of occupation**

Observe employment restrictions under the Maternity Protection Directive (92/85/EEC) for expectant or nursing mothers. Observe restrictions to employment for juvenils according to the 'juvenile work protection guideline' (94/33/EC).

## Other regulations, restrictions and prohibition regulations

#### 15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this preparation were not carried out.

#### 16. Other information

#### Full text of classification in section 3:

Flam. Liq. 3 / H226 flammable liquids Flammable liquid and vapour. STOT SE 3 / H336 Specific target organ toxicity (single May cause drowsiness or dizziness.

exposure)

Repr. 1B / H360 Reproductive toxicity May damage the unborn child. Specific target organ toxicity (single May cause respiratory irritation.

STOT SE 3 / H335

exposure)

Skin Irrit. 2 / H315 skin corrosion/irritation Causes skin irritation.

Eye Dam. 1 / H318 Serious eye damage/eye irritation Causes serious eye damage.

## **Additional information**

Classification according to Regulation (EC) No. 1272/2008 [CLP]

The information supplied on this safety data sheet complies with our current level of knowledge as well as with national and EU regulations. Without written approval, the product must not be used for purposes different from those mentioned in chapter 1.It is always the user's duty to take any necessary measures for meeting the requirements laid down by local rules and regulations. The details in this safety data sheet describe the safety requirements of our product and are not to be regarded as guaranteed attributes of the product.