Report No.: MPIJTRYL872437V2

# **MSDS** Report

Sample Name & Model	NI-MH BATTERY 2*AAA
Applicant -	ENIX ENERGIES
Address	27 Rue des Glairaux, BP231, 38120 Saint-Egrève cedex France

## Statement

- 1. The conclusion of the certificate/report is responsible for the provided sample only.
- 2. The applicant shall provide accurately and truly the description and statement of the sample, shall guarantee to match the sample and real situation which they provided and declared. Otherwise the application shall bear any relevant consequences and responsibility.
- 3. In case the sample and documents provided involved in the situation of fake and forgery, any consequences and responsibility caused by this shall be undertaken by applicant.
- 4. The certificate/report is invalid in case of illegal transfer, embezzlement, imposture, modification or any altering, reproducing except in full.
- 5. The certificate/report takes no account of the differences of countries and applicants.
- 6. We have the right to dispose the provided sample after approval of certificate/report.

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 1 of 10

### **Material Safety Data Sheet**

Reference to ST/SG/AC. 10/30/Rev.9(GHS)

#### Section 1 - Chemical Product and Company Identification

Chemical Product Identification
Sample Name: NI-MH Battery

Sample Model: 2\*AAA Recommended Uses: N/A Restrictions on Use: N/a

**Supplier Name:** ENIX ENERGIES

Address: 27 Rue des Glairaux, BP231, 38120 Saint-Egrève cedex France

Phone Number: 0 825 88 65 11

Fax: /

E-mail: commercial@enix-energies.com Emergency Phone Number: 0 825 88 65 11

#### Section 2 - Hazards Identification

#### **Emergency overview:**

This product is a battery. Intended use of the product should not result in exposure to the chemical substance. In case of rupture the below hazards exist.

#### Classification according to GHS

Acute toxicity, oral (4)

Acute toxicity, inhalation: Dusts and mists (4)

Skin corrosion/irritation (1A, 1B, 1C) Sensitisation, respiratory (1, 1A, 1B)

Sensitisation, skin (1, 1A, 1B)

Carcinogenicity (2)

Specific target organ toxicity, single exposure; Respiratory tract irritation (3)

Specific target organ toxicity, repeated exposure (2)

Hazardous to the aquatic environment, long-term hazard (1)

#### Label elements

**Hazard Pictograms(s):** 



Signal word: Danger

#### Hazard statement(s):

H302 Harmful is swallowed

H332 Harmful is inhaled

H314 Causes severe skin burns and eye damage

H334 May cause allergy or asthma symptoms or breathing difficulties if inhaled

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 2 of 10

- H317 May cause and allergic skin reaction
- H351 Suspected of causing cancer
- H335 May cause respiratory irritation
- H373 May cause damage to organs through prolonged or repeated exposure
- H410 Very toxic to aquatic life with long lasting effects

#### Precautionary statement(s):

#### Prevention:

- P201 Obtain special instructions before use.
- P202 Do not handle until all safety precautions have been read and understood.
- P260 Do not breathe dusts or mists.
- P264 Wash skin and clothing thoroughly after handling.
- P270 Do not eat, dring or smoke when using this product.
- P271 Use only outdoors or in a well-ventilated area.
- P273 Avoid release to the environment.
- P280 Wear protective gloves, protective clothing, eye protection, face protection.

#### Response:

- P330 Rinse mouth.
- P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
- P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER.
- P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
- P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.
- P363 Wash contaminated clothing before reuse.
- P321 Specific treatment (See additional emergency instructions).
- P391 Collect spillage.

#### **Storage**

P405 Store locked up.

#### Disposal:

P501 Send contents to approved waste treatment plants.

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 3 of 10

#### Section 3 - Composition/Information on Ingredients

#### Chemical characterization: Mixture

Chemical Composition	CAS NO.	EC#	Weight (%)
Nickel Hydroxide	12054-48-7	235-008-5	35
Nickel alloy, base, Ni,Al,Co,Cr,Mo,Ti (IN 731)	12604-68-1	603-119-1	40
Cobalt oxide	1307-96-6	215-154-6	5
Cellulose, carboxymethyl ether	9000-11-7	618-326-2	2
Polytetrafluoroethylene resin	9002-84-0	618-337-2	3
Graphite	7782-42-5	231-955-3	5

#### Section 4 - First Aid Measures

#### **Description of first aid measures**

General information No special measure required.

#### After eye contact

Flush eyes with plenty of water for several minutes while holding eyelids open. Get medical attention if irritation persists.

#### After skin contact

Remove contaminated clothing and shoes. Immediately wash with water and soap and rinse thoroughly. Wash clothing and shoes before reuse. If irritation occurs, get medical attention.

#### After inhalation

Remove victim to fres area. Administer artificial respiration if breathing is difficult. Seek medical attention.

#### After swallowing

Do not induce vomiting. Get medical attention.

Personal protective equipment for first-aid responders: No data availabel. Most important symptoms/effects, acute and delayed: No data available.

Indication of immediate medical attention and special treatment needed: Treat symptomatically.

#### Section 5 - Fire Fighting Measures

#### Suitable extinguishing media:

Use extinguishing agent suitable for local conditions and the surrounding environment. Such as dry powder, CO<sub>2</sub>.

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 4 of 10

#### Unsuitable extinguishing media:

No data available.

#### Specific Hazards arising from the chemical:

Special hazards arising from the substance or mixture

Battery may burst and release hazardous decomposition products when exposed to a fire situation.

Some may burn but none ignite readily. Containers may explode when heated. Some may be transported hot.

#### Specific protective actions for fire-fighters:

Protective equipment: Wear self-contained respirator. Wear fully protective impervious suit.

#### Section 6 - Accidental Release Measure

#### Personal precautions:

Wear protective equipment. Keep unprotected persons away. Ensure adequate ventilation

#### **Protective equipment:**

No data available.

#### **Emergency procedures:**

Remove ignition sources, evacuate area. Sweep up using a method that does not generate dust. Collect as much of the spilled material as possible, placed the spilled material into a suitable disposal container. Keep spilled material out of sewers, ditches and bodies of water.

#### **Environmental precautions:**

Do not allow material to be released to the environment without proper governmental permits.

#### Methods and materials for containment and cleaning up:

For all waste handing must refer to United Nations, National and Local Regulations for disposal.

See Section 7 for information on safe handling.

See Section 8 for information on persoanl protection equipment.

See Section 13 for disposall information.

#### Section 7 - Handling and Storage

#### Precautions for safe handling:

Avoid short circuiting the battery. Avoid mechanical damage of the battery. Do not open or disassemble. Batteries may explode or cause burns, if disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect polarity. Avoid all personal contact, including inhalation. Wear protective clothing when rish of exposure occurs. Use in a well-ventilated area. Prevent concentration in hollows and sumps.

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 5 of 10

#### Conditions for safe storage, including any incompatibilities:

Store in a cool, dry, well-ventilated place. Keep away from heat, avoiding the long time of sunlilgt.

#### Section 8 - Exposure Controls/Personal Protection

#### **Control Parameters**

CAS NO.	ACGIH	NIOSH	OSHA
12054-48-7	N/A	N/A	N/A
12604-68-1	N/A	N/A	N/A
1307-96-6	TLV-TWA 0.02mg/m <sup>3</sup>	N/A	N/A
9000-11-7	N/A	N/A	N/A
9002-84-0	N/A	N/A	N/A
7782-42-5	TLV-TWA 2mg/m³	REL-TWA 2.5mg/m³	PEL-TWA 15mppcf PEL-TWA 20mppcf

#### Appropriate engineering controls:

The usual precautionary measures for handling chemicals should be followed.

Keep away from foodstuffs, beverages and feed.

Remove all soiled and contaminated clothing immediately.

Wash hands before breaks and at the end of work.

#### **Personal Protective Equipment:**

**Respiratory protection:** Wear shuitable protective mask. For a large large number of battery leakages, wear chemical protective clothing, including self-contained breathing apparatus.

Hand Protection: Wear appropriate protective gloves to reduce skin contact.

**Eye Protection:** Wear safety goggles or eye protection combined with respiratory protection.

**Skin and Body Protection:** Wroking environment required, wear suitable protective clothing to minimize contact with skin. The type of protective equipment must be according to the concentration and the content of certain hazardous substances in the workplace.

#### Section 9 - Physical and Chemical Properties

#### Information on basic physical and chemical properties

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 6 of 10

Colour: White. **Physical State:** Cylindrical. Not available. Odour: pH: Not available. Not available. Melting point/freezing point: Boiling point or initial boiling point and boiling range: Not available. Flash Point: Not available Not available. Flammability: Solubility: Not available. Lower and upper explosion limit/flammability limit: Not available. Not available. Auto-ignition temperature: **Decomposition temperature:** Not available. **Kinematic viscosity:** Not available. Partition coefficient: n-octanol/water (log value): Not available. Not available. Vapour pressure: Not available. Density and/or releative density: Relative vapour density: Not available. Particle characteristics: Not available.

Other information:

Voltage 2.4V
Electric capacity 700mAh
Electric Energy 1.68Wh

#### Section 10 - Stability and Reactivity

Reactivity: No data available.

Chemical stability: Stable.

Possibility of hazardous reactions: No data available.

Conditions to Avoid: Flames, sparks, and other sources of ignition, incompatible materials.

Incompatible materials: Oxidizing agents, acid base.

Hazardous decomposition products: Carbon monoxide, carbon dioxide.

#### Section 11 - Toxicological Information

**Acute Toxicity:** 

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 7 of 10

CAS NO.	LC50/LD50
12054-48-7	LD50 Rat (oral): 1600mg/kg LC50 Rat (Inhalation: Dusts and mists): 1200mg/m³
12604-68-1	No data available.
1307-96-6	LD50 Rat (oral): 202mg/kg
9000-11-7	No data available.
9002-84-0	No data available.
7782-42-5	No data available.

Skin corrosion/irritation: No data available.

Serious eye damage/irritation: No data available.
Respiratory or Skin sensitization: No data available.

Germ Cell mutagenicity: No data available.

Carcinogenicity: No data available.

Reproductive toxicity: No data available.

Specific target organ toxicity-Single exposure: No data available.

Specific target organ toxicity-Repeated exposure: No data available.

Aspiration hazard: No data available.

Information on the likely routes of exposure: No data available.

Eye: No data available. Skin: No data available.

**Ingestion:** No data available. **Inhalation:** No data available.

#### Section 12 - Ecological Information

Ecological Toxicity:No data available.Persistence and degradability:No data available.Bloaccumulative Potential:No data available.Mobility in Soil:No data available.Other adverse effects:No data available.

#### Section 13 - Disposal Considerations

#### **Disposal methods:**

#### **Recommendation:**

Consult state, local or national regulations to ensure proper disposal.

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 8 of 10

#### **Uncleaned packaging**

**Recommendation:** Disposal must be made according to official regulations.

#### Section 14 - Transport Information

UN or ID Number			
IATA, IMDG,Model Regulation	N/A		
Proper Shipping Name/Description			
IATA, IMDG,Model Regulation	N/A		
Class or Div. (Sub Hazard)			
IATA, IMDG,Model Regulation	Not Subjected for transport of dangerous goods		
Packing Group			
IATA, IMDG,Model Regulation	N/A		
Hazard Label			
IATA, IMDG,Model Regulation	N/A		
Environmental hazards			
Marine pollutant:	No		
Special precautions for user	No information available.		

**Transport information: NI-MH Battery 2\*AAA is exempt from Dangerous goods. It is** considered non-dangerous goods by the International Civil Aviation Organization (ICAO), the International Air Transport Association (IATA) DGR 63<sup>rd</sup>, IATA Special Provisions A199, International Martine Dangerous Goods Regulations (IMDG) (40-20), IMDG Special Provisions 963, or the <<Recommendations on the Transport of Dangerous Goods Model Regulations>>(22<sup>nd</sup>).

- **S.P.A199** The UN number 3496 is only applicable in sea transport. Nickel-metal hydride batteries or nickel-metal hydride battery-powered devices, equipment or vehicles having the potential of a dangerous evolution of heat are not subject to these Regulations provided they are prepared for transport so as to prevent:
- (a) a short-circuit (e.g. in the case of batteries, by the effective insulation of exposed terminals; or, in the case of equipment, by disconnection of the battery and protection of exposed terminals); and (b) unintentional activation.

The words "Not Restricted" and the Special Provision number must be included in the description of the substance on the Air Waybill as required by 8.2.6, when an Air Waybill is issued.

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 9 of 10

Separate batteries when shipping to prevent short-circuiting. They should be packed in strong packaging for support during transport.

Note: A total quantity less than 100kg gross mass in a cargo transport unit. (By sea).

#### Section 15 - Regulatory Information

#### Safety, health and environmental regulations/legislation specific for the substance or mixture

CAS No.	TSCA	IECSC	DSL/NDSL	EINECS/ELINCS/NLP
12054-48-7	Listed	Listed	Listed DSL	Listed
12604-68-1	Listed	Listed	Listed DSL	Listed
1307-96-6	Listed	Listed	Listed DSL	Listed
9000-11-7	Listed	Listed	Listed DSL	Listed
9002-84-0	Listed	Listed	Listed DSL	Listed
7782-42-5	Listed	Listed	Listed DSL	Listed

#### Section 16 - Other Information

Issue Date: 2023-01-10

Issue Department: Technical department

Modification record:

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Other Information:

CAS: (Chemical Abstracts Service);

EC: (European Commission);

ACGIH:: (American Conference of Governmental Industrial Hygienists);

NIOSH: (US National Institute for Occupational Safety and Health);

OSHA: (US Occupational Safety and Health);

TLV: (Threshold Limit Value);

TWA: (Time Weighted Average);

Report No.: MPIJTRYL872437V2 Date:2023-01-10 Page 10 of 10

STEL: (Short Term Exposure Limit);

PEL: (Permissible Exposure Level);

REL: (Recommended Exposure Limit);

PC-STEL: (Permissible concentration-short time exposure limit);

PC-TWA: (Permissible concentration-time weighted average);

IARC: (International Agency for Research on Cancer);

LC50: (Lethal concentration, 50 percent kill);

LD50: (Lethal dose, 50 percent kill);

EC50: (Median effective concentration);

BCF: (Bioconcentration Factor);

BOD: (Biochemical oxygen demand);

IECSC: (Inventory of Existing Chemical Substances in China);

NOEC: (No observed effect concentration);

NTP: (US National Toxicology Program);

RTECS: (Registry of Toxic Effects of Chemical Substances);

TOC: (Total Organic Carbon);

TSCA: (Toxic Substances Control Act of USA);

DSL: (the Domestic Substances List of Canada);

NDSL: (the Non-domestic Substances List of Canada);

IATA: (International Air Transport Association);

IMDG: (International Maritime Dangerous Goods);

TDG: (Recommendations on the TRANSPORT OF DANGEROUS GOODS Model Regulations);

\*\*\*End of Report\*\*\*