


		Conditions	
cell type:		NiMH	
cell size:		AA	
nominal voltage:	1.2	V	
max. charge voltage:	1.5	V	at standard charge (0.1C / 20°C)
capacity			
nominal:	1300	mAh	discharge at 0.2C
minimum:	1300	mAh	discharge at 0.2C
	1200	mAh	discharge at 1C
			1.0V end discharge voltage
			ta: 20°C
max. continuous discharge current:	3900	mA	ta: 0...45°C
charge			
standard charge:	130	mA	14....16hrs
quick charge:	390	mA	4hrs
fast charge:	1300	mA	1.1hrs
recommended charge termination control parameters:	0...5	mV	- ΔV (-deltaV)
	0.8...1	°C	temperature rise per minute
	45...50	°C	TCO (temperature cut off)
trickle charge current:	10...30	mA	(recommended)
continuous overcharge: (less than 1 year)	≤ 130	mA	no conspicuous deformation no leakage
internal resistance: (impedance)	≤ 45	mΩ	at 1KHz battery fully charged
life expectancy:	≥ 500	cycles	acc. IEC standard
self discharge			
charge retention:	≥ 80	%	after 12 months storage at 20°C
initial capacity:	≥ 900	mAh	within 30 days after delivery discharge at 0.2C
ambient temperature range:	0...45	°C	standard charge
	10...40	°C	fast charge
	0...45	°C	discharge (≥1C)
	- 20...65	°C	discharge (<1C)
	- 20...50	°C	storage (≤3months)
	- 20...40	°C	storage (≤6months)
	- 20...30	°C	storage (≤24months)
QCT1:	20/1250/45		
QCT2:	30/1150/50		

mechanical specifications


cell dimensions

diameter d1:		14.3 - 0.7	mm
diameter d2:	max.	5.5	mm
height h1:		50.4 - 0.5	mm
height h2:	min.	1.2	mm
weight:		23 ± 2	g
blister card dimensions:		123 x 85	mm
blister card weight (incl. batteries):		100	g




Diagrams


standard charge




fast charge



low rate discharge



high rate discharge



ANSMANN Specifications for model:

data sheet no. / part no.

supplier no.

author / date

**AA - 1300mAh low self discharge
4pcs blister package**

5030792

702069

TG / 02.03.2018