



Nominal Voltage:	1.5 V
Nominal Internal Impedance:	420 m-ohm @ 1kHz
Average Weight:	9.0 gm (0.3 oz.)
Volume:	3.4 cm ³ (0.21 in. ³)
Terminals:	Flat
Operating Temperature Range:	-20°C to 54°C (-4°F to 130°F)
NEDA/ANSI:	910A
IEC:	LR1

Typical Discharge Characteristics at 21°C (70°F)




* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.


Typical Discharge Characteristics




Typical Discharge Characteristics



Typical Discharge Characteristics



Typical Discharge Characteristics



DURACELL®

BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.