


QOMO QIT30 RF Wireless Tablet


Operating Systems:

**Microsoft Windows 2000/XP/Vista
Mac OS X 10.2.8 above**



- Unique integrated rechargeable lithium polymer battery provides up to 25 hours of continuous cable free operation
 - Quick & easy installation, plug-in-play in VISTA (In Windows 2000/XP, tablet driver required)
 - Supports multiple pairing of up to 30 devices
 - Easily recharge battery through your computer via USB cable
 - USB dongle stores at the rear of the tablet
 - 16 programmable macro keys for file linking and function setting
 - Built-in LCD indicator panel
 - Intuitive express keys controls Page Up/Down & adjusts volume
 - Flow! Software allows integration with document cameras and firewire applications
 - Energy saving stylus automatically turns on/off
 - Export notes & annotations into various file formats, including ppt, pdf, jpeg and html for immediate posting to your website
 - A5 high resolution working area 8"x 6" provides plenty of room for writing and annotating
- Pen slot for storage and easy access





QOMO's revolutionary 2.4G wireless solution uses RF technology to allow you to connect with more people for greater interaction! It's sleek, modern design allows you to draw, annotate, edit images and manipulate computer applications without being tethered to a desk or computer. It's a wireless solution that enhances creativity and introduces participants to a new dynamic presentation. Using a single computer a presenter can connect up to 30 wireless tablets at one time to annotate over existing documents and pictures. Because of QOMO's interactive Flow! software, now you and your participants can annotate over captured video files as well as live motion video!

Solution	Wireless 2.4G RF
Resolution	2000lpi
Report Rate	120 rps
Pen Pressure	1024 Levels
Macro Key	16(Top of Active Area)
Hot Key	Page up / Page down, Volume Control
LCD Type	TN LCD
LCD Size	0.7" x 1.63"(17.8mm x 41.4mm)
LCD Icon Content	Battery Status/Connection Mode/Connection Power Status/Volume Adjustment Indicator/Channel Indicator
Feature	Multiple Pairing (1-30 or more)
Battery Type	Nokia BL5C Li-ion Rechargeable Battery
Battery Capacity	850Ma
Battery Life	25 hours
Power Source	USB Charged / USB Plus Adaptor Charged
Pen Require	M3A-020 5V
Power Button	Electrical Power Button
Power Consumption	Max 50 Ma (Operation Mode)
Receiver Dongle	slim type (It can be stored into Tablet)
Operating System	Microsoft Windows 2000/XP/Vista, Mac OS X 10.2.8 above
Active Area	7.8" x 5.9" (19.8cm x 15.0cm)
Size	10.9" x 11.1" x 0.8" (27.7cm x 28.2cm x 2cm)
Weight (including the Battery)	1.22lbs(553.4g)

* Design and specifications are subject to change without notice.



www.qomo.com

QOMO HiteVision, LLC
Toll Free: (866) 990-QOMO
Email: info@qomo.com

Copyright ©2008 QOMO HiteVision, LLC. All rights reserved. This document may not be copied in any form without written permission from QOMO HiteVision, LLC. Information in this document subject to change without notice.