


REV.	SPECIFICATION	ECN NO.	APPD.



Material:
Housing: Thermoplastic Ployester Glass Filled UL94V-0.
Contacts: Copper Alloy.
Cable: 0.635mm(0.025") Pitch flat cable.

Electrical Characteristics:
Current Rating: 1 AMP.
Dielectric Withstanding Voltage: AC 500V For 1 mintue.
Insulator Resistance: 500MΩ min. at DC 500V.
Contact Resistance: 30mΩ max.
Operating Temperature: -40°C ~ +85°C.

***RoHS Compliant**

Position	Dimension		
	A	B	C
10	11.25	8.35	5.08
14	13.79	10.89	7.62
16	15.06	12.16	8.89
20	17.60	14.70	11.43
22	18.87	15.97	12.70
26	21.41	18.51	15.24
30	23.95	21.05	17.78
34	26.49	23.59	20.32
40	30.30	27.40	24.13
44	32.84	29.94	26.67
50	36.65	33.75	30.48
60	43.00	40.10	36.83
68	48.08	45.18	41.91
80	55.70	52.80	49.53
100	68.40	65.50	62.23

1203-A xx C 00 B 1 A
Series Position C: Selective 00: G/F B: Black 1: With Strain Relief A: Tray
Gold Plated 10: 10 μ" 15: 15 μ" 2: Without Strain Relief Package
30: 30 μ"

Tolerances	Dwg. No.	1203D01001	Title:		 OUPIIN ELECTRONIC(KUNSHAN) CO., LTD. P/N: 1203-AxxC00B1A SHEET 1/1 Ver.No. A2
x = ±0.5	Projection		1203-A Series		
.x = ±0.30	Unit	mm	Scale	1:1	
.xx = ±0.20	Drawn By	Peggy06/04'14	I.D.C Socket 1.27mmX2.54mm		
① 718					