



SECTION A-A

- NOTES:
- 1. Rating: 300V 15A(IEC 250V 12A)
PITCH: 5.00mm
 - 2. Insulation Withstands Voltage:
AC 1500 V/MIN
 - 3. Insulation Resistance:
500MΩ or more at DC500V
 - 4. Using Temperature Range:
-40°C~+105°C
 - 5. Screw Torque Value: 5 kg-cm
 - 6. Suitable Electric Wire:
AWG 28~12(IEC 4.0~5.6mm)
~~24~12(IEC 2.5mm²)~~
 - 7. Undimensioned Tolerances:

—	∩	∇	0.05/10
⊥	//	≡	0.2/10
PITCH ERROR			0.05/10
UNDIMENSIONED TOLERANCES			±0.3

P	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
U	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00	70.00	75.00
V	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00	70.00	75.00	80.00
P	17	18	19	20	21	22	23	24	25						
U	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00	120.00						
V	85.00	90.00	95.00	100.00	105.00	110.00	115.00	120.00	125.00						
Tolerances for PITCH ERROR															

工程變更處

5	SCREW	S000003400	P	STEEL	M2.5 Zinc Plated
4	WIRE CAGE	X000000800	P	STEEL	Zinc Plated
3	CLAMP	0120B00400	P	PHOSPHOR BRONZE	Solder Plated
2	COVER	0120L00000	1	PA66(V0)	GREEN
1	HOUSING	0120A00000	1	PA66(V0)	GREEN
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
DWG.	ZHENG	DATE	98.11.20	UNITS	MM
CHK.		DATE		SCALE	4:1 (:)
APP.		DATE			
				NAME	20.950M
				DWG NO.	SP-02

3	工程變更1處	梁紅英	01.04.04
2	圖面修	梁紅英	99.11.17
REV.	正	CONTENT	CHK. DATE

