

# 221 Seires Compact Lever Connectors

## Mounted in Abox 060 enclosure



### Suitable applications:-

- Ideal for lighting and power
- IP65 rating enclosure (glands sold separately)
- Damp areas
- Agricultural and garden locations

### 221-413 Benefits:-

- CAGE CLAMP® connection, re-usable
- 0.2 - 4mm<sup>2</sup> solid & stranded conductors
- 0.14 - 4mm<sup>2</sup> fine-stranded conductors
- Rating of 32A & 450V

### Material

Polystyrene Abox

### Part No


60290788

### Abox Dimensions (mm)


110 x 110 x 67 (WxLxH)

### Includes


- IP65 Abox with cable entry holes (shown in diagram to the right)
- Mounting bracket for the 221 Series connectors
- IP54 adapters / M25 blanking plug / fixing covers
- 5 x 221-413




### Operating:-



1. Strip the conductor  
11mm.



2. Open clamping unit  
using the lever and  
insert the  
conductor.



3. Lower the lever to  
close the clamp  
to complete the  
connection.

4. To remove, lift  
the lever and pull out  
the conductor.



Easy testing, test point  
on the back and front of  
the housing.