




These Open Former Differential Mode Suppression Chokes, are specifically designed to attenuate mains borne RF interference.

Constructed using a single wound ferrite ring mounted vertically onto a flame retardant plastic carrier.



PCB Drilling Detail



SPECIFICATION

Voltage Rating	250 VAC
Live Frequency	50 / 60Hz
Inductance Tolerance	± 20 %
Temperature Range	-25°C to +85°C
Temperature Rise @ Rated Current	30°C
Approvals	BS, EN, ISO 9001-2008

Part No	Amp	Inductance	D.C Resistance (mΩ)
DF1	1	1.17 mH	1470
DF2	2	0.5 mH	370
DF3	3	0.26 mH	140
DF4	4	0.21 mH	100
DF5	6	0.12 mH	40
DF6	8	0.085 mH	25