

Hand-Held and Remote

Order code	Manufacturer code	Description
30-1620	110-404	110X110X66 POLYSTYRENE ENCLOSURE
30-1720	120-404	110X110X66 POLYCARB.ENCLOSURE

Hand-Held and Remote	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

Polystyrene/Polycarbonate Enclosures

Specification

Rapid Order Code	Material Used
30-1620	Polystyrene
30-1720	Glass-fibre reinforced Polycarbonate

Parameter	Material Type	
	Polystyrene	Polycarbonate
Material Properties	Low Halogen Resistance to water, alcohol, weak acid.	Zero Halogen Resistance to water, alcohol, petrol, mineral oil, vegetable & animal fats, weak & strong acids
UV Resistance	-	Approved to UL 746 (sec.26)
Flammability	UL94V-2	UL94V-1
Continuous Working Temperature	+70°C	+115°C
Minimum Working Temperature	-40°C	-35°C
Maximum Working Temperature	+80°C	+130°C
Colour	Grey (RAL7035)	
Rating	IP66	

Technical Drawing

