


| Order code | Manufacturer code | Description |
|-------------------|--------------------------|-----------------------------------------|
| 33-1060 | n/a | RED 4.8X0.5MM INSULATED FEMALE PK100 RC |

| | |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|
| | Page 1 of 2 |
| The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E. | Revision A 20/02/2007 |

DESCRIPTION

Data Sheets For Standard Industrial Light Duty Terminals

QUALITY SYSTEM No:

DAV1850DRAWN BY: **M.TAMAN**SIGNED: *Alan*ISSUE DATE: **30-01-2001**DRAWING SCALE SIZE: **N/A**SHEET **8 of 12****FULLY INSULATED FEMALE PUSH-ON TERMINALS**

| | |
|---------------------|--------------------|
| Working Voltage | 600 V.Max AC or DC |
| Working Temperature | -40 To +85 Deg C |
| Basic Tolerance | ±0.5 mm |
| Insulation | Vinyl |

For Further Technical Specification
Refer To DAV 1069 Sheets 1 To 4

| Davico Part No. | NEMA Tab Size | B (mm) | C (mm) | D (mm) | F (mm) | L (mm) | W (mm) |
|-----------------|---------------|--------|--------|--------|--------|--------|--------|
| ERFPO 63F | 6.3 | 10.5 | 1.7 | 4.0 | 7.3 | 22.0 | 6.6 |
| EBFPO 63F | 6.3 | 10.5 | 2.3 | 4.5 | 7.3 | 22.0 | 6.6 |
| EYFPO 63F | 6.3 | 12.5 | 3.4 | 5.5 | 7.3 | 24.3 | 6.6 |
| ERFPO 48F | 4.8 | 10.5 | 1.7 | 3.8 | 6.4 | 20.5 | 5.0 |
| EBFPO 48F | 4.8 | 10.5 | 2.3 | 4.7 | 6.4 | 20.5 | 5.0 |

DAVICO

Keeping electricity firmly in its place.

Davico Industrial Limited, Charles Street, West Bromwich, West Midlands, B70 6AZ, U.K.
Tel: (0121) 520-7101/5040. Fax: (0121) 520-7775 (SALES) / (0121) 520-6035 (ENQUIRES)
E-Mail sales: sales@davico.co.uk Enquiries: enq@davico.co.uk
World Wide Web: <http://www.davico.co.uk>

| REV | DATE | SIG. |
|-----|------|------|
| 1 | | |
| 2 | | |
| 3 | | |