


A B C D E F G H

REV	DESCRIPTION	DATE
-----	-------------	------

△ RDK-98053

洗勝賢 2009/03/17



NOTE :

1. MAXIMUM ELECTRIC CURRENT : 

A.W.G.	22	20	18	16
AMP.	3	4	7	10
2. MAXIMUM ELECTRICAL RATING : 75°C 600 VOLTS MAX.
3. INSULATION MATERIAL : VINYL
4. INSULATION COLOR : RED
5. TERMINAL MATERIAL : BRASS
6. WIRE RANGE : 22-16 A.W.G. ( 0.5-1.5 mm<sup>2</sup> )
7. DOUBLE CRIMP : WITH COPPER SLEEVE ON BARREL
8. TERMINAL SURFACE TREATMENT : TIN PLATED
9. TERMINAL THICKNESS : 0.40 mm

Tolerance Unless Otherwise Specified	
0 > 6 mm ± 0.20	ANGLE
6 > 18 mm ± 0.30	0° > ° REF ±
18 > 30 mm ± 0.40	° > ° ±
30 > 75 mm ± 0.50	° > ° ±

NAME	VINYL-INSULATED DOUBLE CRIMP BULLET DISCONNECTORS				UNIT	mm	
PART NO.	MPD1-156	MATERIAL	-----	APPROVE			
NUMBER	KA-95152-C	SCALE	SHEET	PAGE	CHECKED		
DATE	2006/03/27	4/1	1-1	10F2	DRAWN	張馨尹	

**KST. K.S. TERMINALS INC.**

A B C D E F G H