

Safety data sheet

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Code: 5L-FERRIC & 25L-FERRIC FERRIC CHLORIDE

Product name FERRIC CHLORIDE 40%

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use Professional industrial use

1.3. Details of the supplier of the safety data sheet

FORTEX ENGINEERING LTD Name Full address **UNIT 16 FREEMAN ROAD**

LINCOLN, LINCOLNSHIRE LN6 9AP District and Country

UNITED KINGDOM Tel. +44 (0) 1522 718168

e-mail address of the competent person

responsible for the Safety Data Sheet sales@fortex.co.uk

1.4. Emergency telephone number

For urgent inquiries refer to +44 (0) 2476 374999 - 08:30 - 17: 00 Monday to Friday - or you

can call the nearest hospital showing the MSDS

SECTION 2. Hazards identification.

2.1. Classification of the substance or mixture.

The product is classified as hazardous pursuant to those provisions set forth in EC Regulation 1272/20 0(8CLP) (and subsequent amendments and supplements). The product thus requires a safety datasheet that complies with the provisions of EC Regulation 1907/2006 and subsequent amendments. Any additional information concerning the risks for health and/or the environment are given in sections 11 and 12 of this sheet.

2.1.1. Regulation 1272/2008 (CLP) and following amendments and adjustments.

Hazard classification and indication: Acute Tox. 4 H302 Skin Corr. 1B H314 Eye Dam. 1 H318 Aquatic Chronic 3 H412

2.1.2. 67/548/EEC and 1999/45/EC Directives and following amendments and adjustments.

Danger Symbols:

R phrases:

22-34-52/53

The full wording of the Risk (R) and hazard (H) phrases is given in section 16 of the sheet.



2.2. Label elements.

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms:





Signal words: Danger

Hazard statements:

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage. H412 Harmful to aquatic life with long lasting effects.

Precautionary statements:

P264 Wash thoroughly with soap and water after use.

P273 Avoid release to the environment.

P280 Wear protective gloves / protective clothing / eye protection / face protection. P301+P312 IF SWALLOWED: Call a POISON CENTER or doctor / physician if you feel unwell.

P304+P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

Contains: FERRIC CHLORIDE, SOLUTION

2.3. Other hazards.

Information not available.

SECTION 3. Composition/information on ingredients.

3.1. Substances.

Information not relevant.

3.2. Mixtures.

Contains:

Classification 67/548/EEC. Classification 1272/2008 (CLP). Identification. Conc. %.

FERRIC CHLORIDE, SOLUTION

R52/53, C R34, Xn R22 Acute Tox. 4 H302, Skin Corr. 1B H314, Aquatic Chronic 3 H412 CAS. 7705-08-0 30 - 50

EC. 231-729-4 INDEX. -

Reg. no. 01-2119497998-05



Note: Upper limit is not included into the range.

The full wording of the Risk (R) and hazard (H) phrases is given in section 16 of the sheet. T+ = Very Toxic(T+), T = Toxic(T), Xn = Harmful(Xn+) Corrosive(C), Xi = Irritant(Xi), O = Oxig(Xi), E = Explosive(E), F+ = Extremely Flammable(F+), F = Highly Flammable(<math>F), N = Dangerous for the Environment(N)

SECTION 4. First aid measures.

4.1. Description of first aid measures.

EYES: Remove contact lenses, if present. Wash immitedly with plenty of water for at least 30-60 miles, opening the eyelids fully. Get medical

SKIN: Remove contaminated clothing. Rinse skin with a shower immediately. Get medical advice/attention.

INGESTION: Have the subject drink as much water aspossible. Get medical advice/attention. Do not induce vomiting unless explicitly authorised by a

INHALATION: Get medical advice/attention immediated Remove victim to fresh air, away from the accitibecene. If the subject stops breathing, administer artificial respiration. Take suitable precautions for rescue workers.

4.2. Most important symptoms and effects, both acute and delayed.

For symptoms and effects caused by the contained substances, see chap. 11.

4.3. Indication of any immediate medical attention and special treatment needed.

Information not available.

SECTION 5. Firefighting measures.

5.1. Extinguishing media.

SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray. UNSUITABLE EXTINGUISHING EQUIPMENT None in particular.

5.2. Special hazards arising from the substance or mixture.

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE Do not breathe combustion products.

5.3. Advice for firefighters.

GENERAL INFORMATION

Use jets of water to cool the containers to preventproduct decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewerystem. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures.



6.1. Personal precautions, protective equipment and emergency procedures.

Block the leakage if there is no hazard.

Wear suitable protective equipment (including persal protective equipment referred to under Section of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions.

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up.

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Check compactibility for container material in section 7.00 taminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections.

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage.

7.1. Precautions for safe handling.

Before handling the product, consult all the othersections of this material safety data sheet. Avoideakage of the product into the environment. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat.

7.2. Conditions for safe storage, including any incompatibilities.

Store only in the original container. Store the cotainers sealed, in a well ventilated place, away ofm direct sunlight. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s).

Information not available.

SECTION 8. Exposure controls/personal protection.

8.1. Control parameters.

Regulatory References:

United Kingdom EH40/2005 Workplace exposure limits. Containing the list of workplace exposure

limits for use with the Control of Substances Hazardous to Health Regulations (as

amended).

Éire Code of Practice Chemical Agent Regulations 2011.

OEL EU Directive 2009/161/EU; Directive 2006/15/EC; Directive 2004/37/EC; Directive

2000/39/EC.

TLV-ACGIH ACGIH 2012



FERRIC CHLORIDE, SOLU	TION							
Threshold Limit Value.								
Туре	Country	TWA/8h		STEL/15min				
		mg/m3	ppm	mg/m3	ppm			
TLV-ACGIH		1						
Predicted no-effect concentration	n - PNEC.							
Normal value for the terrestrial compartment Normal value for fresh water sediment Normal value for marine water sediment Normal value of STP microorganisms				55,5 49,5 49,5 500		mg/kg mg/kg mg/kg mg/L		
Health - Derived no-effect	Effects on consumers.	OMEL			Effects on workers			
Route of exposure	Acute local	Acute systemic	Chronic local	Chronic systemic	Acute local	Acute systemic	Chronic local	Chronic systemic
Oral.			VND	0,29 mg/kg		•		•
Inhalation.			VND	0,5 mg/m ³			VND	2,01 mg/m ³
Skin.			VND	0,29 mg/kg				

Legend:

(C) = CEILING; INHAL = Inhalable Fraction; RESP = Respirable Fraction; THORA = Thoracic Fraction.

VND = hazard identified but no DNEL/PNEC available ; NEA = no exposure expected ; NPI = no hazard identified.

8.2. Exposure controls.

As the use of adequate technical equipment must always take priority over personal protective equipment make sure that the workplace is well aired through effective local aspiration.

When choosing personal protective equipment, ask your chemical substance supplier for advice.

Personal protective equipment must be CE marked, showing that it complies with applicable standards.

Provide an emergency shower with face and eye wash station.

HAND PROTECTION

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

SKIN PROTECTION

Wear category II professional long-sleeved overalls and safety footwear (see Directive 89/686/EEC and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

In the presence of risks of exposure to splashes orsquirts during work, adequate mouth, nose and eyeprotection should be used to prevent accidental

RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded f the substance or one of the substances present ithe product, use a mask with a type B filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 4387). In the presence of gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if thechnical measures adopted are not suitable for resicting the worker's exposure to the threshold



values considered. The protection provided by masks is in any case limited.

If the substance considered is odourless or its outcome threshold is higher than the corresponding IIV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (incompliance with standard EN 137) or external aintake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

Product residues must not be indiscriminately disposed of with waste water or by dumping in waterways.

SECTION 9. Physical and chemical properties.

9.1. Information on basic physical and chemical properties.

Appearance Colour brown Odour characteristic Odour threshold. Not available. acidic Melting point / freezing point. -10°C 280 ℃. Initial boiling point. Not available. > 60 ℃. Boiling range. Flash point. Evaporation Rate Not available. Flammability of solids and gases Not available. Lower inflammability limit. Not available. Upper inflammability limit. Not available. Lower explosive limit. Not available. Upper explosive limit. Not available. Vapour pressure. Not available. Vapour density Not available. Not available. Relative density. Solubility soluble in water Partition coefficient: n-octanol/water Not available. Auto-ignition temperature. Not available. Decomposition temperature. Not available. Viscosity Not available. Explosive properties Not available. Oxidising properties Not available.

9.2. Other information.

Information not available

SECTION 10. Stability and reactivity.

10.1. Reactivity.

There are no particular risks of reaction with other substances in normal conditions of use.

FERRIC CHLORIDE, SOLUTION: decomposes above 160℃.

10.2. Chemical stability.

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions.



No hazardous reactions are foreseeable in normal conditions of use and storage.

FERRIC CHLORIDE, SOLUTION: can react dangerously with water, strong bases, akaline metals, allyle chloride, ethylene oxide.

10.4. Conditions to avoid.

None in particular. However the usual precautions used for chemical products should be respected.

10.5. Incompatible materials.

Information not available.

10.6. Hazardous decomposition products.

FERRIC CHLORIDE, SOLUTION: hydrochloric acid.

SECTION 11. Toxicological information.

11.1. Information on toxicological effects.

In the absence of experimental data for the productitself, health hazards are evaluated according tothe properties of the substances it contains, using the criteria specified in the applicable regulation classification. It is therefore necessary token into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

Acute effects: ingestion of this product is harmful Even small amounts of product may cause serious health problems (stomach pain, nausea, sickness, diarrhoea).

This product is corrosive and causes serious burnsand vesicles on the skin, which can arise even afte exposure. Burns are very stinging and painful. Upon contact with eyes, it may cause serious harm, such as cornea opacity, iris lesions, irreversibleeye coloration. Possible vapours are caustic for the respiratory system and may cause pulmonary edema, whose symptoms sometimes arise only after some hours.

Exposure symptoms may include: sting, cough, asthma, laryngitis, respiratory disorders, headache, nausea and sickness.

If swallowed, it may cause mouth, throat and oesophagus burns, sickness, diarrhoea, edema, larynx swelling and, consequently, asphyxia. Perforation of the gastro-intestinal tract is also possible.

This product may cause serious ocular lesions, cornea opacity, iris lesions, irreversible eye coloration.

Acute effects: stinging eyes. Symptoms may include: rubescence, edema, pain and lachrymation.

Vapour inhalation may moderately irritate the upper respiratory trait. Contact with skin may cause slight irritation.

Ingestion may cause health problems, including stomach pain and sting, nausea and sickness.

FERRIC CHLORIDE, SOLUTION LD50 (Oral). 500 mg/kg Rat

SECTION 12. Ecological information.

This product is dangerous for the environment and the aquatic organisms. In the long term, it have negative effects on aquatic environment.

12.1. Toxicity.

Information not available.

12.2. Persistence and degradability.

Information not available.



12.3. Bioaccumulative potential.

Information not available.

12.4. Mobility in soil.

Information not available.

12.5. Results of PBT and vPvB assessment.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects.

Information not available.

SECTION 13. Disposal considerations.

13.1. Waste treatment methods.

Reuse, when possible. Product residues should be assidered special hazardous waste. The hazard levebf waste containing this product should be evaluated according to applicable regulations.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

Avoid littering. Do not contaminate soil, sewers and waterways.

Waste transportation may be subject to ADR restrictions.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information.

These goods must be transported by vehicles authorized to the carriage of dangerous goods according to the provisions set out in the current edition of the Code of International Carriage of Dangerous Gods by Road (ADR) and in all the applicable national egulations. These goods must be packed in their original packagings or in packagings made of materials resistant to their content and not reacting dangerously with it. People loading and unloading dangerous goods must be trained on all the risks deriving from these substances and on all actions that must be taken in case of emergency situations.

Road and	d rail transport: ADR/RID Class:	8	UN:	2582		
47	Packing Group:	III				
	Label:	8				
	Nr. Kemler:	80				
	Limited Quantity.	5 L				
	Tunnel restriction code.	(E)				
	Proper Shipping Name:	FERRIC CHLORIDE S	SOLUTION			
Carriage	by sea (shipping): IMO Class:	8	UN:	2582		
	Packing Group:	III				



Label: EMS: F-A, S-B Marine Pollutant. NO Proper Shipping Name: FERRIC CHLORIDE SOLUTION Transport by air: UN: 2582 IATA: 8 Packing Group: Ш Label: 8 Cargo: Packaging instructions: 856 Maximum quantity: 60 L Pass.: Packaging instructions: 852 Maximum quantity: 5 L Special Instructions: A3, A803 Proper Shipping Name: FERRIC CHLORIDE SOLUTION **SECTION 15. Regulatory information.** 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture. Seveso category. None. Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006. Product. Point. 3 Substances in Candidate List (Art. 59 REACH). None. Substances subject to authorisarion (Annex XIV REACH). None. Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012: None. Substances subject to the Rotterdam Convention:

Substances subject to the Stockholm Convention:

None.

None.



Healthcare controls.

Workers exposed to this chemical agent must not undergo health checks, provided that available risk-assessment data prove that the risks related to the workers' health and safety are modest and that the 98/24/EC directive is respected.

15.2. Chemical safety assessment.

No chemical safety assessment has been processed for the mixture and the substances it contains.

SECTION 16. Other information.

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

Acute Tox. 4 Acute toxicity, category 4 Skin Corr. 1B Skin corrosion, category 1B

Aquatic Chronic 3 Hazardous to the aquatic environment, chronic toxicity, category 3

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage. H412 Harmful to aquatic life with long lasting effects.

Text of risk (R) phrases mentioned in section 2-3 of the sheet:

R22 HARMFUL IF SWALLOWED.

R34 CAUSES BURNS

R52/53 HARMFUL TO AQUATIC ORGANISMS, MAY CAUSE LONG-TERM ADVERSE

EFFECTS IN THE AQUATIC ENVIRONMENT.

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
 CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
 IATA DGR: International Air Transport AssociationDangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
 PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.



- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

- 1. Directive 1999/45/EC and following amendments
- Directive 67/548/EEC and following amendments and adjustments
 Regulation (EC) 1907/2006 (REACH) of the European Parliament
- 4. Regulation (EC) 1272/2008 (CLP) of the European Parliament
- 5. Regulation (EC) 790/2009 (I Atp. CLP) of the European Parliament

- Regulation (EC) 453/2010 of the European Parliament
 Regulation (EC) 286/2011 (II Atp. CLP) of the European Parliament
 Regulation (EC) 618/2012 (III Atp. CLP) of the European Parliament
- 9. The Merck Index. 10th Edition
- Handling Chemical Safety
 Niosh Registry of Toxic Effects of Chemical Substances
 INRS Fiche Toxicologique (toxicological sheet)
- 13. Patty Industrial Hygiene and Toxicology
- 14. N.I. Sax Dangerous properties of Industrial Materials-7, 1989 Edition
- 15. ECHA website

Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the lastersion. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.