



Multipole Connectors - Revos Basic METRIC

The industrial standard, heavy duty, 500V, 16A













| | Socket Insert Pl | ug Insert | Narrow Entr | y Hood | Top Entr | y Hood | Narrow Entry with Locking | | Top Entry with Locking | • |
|-------------|------------------|---------------|---------------|--------|---------------|--------|------------------------------|-------|---------------------------|-------|
| Description | Part No. | Part No. | Part No. | Gland | Part No. | Gland | Part No. | Gland | Part No. | Gland |
| 10 POLE | 70.300.1040.0 | 70.310.1040.0 | 70.350.1035.0 | M20 | 70.352.1035.0 | M20 | 70.355.1035.0 | M20 | 70.357.1035.0 | M20 |
| 16 POLE | 70.300.1640.0 | 70.310.1640.0 | 70.350.1635.0 | M25 | 70.352.1635.0 | M25 | 70.355.1635.0 | M25 | 70.357.1635.0 | M25 |
| 24 POLE | 70.300.2440.0 | 70.310.2440.0 | 70.350.2435.0 | M25 | 70.352.2435.0 | M25 | 70.355.2435.0 | M25 | 70.357.2435.0 | M25 |
| 32 POLE | 70.300.3253.0 | 70.310.3253.0 | 70.350.3235.0 | M32 | 70.352.3235.0 | M32 | - | - | - | - |













| | Socket Insert | Plug Insert | Open Entry Base | Double Entr | ry Base | With Protective Cover | Double Ent with Protectiv | |
|-------------|---------------|---------------|-----------------|---------------|---------|-----------------------|------------------------------|-------|
| Description | Part No. | Part No. | Part No. | Part No. | Gland | Part No. | Part No. | Gland |
| 10 POLE | 70.300.1040.0 | 70.310.1040.0 | 70.320.1028.0 | 70.330.1035.0 | M20 | 70.325.1028.0 | 70.340.1035.0 | M20 |
| 16 POLE | 70.300.1640.0 | 70.310.1640.0 | 70.320.1628.0 | 70.330.1635.0 | M25 | 70.325.1628.0 | 70.340.1635.0 | M25 |
| 24 POLE | 70.300.2440.0 | 70.310.2440.0 | 70.320.2428.0 | 70.330.2435.0 | M25 | 70.325.2428.0 | 70.340.2435.0 | M25 |
| 32 POLE | 70.300.3253.0 | 70.310.3253.0 | *70.320.3228.0 | - | - | - | - | _ |

^{*} Contrary to picture, these bases have metal levers, more metal lever versions available on page 91.













| | Socket Insert | Plug Insert | Narrow Entr | y Hood | Top Entr | y Hood | Single Ent | ry Base | with Protective | |
|-------------|---------------|---------------|---------------|--------|---------------|--------|---------------|---------|-----------------|-------|
| Description | Part No. | Part No. | Part No. | Gland | Part No. | Gland | Part No. | Gland | Part No. | Gland |
| 6 POLE | 70.300.0640.0 | 70.310.0640.0 | 70.350.0635.0 | M20 | 70.352.0635.0 | M20 | - | - | - | - |
| 48 POLE | 70.300.4840.0 | 70.310.4840.0 | 70.350.4835.0 | M32 | 70.352.4835.0 | M32 | 70.331.4835.0 | M32 | 70.344.4835.1 | M40 |













| | Socket Insert | Plug Insert | Open Entry Base | Double Entr | y Base | Open Entry Base with Protective Cover | Double Ent with Protective | |
|-------------|---------------|---------------|-----------------|---------------|--------|---------------------------------------|-------------------------------|-------|
| Description | Part No. | Part No. | Part No. | Part No. | Gland | Part No. | Part No. | Gland |
| 6 POLE | 70.300.0640.0 | 70.310.0640.0 | 70.320.0628.0 | 70.330.0635.0 | M20 | 70.325.0628.0 | 70.340.0635.0 | M20 |
| 48 POLE | 70.300.4840.0 | 70.310.4840.0 | *70.320.4828.0 | - | - | *70.325.4828.0 | - | - |

Note: PG and Metric thread Sizes

Worldwide the use of PG threads are being changed over to Metric thread sizes. Because of pre-existing demand, we need to supply in both styles of PG and Metric. Please select Metric thread multipoles wherever possible as PG threads will be phased out.





Multipole Connectors - Revos Basic PG

The industrial standard, heavy duty, 500V, 16A













| | | | | | | | INGITOW ETTE | y 1100u | TOP ETIT | y 1100u |
|-------------|---------------|---------------|---------------|--------|---------------|--------|---------------|---------|---------------|---------|
| | Socket Insert | Plug Insert | Narrow Entr | y Hood | Top Entr | y Hood | with Locking | Levers | with Locking | Levers |
| Description | Part No. | Part No. | Part No. | Gland | Part No. | Gland | Part No. | Gland | Part No. | Gland |
| 10 POLE | 70.300.1040.0 | 70.310.1040.0 | 70.350.1028.0 | PG16 | 70.352.1028.0 | PG16 | 70.355.1028.0 | PG16 | 70.357.1028.0 | PG16 |
| 16 POLE | 70.300.1640.0 | 70.310.1640.0 | 70.350.1628.0 | PG21 | 70.352.1628.0 | PG21 | 70.355.1628.0 | PG21 | 70.357.1628.0 | PG21 |
| 24 POLE | 70.300.2440.0 | 70.310.2440.0 | 70.350.2428.0 | PG21 | 70.352.2428.0 | PG29 | 70.355.2428.0 | PG21 | 70.357.2428.0 | PG29 |
| 32 POLE | 70.300.3253.0 | 70.310.3253.0 | 70.350.3228.0 | PG29 | 70.352.3228.0 | PG29 | - | - | - | - |













| | | | | | | Open Entry base | Double Elli | пу вазе |
|-------------|---------------|---------------|------------------------|---------------|--------|-----------------------|----------------|---------|
| | Socket Insert | Plug Insert | Open Entry Base | Double Entr | y Base | with Protective Cover | with Protectiv | e Cover |
| Description | Part No. | Part No. | Part No. | Part No. | Gland | Part No. | Part No. | Gland |
| 10 POLE | 70.300.1040.0 | 70.310.1040.0 | 99.513.0000.6 | 70.330.1028.0 | PG16 | 70.325.1028.0 | 70.340.1028.0 | PG16 |
| 16 POLE | 70.300.1640.0 | 70.310.1640.0 | 99.502.0000.6 | 70.330.1628.0 | PG21 | 70.325.1628.0 | 70.340.1628.0 | PG21 |
| 24 POLE | 70.300.2440.0 | 70.310.2440.0 | 99.531.0000.6 | 70.330.2428.0 | PG21 | 70.325.2428.0 | 70.340.2428.0 | PG21 |
| 32 POLE | 70.300.3253.0 | 70.310.3253.0 | 70.320.3228.0 | - | - | - | - | - |













| | Socket Insert | Plug Insert | Narrow Ent | ry Hood | Top Ent | ry Hood | Single Ent | ry Base | with Protective | • |
|-------------|---------------|---------------|---------------|---------|---------------|---------|---------------|---------|-----------------|-------|
| Description | Part No. | Part No. | Part No. | Gland | Part No. | Gland | Part No. | Gland | Part No. | Gland |
| 6 POLE | 70.300.0640.0 | 70.310.0640.0 | 70.350.0628.0 | PG13.5 | 70.352.0628.0 | PG13.5 | - | - | - | - |
| 48 POLE | 70.300.4840.0 | 70.310.4840.0 | 70.363.4828.0 | PG36 | 70.362.4828.0 | PG29 | 70.331.4828.0 | PG29 | 70.344.4828.0 | PG36 |













| | | | | | | Open Entry Base | Double Ent | ry Base |
|-------------|---------------|---------------|------------------------|---------------|---------|------------------------|----------------|---------|
| | Socket Insert | Plug Insert | Open Entry Base | Double Ent | ry Base | with Protective Cover | with Protectiv | e Cover |
| Description | Part No. | Part No. | Part No. | Part No. | Gland | Part No. | Part No. | Gland |
| 6 POLE | 70.300.0640.0 | 70.310.0640.0 | 99.503.0000.6 | 70.330.0628.0 | PG16 | 70.325.0628.0 | 70.340.0628.0 | PG16 |
| 48 POLE | 70.300.4840.0 | 70.310.4840.0 | 70.320.4828.0 | - | - | 70.325.4828.0 | - | - |

Note: PG and Metric thread Sizes

Worldwide the use of PG threads are being changed over to Metric thread sizes. Because of pre-existing demand, we need to supply in both styles of PG and Metric. Please select Metric thread multipoles wherever possible as PG threads will be phased out.





Multipole Connectors - Revos Coupling Hoods

Coupling hoods for cable to cable coupling













| | | Basic | | Basic | | Basic | | Basic | Eexi tı | umpet | Eexi tr | umpet |
|-------------|---------------|-------|---------------|-------|---------------|-------|---------------|-------|---------------|-------|---------------|-------|
| Description | Part No. | Gland |
| 6 POLE | 70.372.0635.0 | M20 | - | - | 99.547.0000.6 | M20 | - | - | 99.741.3329.7 | M20 | - | - |
| 10 POLE | 71.372.1035.0 | M20 | 70.372.1035.0 | M20 | 99.548.0000.6 | M20 | 99.700.0120.5 | PG21 | - | - | 99.743.3329.7 | M20 |
| 16 POLE | 71.372.1635.0 | M25 | 70.372.1635.0 | M25 | 99.549.0000.6 | M25 | 70.372.1628.0 | PG21 | - | - | 99.745.3329.7 | M25 |
| 24 POLE | 71.372.2435.0 | M25 | 70.374.2435.0 | M32 | - | - | - | - | - | - | 99.748.3329.7 | M32 |

Multipole Connectors - Revos Mini

Metric

Thanks to its compact contact inserts with 3 to 8 poles revos MINI fits into mechanical, control and switchgear engineering applications as well as small motors and lighting technology.

Revos MINI with its connector housings in zinc die-cast or polyamide withstand the toughest application conditions.

Specifications:

- Screw connect 600V, 10A
- Crimp connect 50V,10A
- see page 96, for HD crimp contacts, use extraction tool"1"













| | Socket insert | Plug insert | Socket insert | Plug insert crimp | | |
|--------|---------------|---------------|--------------------|-------------------|--------------------|--------------------|
| | screw clamp | screw clamp | crimp w/o contacts | w/o contacts | Basic single lever | Basic double lever |
| Size | Part No. | Part No. | Part No. | Part No. | Part No. Gland | Part No. Gland |
| 3 POLE | 73.300.0353.0 | 73.310.0353.0 | - | - | 76.350.0736.0 M20 | 76.352.0736.0 M20 |
| 4 POLE | 73.300.0453.0 | 73.310.0453.0 | - | - | 76.350.0736.0 M20 | 76.352.0736.0 M20 |
| 7 POLE | - | - | *73.700.0753.0 | *73.710.0753.0 | 76.350.0736.0 M20 | 76.352.0736.0 M20 |









| | | | Closed bottom base | | Open entry base | Open entry angled base | Coupling hood | |
|--------|---------------|-------|--------------------|---------------|-----------------|------------------------|---------------|--|
| Size | Part No. | Gland | Part No. | Part No. | Part No. | Gland | | |
| 3 POLE | 76.322.0736.0 | M20 | 76.320.0729.0 | 76.321.0729.0 | 76.372.0736.0 | M20 | | |
| 4 POLE | 76.322.0736.0 | M20 | 76.320.0729.0 | 76.321.0729.0 | 76.372.0736.0 | M20 | | |
| 7 POLE | 76.322.0736.0 | M20 | 76.320.0729.0 | 76.321.0729.0 | 76.372.0736.0 | M20 | | |