

1

2

3

4



5

6

7

A

A



Product Specification

Material

Insulator : Glass-Filled thermoplastic PBT
UL94V-0 rated

Contact : Brass

Shell : Steel

Electrical

Contact Resistance : 20 milliohms
Max at 1 AMP DC.

Insulation Resistance : 1000
megohms at 500 VDC

Dielectric Withstanding Voltage :
1000 VAC/rms 60Hz for 1 minute

Current Rating : 5AMP

Voltage Rating : 250 VAC/rms 60Hz

③ Operation temperature: -55°C~+105°C

B

B

C




C

D

D

E

E



Dimensions

Positions	A	B	C	E
9	30.81	24.99	16.92	11.08
15	39.14	33.32	25.50	19.39
25	53.04	47.04	38.96	33.24
37	69.32	63.50	55.42	49.86

9.4mm Footprint

G

G

RoHS compliant

Scale	1:1					Date	Name	Customer-No.
TOLERANCE						Drawn	17.05.2000	Hellwig
X.	±0.38					Approved	30.05.2014	Joanna
X.X	±0.25							
X.XX	±0.13	③	Update	30.05.2014	Joanna			
DIM	TOL	②	Update	08.04.2009	Dean			
X.°	±3°							
X.X°	±1.0°	①	Drawn	17.05.2000	Hellwig			
Angle	TOL	Id.	Modification	Date	Name			ASSMANN WSW-No. A-DS xx A/KG-T1
								Drawing-No.
						Replace	ASS 0146 CO 11.11.1997	Sheet

H

H

1

2

3

4

5

6

7

SVXXX