



- ◆ High MTBF up to 700 000 hours
- ◆ Superior operating temperature performance up to 70 °C
- ◆ Very High efficiency up to 87%
- ◆ Very Low Cost
- ◆ Compact
- ◆ Withstands 300VAC surges (5s)
- ◆ Three Year Warranty

LS Series Single Output General Purpose Power Supplies

Key Market Segments & Applications

Test & Measurement
Automated Service
Factory Automation

General Purpose
LED Lighting & Displays

LS Features and Benefits

Features

- ◆ High MTBF
- ◆ High Efficiency
- ◆ -25 to +70 deg C Operating Temperature
- ◆ Low Derating above 50 degs C (up to 70% load available at 70° C)
- ◆ Curve B emc

Benefits

- ◆ Superior Reliability
- ◆ Easier System Cooling
- ◆ Suitable for Indoor & Outdoor Enclosures
- ◆ Improved System Power Optimisation
- ◆ Assists System Compliance

Specifications

| | | LS50 | LS75 | LS100 | LS150 |
|-------------------------------------|-----|---|-----------------|----------------------|-----------------|
| AC Input Voltage (300VAC for 5s) | VAC | 88 - 264VAC | | 88-132/176-264VAC(1) | |
| Input Frequency | Hz | 47 - 63Hz | | | |
| DC Input Voltage | VDC | 125 - 373VDC | | 258 - 273VDC | |
| Inrush Current (230VAC, cold start) | A | 40 | 40 | 40 | 40 |
| Power Factor | - | Meets EN61000-3-2, -3 | | | |
| Input Current (115/230VAC) | A | 1.3 / 0.8 | 1.6 / 1.0 | 2.5 / 1.5 | 3 / 2 |
| Temperature Coefficient | - | <0.03%/°C (0 - 50°C) | | | |
| Overcurrent Protection | - | > 110% | | | |
| Overvoltage Protection | V | 3.3V: 3.8-4.45V, 5V: 5.75-6.75V, 12V: 13.8-16.2V, 15V: 17.25-20.25V, 24V: 27.6-32.4V, 36V: 41.4-48.6V, 48V: 55.2-64.8V | | | |
| Hold Up Time (115 / 230V input) | ms | 14 / 60 | 14 / 60 | 18 / 100 | 20 / 28 |
| Leakage Current (230VAC 60Hz) | mA | <1mA | | TBA | |
| Remote Sense | - | No | | | |
| LED Indicator | - | Green LED = On | | | |
| Operating Temperature | -- | 25 to +70°C. Derate linearly to 50% load from +50 to +70°C (2) | | | |
| Storage Temperature | - | -40 to +85°C | | | |
| Operating Humidity | - | 20 - 90% RH (non condensing) | | | |
| Storage Humidity | - | 10 - 95% RH (non condensing) | | | |
| Cooling | - | Convection | | | |
| Withstand Voltage | - | Input to Ground 1.5kVAC, Input to Output 3kVAC, Output to Ground 500VAC for 1 min. | | | |
| Isolation Resistance | - | >100M at 25C & 70%RH, Output to Ground 500VDC | | | |
| Vibration (non operating) | - | 10 - 55Hz: 19.6m/s ² constant sweep 1 min X, Y, Z for 1 hour | | | |
| Shock | - | < 196.1 m/s ² (20G) | | | |
| Immunity | - | IEC61000-4-2, -3, -4, -5, -6, -8, -11 | | | |
| Safety Agency Approvals | - | UL60950-1, EN60950-1, IEC60950-1, CE Mark | | | |
| Conducted & Radiated EMI | - | EN55011/EN55022-B, FCC-B | | | |
| MTBF (MIL-HDBK-217F) | | 712,890 | 648,786 | 545375 | 505393 |
| Weight (Typ) | g | 350 | 410 | 600 | 700 |
| Size (LxWxH) | in | 3.9 x 3.8 x 1.4 | 5.1 x 3.8 x 1.5 | 6.3 x 3.8 x 1.5 | 7.8 x 3.9 x 1.5 |
| Warranty | yrs | Three Years | | | |


Model Selector

| Model | Voltage | Adjust Range (V) | Max Current (A) | Load Reg (mV) | Line Reg (mV) | Ripple Noise (mV) | Efficiency (typ) % |
|----------|---------|------------------|-----------------|---------------|---------------|-------------------|--------------------|
| LS50-3 | 3.3V | 3.0 - 3.6 | 10 | 40 | 20 | 80 | 75 |
| LS50-5 | 5V | 4.75 - 5.5 | 10 | 40 | 20 | 80 | 80 |
| LS50-12 | 12V | 10.8 - 13.2 | 4.2 | 96 | 48 | 120 | 84 |
| LS50-15 | 15V | 13.5 - 16.5 | 3.4 | 120 | 60 | 120 | 85 |
| LS50-24 | 24V | 22 - 27.2 | 2.2 | 192 | 96 | 120 | 86 |
| LS50-36 | 36V | 32 - 40 | 1.4 | 288 | 144 | 150 | 86 |
| LS50-48 | 48V | 42 - 54 | 1.1 | 384 | 192 | 200 | 86 |
| LS75-3 | 3.3V | 3.0 - 3.6 | 15 | 40 | 20 | 80 | 75 |
| LS75-5 | 5V | 4.75 - 5.5 | 12 | 40 | 20 | 80 | 79 |
| LS75-12 | 12V | 10.8 - 13.2 | 6 | 96 | 48 | 120 | 84 |
| LS75-15 | 15V | 13.5 - 16.5 | 5 | 120 | 60 | 120 | 85 |
| LS75-24 | 24V | 22 - 27.2 | 3.2 | 192 | 96 | 120 | 86 |
| LS75-36 | 36V | 32 - 40 | 2.1 | 288 | 144 | 150 | 86 |
| LS75-48 | 48V | 42 - 54 | 1.6 | 384 | 192 | 200 | 87 |
| LS100-3 | 3.3V | 3.0 - 3.3 | 20 | 66 | 16.5 | 80 | 74 |
| LS100-5 | 5V | 4.75 - 5.5 | 16 | 50 | 25 | 80 | 77 |
| LS100-12 | 12V | 10.8 - 13.2 | 8.5 | 60 | 60 | 120 | 81 |
| LS100-15 | 15V | 13.5 - 16.5 | 7 | 75 | 75 | 120 | 82 |
| LS100-24 | 24V | 22 - 27.2 | 4.5 | 120 | 120 | 120 | 84 |
| LS100-36 | 36V | 32 - 40 | 3 | 150 | 150 | 150 | 84 |
| LS100-48 | 48V | 42 - 54 | 2.3 | 180 | 180 | 200 | 84 |
| LS150-3 | 3.3V | 3.0 - 3.3 | 30 | 66 | 16.5 | 80 | 74 |
| LS150-5 | 5V | 4.75 - 5.5 | 26 | 50 | 25 | 80 | 78 |
| LS150-12 | 12V | 10.8 - 13.2 | 12.5 | 60 | 60 | 120 | 83 |
| LS150-15 | 15V | 13.5 - 16.5 | 10 | 75 | 75 | 120 | 84 |
| LS150-24 | 24V | 22 - 27.2 | 6.5 | 120 | 120 | 120 | 86 |
| LS150-36 | 36V | 32 - 40 | 4.3 | 150 | 150 | 150 | 86 |
| LS150-48 | 48V | 42 - 54 | 3.3 | 180 | 180 | 200 | 87 |


Notes: Preliminary models shaded in blue

- (1) Switch selectable for 115 or 230VAC
- (2) LS50, LS75-3 & -5: Derate linearly to 70% load from +50 to +70°C.
LS75-12, -15, -24, -36, -48 Derate linearly to 60% load from +50 to +70°C.


LS50 Outline Drawing




LS75 Outline Drawing



LS100 Outline Drawing



LS150 Outline Drawing



LAMBDA EUROPE

AUSTRIA

LAMBDA ELECTRONICS GmbH
Aredstraße 22
A-2544 Leobersdorf

Telephone: +43 (0) 2256 655 84
Facsimile: +43 (0) 2256 645 12
www.lambda-austria.com

FRANCE

LAMBDA SAS
ZAC des Delaches, BP1077 - Gometz le Chatel
91940 Les Ulis

Telephone: +33 (0) 1 60 12 71 65
Facsimile: +33 (0) 1 60 12 71 66
Web: www.lambda-f.com

GERMANY

LAMBDA GmbH
Karl-Bold-Straße 40
D-77855 Achern

Telephone: +49 (0) 78 41 666 0
Facsimile: +49 (0) 78 41 5000
Web: www.lambda-germany.com

ISRAEL

NEMIC LAMBDA LTD
Kibbutz Givat
Hashlosha 48800

Telephone: +972 (0) 3 902 4333
Facsimile: +972 (0) 3 902 4777
Web: www.nemic.co.il

ITALY

LAMBDA s.r.l.
Via dei Laboratori 128/130,
20092, Cinisello Balsamo (Mi)

Telephone: +39 (0) 02 61 29 38 63
Facsimile: +39 (0) 02 61 29 09 00
Web: www.lambda-italy.com

SWEDEN

LAMBDA SCANDINAVIA
PO Box 546, Rallarvägen 41
SE-184 25. Akersberga

Telephone: +46 (0) 8 598 94 090
Facsimile: +46 (0) 8 540 66 096
Web: www.lambda-scandinavia.com

UK

LAMBDA UK
Kingsley Avenue
Ilfracombe Devon EX34 8ES

Telephone: +44 (0) 1271 856666
Facsimile: +44 (0) 1271 864894
Web: www.lambda-gb.com

LAMBDA NORTH AMERICA

visit www.lambda-power.com for a list of Lambda offices and distributors

LAMBDA ASIA

visit www.dense-lambda.com for a list of Lambda offices and distributors

LOCAL DISTRIBUTION

