

- Low Cost
- 3 Year Warranty
- Low Cost
- 3 Year Warranty
- Semi F47 Compliant (DLP180&240 only)
- Convection Cooled
- Conducted and Radiated EMI, Class B
- Input Transient Protection, IEC61000-4
- NEC Class 2 Compliant (DLP75&100/C2 models only)

# DLP Series

## 75 to 240W, 24V Output DIN Rail Mount Power Supply

### Key Market Segments & Applications

- Industrial Controls: Motor Control Systems
- Factory Automation: Process Control, Automotive,
- Chemical Processing
- Test & Measurement: Burn in & Test, Instrumentation
- Measurement

### DLP Features and Benefits

#### Features

- PFC Compliant to EN61000-3-2
- UL508 Approvals
- 3 Year Warranty

#### Benefits

- Supports Global Use
- Enables System Certification
- Fit & Forget

### Specifications


ITEMS	MODELS	DLP75-24-1/E	DLP100-24-1/E	DLP120-24-1/E	DLP180-24-1/E	DLP240-24-1/E
		DLP75-24-1/C2EJ	DLP100-24-1/C2EJ			
Output Voltage	V	24	24	24	24	24
Output Current (/C2 models)	A	3.1 (2.5)	4.1 (3.7)	5.0	7.5	10
Output Power (/C2 models)	W	75 (60)	98.4 (88.8)	120	180	240
Output Voltage Adjustment	V	21.6 - 28 (fixed for /C2 models)				
Load Regulation	-	192mV				
Line Regulation	-	120mV				
Ripple/Noise (0-60°C)	mV	240				
AC Input Voltage & Frequency	-	85-132/170-265VAC, 47-63Hz Auto select			85-265VAC (47-63Hz) or 120-370VDC <sup>(1)</sup>	
Input Current 100/230VAC	A	1.7/0.8	2.3/1.2	2.4/1.3	2.3/1.0	3.0/1.3
	/C2	A	1.4/0.7	2.0/1.0	-	-
Efficiency 100/230VAC	%	81/83	82/85	83/85	84/87	82/86
Power Factor	-	Meets EN61000-3-2 (DLP180, 240: >0.95)				
Inrush Current (Typ) 100/230VAC	A	20/45				
Leakage Current	mA	Less than 0.75mA				
Hold-up Time 100/230VAC	ms	20/30 (Semi F47 Compliance, DLP 180 & 240 only)				
Overcurrent Protection	-	>105% Fold Back	>105%, Constant Current			-
	/C2	-	~2.6A	~3.75A	-	-
Overvoltage Protection	-	30-35V, latching, cycle AC line to reset (26-30V DLP75-24-1/C2EJ)				
LED Indicators	-	Green LED = DC ok Red LED = overcurrent				
Operating Temperature (2)	-	Convection cooled, -10°C to 60°C, derate linearly to 60% load from 50 to 60°C				
Storage Temperature	-	-30°C ~ +85°C				
Humidity (Non-Condensing)	%RH	30-90% operating 10-95% non operating				
Withstand Voltage	-	Input - Ground 2kVAC, Input to Output 3kVAC, Output - Ground 500VAC				
Vibration	-	9.8m/s <sup>2</sup> (1.0G) at DIN rail; (10-55Hz: 9.8m/s <sup>2</sup> Constant, X,Y, Z each 1 hour)				
Shock	-	196m/s <sup>2</sup> (20G)				
Safety Agency Approvals	-	UL508, NEC Class 2(3) (/C2 models), UL60950, CSA60950, EN60950, CE, EN50178 Cat III (Pri)				
Conducted EMI	-	FCC-B, EN55011/EN55022-B, VCCI-B; Meets IEC61000-4-1				
Radiated EMI	-	EN55011/EN55022-B, FCC-Class B, VCCI-B				
ESD	-	IEC61000-4-2 ±10kV (Air), ±5kV (Contact)				
Radiated RFI	-	IEC61000-4-3 80-1000MHz, 12V/m 80% AM 1kHz				
Fast Transient Burst	-	IEC61000-4-4 2.4kV 5kHz				
Lightning Surge	-	IEC61000-4-5 4.4kV, 1.2x50µs (Common Mode) 2.4kV 1.2x50µs (Normal)				
Conducted RFI	-	IEC61000-4-6 150kHz-80MHz, 12V, 80% AM 1kHz				
Magnetic Field	-	IEC61000-4-8 36A/m				
Voltage Dips	-	IEC61000-4-11 70% 10ms, 40% 100ms, 0% 5s				
Size	mm	50x97x110	60x97x110	60x97x110	80x97x110	120x97x110
Weight	g	470	540	540	780	1000
Warranty	-	3 Years				

(1) DC input is not safety approved


(2) DLP240-24-1/E, 170-265VAC: -10°C~+70°C, derated linearly to 60% load from 50° to 70°C.  
 DLP75-24-1/C2EJ: -10°C~+70°C, derated linearly to 75% load from 50° to 60°C.  
 DLP100-24-1/C2EJ: -10°C~+70°C, derated linearly to 80% load from 50° to 60°C.

(3) Evaluated to NEC NFPA70 Class 2 output per UL1310


## DLP75 Outline Drawing




## DLP100/120 Outline Drawing





### DLP180 Outline Drawing



### DLP 240 Outline Drawing



### Derating Curve



## LAMBDA EUROPE

<b>AUSTRIA</b> LAMBDA ELECTRONICS GmbH Aredstraße 22 A-2544 Leobersdorf	Telephone: +43 (0) 2256 655 84 Facsimile: +43 (0) 2256 645 12 www.lambda-austria.com
<b>FRANCE</b> LAMBDA SAS ZAC des Delaches, BP1077 - Gometz le Chatel 91940 Les Ulis	Telephone: +33 (0) 1 60 12 71 65 Facsimile: +33 (0) 1 60 12 71 66 Web: www.lambda-f.com
<b>GERMANY</b> LAMBDA GmbH Karl-Bold-Straße 40 D-77855 Achern	Telephone: +49 (0) 78 41 666 0 Facsimile: +49 (0) 78 41 5000 Web: www.lambda-germany.com
<b>ISRAEL</b> NEMIC LAMBDA LTD Kibbutz Givat Hashlosha 48800	Telephone: +972 (0) 3 902 4333 Facsimile: +972 (0) 3 902 4777 Web: www.nemic.co.il
<b>ITALY</b> LAMBDA s.r.l. Via dei Laboratori 128/130, 20092, Cinisello Balsamo (Mi)	Telephone: +39 (0) 02 61 29 38 63 Facsimile: +39 (0) 02 61 29 09 00 Web: www.lambda-italy.com
<b>SWEDEN</b> LAMBDA SCANDINAVIA PO Box 546, Rällärvägen 41 SE-184 25. Akersberga	Telephone: +46 (0) 8 598 94 090 Facsimile: +46 (0) 8 540 66 096 Web: www.lambda-scandinavia.com
<b>UK</b> LAMBDA UK Kingsley Avenue Ilfracombe Devon EX34 8ES	Telephone: +44 (0) 1271 856666 Facsimile: +44 (0) 1271 864894 Web: www.lambda-gb.com

## LAMBDA NORTH AMERICA

visit [www.lambdapower.com](http://www.lambdapower.com) for a list of Lambda offices and distributors

## LAMBDA ASIA

visit [www.densei-lambda.com](http://www.densei-lambda.com) for a list of Lambda offices and distributors

## LOCAL DISTRIBUTION

