



# SAFETY DATA SHEET

according to 1907/2006/EC, Article 31

Page 1/5

## QSWNC601E-SN60-Sn63-CLP

Revision 1  
Revision date 2015-06-04

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

|              |                         |
|--------------|-------------------------|
| Product name | QSWNC601E-SN60-Sn63-CLP |
| CAS No.      | 7439-92-1               |
| EC No.       | 231-100-4               |

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

|             |  |
|-------------|--|
| Product Use | [SU22] Professional uses: Public domain (administration, education, entertainment, services, craftsmen); |
| Description | Soldering.   |

#### 1.3. Details of the supplier of the safety data sheet

|                                       |   |
|---------------------------------------|---|
| Company                               | Qualitek Europe Ltd   |
| Address                               | Unit 9 Apex Court<br>Bassendale Road<br>Bromborough<br>Wirral<br>CH62 3RE |
| Web                                   | www.qualitek.com  |
| Telephone                             | + 44(0)151 334 0888   |
| Fax                                   | + 44(0)151 334 1408   |
| Email address of the competent person | sales@qualitek-europe.com   |

#### 1.4. Emergency telephone number

|                            |   |
|----------------------------|---|
| Emergency telephone number | + 44(0)151 334 0888<br>9.00 am - 5.00 pm Mon -Fri |
|----------------------------|---|

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

|                                      |  |
|--------------------------------------|--|
| 2.1.1. Classification - 67/548/EEC   | T; R61 Xn; R22-33-62<br>Symbols: T: Toxic.   |
| Main hazards                         | Harmful if swallowed. Danger of cumulative effects. May cause harm to the unborn child. Possible risk of impaired fertility. |
| 2.1.2. Classification - EC 1272/2008 | Acute Tox. 4: H302+H332; STOT SE 3: H335; Repr. 1A: H360Df; STOT RE 2: H373; Aquatic Acute 1: H400; Aquatic Chronic 1: H410; |

#### 2.2. Label elements

|                   |        |
|-------------------|--------|
| Hazard pictograms |        |
| Signal Word       | Danger |

## QSWNC601E-SN60-Sn63-CLP

Revision 1

Revision date 2015-06-04

## 2.2. Label elements

|  |  |
|--|--|
| <b>Hazard Statement</b>                    | Acute Tox. 4: H302+H332 - Harmful if swallowed or if inhaled.<br>STOT SE 3: H335 - May cause respiratory irritation.<br>Repr. 1A: H360Df - May damage the unborn child. Suspected of damaging fertility.<br>STOT RE 2: H373 - May cause damage to organs through prolonged or repeated exposure .<br>Aquatic Acute 1: H400 - Very toxic to aquatic life.<br>Aquatic Chronic 1: H410 - Very toxic to aquatic life with long lasting effects.    |
| <b>Precautionary Statement: Prevention</b> | P202 - Do not handle until all safety precautions have been read and understood.<br>P261 - Avoid breathing dust/fume/gas/mist/vapours/spray.<br>P264 - Wash thoroughly after handling.<br>P270 - Do not eat, drink or smoke when using this product.<br>P271 - Use only outdoors or in a well-ventilated area.<br>P273 - Avoid release to the environment.<br>P281 - Use personal protective equipment as required.<br>Warning! Contains lead. |
| <b>Precautionary Statement: Response</b>   | P301+P312 - IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell.<br>P304+P340 - IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.<br>P308+P313 - IF exposed or concerned: Get medical advice/attention.   |
| <b>Precautionary Statement: Disposal</b>   | Do not empty into drains; dispose of this material and its container in a safe way.  |

## SECTION 3: Composition/information on ingredients

## 3.1. Substances

67/548/EEC / 1999/45/EC

| Chemical Name          | Index No. | CAS No.   | EC No.    | REACH Registration Number | Conc. (%w/w) | Classification       |
|------------------------|-----------|-----------|-----------|---------------------------|--------------|----------------------|
| Lead                   |           | 7439-92-1 | 231-100-4 | 01-2119513221-59          | 35-55%       | T; R61 Xn; R22-33-62 |
| Tin                    |           | 7440-31-5 | 231-141-8 | 01-2119486474-28          | 55-75%       |                      |
| Other (Not Classified) |           |           |           |                           | 1 - 10%      | Xi; R36/37/38        |

EC 1272/2008

| Chemical Name          | Index No. | CAS No.   | EC No.    | REACH Registration Number | Conc. (%w/w) | Classification  |
|------------------------|-----------|-----------|-----------|---------------------------|--------------|---|
| Lead                   |           | 7439-92-1 | 231-100-4 | 01-2119513221-59          | 35-55%       | Acute Tox. 4: H302+H332;<br>Repr. 1A: H360Fd; STOT RE<br>2: H373; Aquatic Chronic 2:<br>H411; |
| Tin                    |           | 7440-31-5 | 231-141-8 | 01-2119486474-28          | 55-75%       |   |
| Other (Not Classified) |           |           |           |                           | 1 - 10%      |   |

## SECTION 4: First aid measures

## 4.1. Description of first aid measures

|                     |  |
|---------------------|--|
| <b>Inhalation</b>   | Toxic by inhalation. Inhalation may cause coughing, tightness of the chest and irritation of the respiratory system. Inhalation of vapour may cause shortness of breath. Move the exposed person to fresh air. Seek medical attention. |
| <b>Eye contact</b>  | May cause irritation to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.  |
| <b>Skin contact</b> | Toxic in contact with skin. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention.  |
| <b>Ingestion</b>    | Toxic if swallowed. Ingestion is irritating to the respiratory tract and may cause damage to the central nervous system. If swallowed, seek medical advice immediately and show this container or label. DO NOT INDUCE VOMITING.       |

## SECTION 5: Firefighting measures

## QSWNC601E-SN60-Sn63-CLP

Revision 1  
Revision date 2015-06-04

## 5.1. Extinguishing media

Use as appropriate: Carbon dioxide (CO2), Dry chemical, Foam.

## 5.2. Special hazards arising from the substance or mixture

Burning produces irritating, toxic and obnoxious fumes.

## 5.3. Advice for firefighters

Wear: Self-contained breathing apparatus. Wear chemical protective clothing.

## SECTION 6: Accidental release measures

## 6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation of the working area. Evacuate personnel to a safe area. Wear suitable protective equipment.

## 6.2. Environmental precautions

Do not allow product to enter drains. Prevent further spillage if safe.

## 6.3. Methods and material for containment and cleaning up

Sweep up. Transfer to suitable, labelled containers for disposal. Clean spillage area thoroughly with plenty of water.

## SECTION 7: Handling and storage

## 7.1. Precautions for safe handling

Avoid contact with eyes and skin. Ensure adequate ventilation of the working area.

## 7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated area. Keep containers tightly closed.

## SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

## 8.1.1. Exposure Limit Values

|                                   |                   |              |
|-----------------------------------|-------------------|--------------|
| QSWNC601E-SN60-Sn63-CLP<br>(Lead) | DIR: 82/605       | 8hTWA ppm: - |
|                                   | 8hTWA mg/m3: 0.15 | STEL ppm: -  |
|                                   | STEL mg/m3: -     | NOT: -       |

## 8.2. Exposure controls

|   |  |
|---|--|
| 8.2.1. Appropriate engineering controls | Ensure adequate ventilation of the working area.             |
| 8.2.2. Individual protection measures   | Wear chemical protective clothing.                           |
| Eye / face protection                   | Approved safety goggles.                                     |
| Skin protection - Handprotection        | Chemical resistant gloves (PVC).                             |
| Respiratory protection                  | Self-contained breathing apparatus must be used in handling. |

## SECTION 9: Physical and chemical properties

## 9.1. Information on basic physical and chemical properties

|                          |                     |
|--------------------------|---------------------|
| State                    | Solid               |
| Colour                   | Grey                |
| Melting point            | 183 - 190 °C        |
| Flash point              | 115 °C              |
| Autoignition temperature | 226 °C              |
| Solubility               | Immiscible in water |

## QSWNC601E-SN60-Sn63-CLP

Revision 1

Revision date 2015-06-04

**SECTION 10: Stability and reactivity**

## 10.2. Chemical stability

Stable under normal conditions.

**SECTION 11: Toxicological information**

## 11.1.4. Toxicological Information

|                         |                          |                             |
|-------------------------|--------------------------|-----------------------------|
| Lead                    | Oral Rat LD50: 40mg/gm   | Dermal Rabbit LD50: 25mg/gm |
| QSWNC601E-SN60-Sn63-CLP | Dermal Rat LD50: 25mg/gm | Oral Rat LD50: 40mg/gm      |

**SECTION 12: Ecological information**

## 12.1. Toxicity

|                         |                              |                           |
|-------------------------|------------------------------|---------------------------|
| QSWNC601E-SN60-Sn63-CLP | Daphnia EC50/48h: 0.009 mg/l | Fish LC50/96h: 0.003 mg/l |
|-------------------------|------------------------------|---------------------------|

## 12.2. Persistence and degradability

Danger of cumulative effects. Dangerous for the environment.

**SECTION 13: Disposal considerations**

## General information

Dispose of in compliance with all local and national regulations.

**SECTION 14: Transport information**

## ADR/RID

The product is not classified as dangerous for carriage.

## IMDG

The product is not classified as dangerous for carriage.

## IATA

The product is not classified as dangerous for carriage.

**SECTION 15: Regulatory information**

## 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

This Product is Classified to Regulation 1272/2008/EC(CLP).

**SECTION 16: Other information**

## Other information

|  |   |
|--|---|
| Revision                               | This document differs from the previous version in the following areas:<br>2 - 2.1.2. Classification - EC 1272/2008.<br>2 - Hazard pictograms.  |
| Text of risk phrases in Section 3      | R22 - Harmful if swallowed.<br>R33 - Danger of cumulative effects.<br>R36/37/38 - Irritating to eyes, respiratory system and skin.<br>R61 - May cause harm to the unborn child.<br>R62 - Possible risk of impaired fertility.   |
| Text of Hazard Statements in Section 3 | Acute Tox. 4: H302+H332 - Harmful if swallowed or if inhaled<br>Repr. 1A: H360Fd - May damage fertility. Suspected of damaging the unborn child.<br>STOT RE 2: H373 - May cause damage to organs through prolonged or repeated exposure .<br>Aquatic Chronic 2: H411 - Toxic to aquatic life with long lasting effects. |

## Further information

The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.

# QSWNC601E-SN60-Sn63-CLP

Revision 1

Revision date 2015-06-04

---