

Kit Resistors



Chip Kit



Coated Kit

Ordering Procedure: Ex: 0603, 1/16W, +/-1%, E-6 series, Chip Kit Resistors

0 6 0 3 W G F E 0 0 6 K I T

Resistor Size:

- Chip type:
0402, 0603, 0805, 1206, 2512
- Coated type:
Carbon Film Fixed Resistors
(see page 25 for boxes no.1st - 7th)
Metal Film Fixed Resistors
(see page 28 for boxes no.1st - 7th)

Wattage:

- Normal:
 WG = 1/16W
 WA = 1/10W
 W8 = 1/8W
 W4 = 1/4W
 W2 = 1/2W
 1W = 1W
- Small size:
 SA = 1/10WS
 S8 = 1/8WS
 S4 = 1/4WS
 S2 = 1/2WS

Resistance value:

- For Kit Resistors
 E006 = E-6 Series
 E012 = E-12 Series
 E024 = E-24 Series

Special Feature:


- KIT = Kit resistors (with resistors)
- KON = Album only (no resistors)
- KIL = Index only
- KIN = Insert only
- KIC = Insert and Album, Cover lid, (No resistors)

Tolerance:

- F = ±1%
- J = ±5%


Chip Type

Album Kit Dimension




Coated Type


Album Kit Dimension



Inserts for Chip Kit



Inserts for Coated Kit



Sample:

- 1.) SMD Kit 1/16W (0603) 1% E-6 Series-0603WGFE006KIT
- 2.) Album only Kit 1/16W (0603) 1% E-6 Series-0603WGFE006KON (no chip resistors)
- 3.) Chip Kit Standard : E-6 : 32 values
 E-12 : 62 values
 E-24 : 121 values

Thick Film Chip Resistors

Performance Specification

Temperature Coefficient	0Ω1 ~ 0Ω99 1Ω ~ 10Ω 11Ω ~ 100Ω >100Ω	±800PPM/°C ±400PPM/°C ±200PPM/°C ±100PPM/°C	(0201: >100 Ω ≤ ±200PPM/°C)
Short Time Overload	±5%: ±(2.0% + 0.1Ω)Max ±1%: ±(1.0% + 0.1Ω)Max		
Insulation Resistance	Min. 1,000 Mega Ohm		
Dielectric Withstanding Voltage	No evidence of flashover, mechanical damage, arcing or insulation breakdown.		
Terminal Bending	±(1.0% + 0.05Ω) Max		
Soldering Heat	±(1.0% + 0.05Ω)Max		
Solderability	Min. 95% coverage.		
Temperature Cycling	±5% : ±(1.0% + 0.05Ω)Max ±1% : ±(0.5% + 0.05Ω)Max		
Humidity (Steady State)	±5% : ±(3.0% + 0.1Ω)Max ±1% : ±(0.5% + 0.1Ω)Max		
Load Life in Humidity	±5% : ±(3.0% + 0.1Ω)Max ±1% : ±(1.0% + 0.1Ω)Max		
Load Life	±5% : ±(3.0% + 0.1Ω)Max ±1% : ±(1.0% + 0.1Ω)Max		

Ordering Procedure: Ex.: 1206, 1/4W-S, +/-5%, 10Ω T/R-5000

1 2 0 6 S 4 J 0 1 0 0 T 5 E

<p>Resistor Size: 0201, 0402, 0603, 0805, 1206, 1210, 1812, 2010, 2512 Wide Terminals: 0508, 0612, 1020, 1218, 1225</p>		<p>Resistance Value:</p> <ul style="list-style-type: none"> E-24 series: 1st digit is "0" 2nd & 3rd digits are significant figures of the resistance 4th indicates the number of zeros E-96 series: 1st to 3rd digits are significant figures of the resistance 4th digit indicates the number of zeros. "J" ~ 0.1, "K" ~ 0.01, "L" ~ 0.001 Ex. 012J ~ 1Ω2, 226K ~ 2Ω26 Jumper : use "0" for 1st to 4th digits 	
<p>Wattage: Normal size: WH=1/32W, WM=1/20W, WG=1/16W, WA=1/10W, W8=1/8W, W4=1/4W, W2=1/2W, 1W=1W Small size: SA=1/10W-S, S8=1/8W-S, S4 =1/4W-S, S3=1/3W-S, 07=3/4W-S, U2=1/2W-SS Applicable for Wide Terminal only: WJ=1.5W, 2W, 3W</p>			
	<p>Tolerance: D = ±0.5% F = ±1% G = ±2% J = ±5%</p>		
		<p>Packing Type: T = Tape/Reel</p>	
			<p>Packing Qty: 1 = 1,000 pcs. 2 = 2,000 pcs. 4 = 4,000 pcs. 5 = 5,000 pcs. A = 500 pcs. C = 10,000 pcs. D = 20,000 pcs. E = 15,000 pcs.</p>
<p>Note : 1.) Special resistance value, tolerance, T.C.R. requirement is available on a case-to-case basis. 2.) Standard reel size = 7" 3.) 4", 10", & 13" reels are available upon request</p>			<p>Special Feature: E = Lead (Pb) Free Plating Type/ RoHS compliant</p>



Thick Film Chip Resistors



Features

- Small size and light weight
- Suitable for both wave and reflow soldering
- Reduction of assembly costs

Dimension



Type	Power Rating at 70°C	Max Working Voltage	Max Overload Voltage	Dielectric Withstanding Voltage	Tolerance %	Resistance Range	Dimension (mm)				
							L	W	H	l ₁	l ₂
0201 (0603)	1/20W	0.5A	1A	-	Jumper	<50mΩ	0.60±0.03	0.30±0.03	0.23±0.03	0.10±0.05	0.15±0.05
		25V	50V	-	±1% ±2% ±5%	10Ω ~ 1MΩ 10Ω ~ 1MΩ 1Ω ~ 1MΩ					
0402 (1005)	1/16W	1A	2A	-	Jumper	<50mΩ	1.00±0.10	0.50±0.05	0.35±0.05	0.20±0.10	0.25±0.10
		50V	100V	100V	±1% ±2% ±5%	10Ω ~ 1MΩ 1Ω ~ 10MΩ 1Ω ~ 10MΩ					
0603 (1608)	1/10W-S 1/16W	1A	2A	-	Jumper	<50mΩ	1.60±0.10	0.80 ^{+0.15} _{-0.10}	0.45±0.10	0.30±0.20	0.30±0.20
		75V	150V	300V	±1% ±2% ±5%	10Ω ~ 1MΩ 1Ω ~ 10MΩ 1Ω ~ 10MΩ					
0805 (2012)	1/8W-S 1/10W	2A	5A	-	Jumper	<50mΩ	2.00±0.15	1.25 ^{+0.15} _{-0.10}	0.55±0.10	0.40±0.20	0.40±0.20
		150V	300V	500V	±1% ±2% ±5%	10Ω ~ 1MΩ 1Ω ~ 10MΩ 1Ω ~ 10MΩ					
1206 (3216)	1/4W-S 1/8W	2A	10A	-	Jumper	<50mΩ	3.10±0.15	1.55 ^{+0.15} _{-0.10}	0.55±0.10	0.45±0.20	0.45±0.20
		200V	400V	500V	±1% ±2% ±5%	10Ω ~ 1MΩ 1Ω ~ 10MΩ 1Ω ~ 10MΩ					
1210 (3225)	1/2W-SS 1/3W-S 1/4W	2A	10A	-	Jumper	<50mΩ	3.10±0.10	2.60±0.15	0.55±0.10	0.50±0.25	0.50±0.20
		200V	500V	500V	±1% ±2% ±5%	10Ω ~ 1MΩ 1Ω ~ 10MΩ 1Ω ~ 10MΩ					
1812	1/2W 3/4W-S	2A	10A	-	Jumper	<50mΩ	4.50±0.20	3.20±0.20	0.55±0.20	0.50±0.20	0.05±0.20
		200V	500V	500V	±1% ±5%	1Ω ~ 10MΩ					
2010 (5025)	3/4W-S 1/2W	2A	10A	-	Jumper	<50mΩ	5.00±0.10	2.50±0.15	0.55±0.10	0.60±0.25	0.50±0.20
		200V	500V	500V	±1% ±2% ±5%	10Ω ~ 1MΩ 1Ω ~ 10MΩ 1Ω ~ 10MΩ					
2512 (6432)	1W	2.5A	10A	-	Jumper	<50mΩ	6.35±0.10	3.20±0.15	0.55±0.10	0.60±0.25	0.50±0.20
		200V	500V	500V	±1% ±2% ±5%	10Ω ~ 1MΩ 1Ω ~ 10MΩ 1Ω ~ 10MΩ					

Note:

- 1.) Metric information inside parenthesis.
- 2.) Standard Operating Temp (°C): -55 ~ +155
- 3.) Standard: E-96 series: 0.5%, 1%
E-24 series: 2%, 5%
- 4.) Low resistance range (0.1Ω ~ 0.99Ω) is also available for 0402, 0603, 0805, 1206, 1210, 2010 and 2512

Derating Curve

