LABFACILITY L300 8-ZONE TEMPERATURE ALARM / ON-OFF CONTROLLER WITH 10A SWITCHING

The Labfacility L300 Pt100 and Thermocouple temperature alarm / on-off controller can be used in conjunction with a PC to provide accurate monitoring and alarm or on-off control of up to 8-zones simultaneously. It can also be used as a stand-alone instrument without the need for a PC.

The PC software supplied with the instrument allows control, configuration, measurement, logging, charting, alarm & relay configuration and calibration functions via a PC.

The in-built, self-calibration facility for the thermocouple version is a rapid and convenient method for on-site calibration and does not require any additional equipment other than a special, external link. Self-calibration of Pt100 ranges is equally simple and uses plug-in precision resistors.

- Low cost high performance
- USB PC interface
- 8 thermocouple (type J,K,T,E,N,R,S
 & B) or Pt100 (3 wire) inputs
- Built-in display for selected channel or all channels auto-scrolling
- Resolution 0.1°C on display, 0.01°C in software
- Self-calibration feature
- Select °C / °F
- PC software included for remote control and measure, logging, configuration and calibration
- 8 x configurable change-over relays 10A/250V



- Simple operation
- CE marked
- RoHS compliant
- 2 year warranty

Applications

- ◆ Food preparation ◆ Storage facilities ◆ Technical educational establishments
- ◆ Environmental ◆ R&D ◆ Heating & ventilation setup ◆ Building & energy management
- ◆ Instrumentation laboratories ◆ Experimentation ◆ Refrigeration/freezer plant monitoring
- Museums and Galleries



www.labfacility.com

Specification at an ambient temperature of 20°C

Measurement

Input / Ranges

Thermocouple to IEC 584

Type J -200°C to 750°C -200°C to1200°C -200°C to 350°C Type K Type T -200°C to 900°C 0°C to 1300°C Type E Type N Type R 0°C to 1760°C 0°C to 1760°C Type S Type B 300°C to 1800°C -200°C to 850°C Pt100 to IEC751, 3 wire

Note: all inputs are non-isolated and sensors must be of insulated construction.

Accuracy

Thermocouples J K T E & N

better than +/- 0.1°C +/-0.1% of range -100°C to span (Zero to span Type N) +/-0.15% of range -101 to -200°C (J K T & E)

Thermocouples R S & B

better than+/-0.1°C +/-0.15%

of range

Linearisation ±0.05°C

Pt100 range better than ±0.05°C ±0.1% of range

Zero drift ±0.01% of span per °C Span drift ±0.01% of span per °C Display LCD, backlight

Thermocouple ranges 0.1°C Display resolution

Pt100 range 0.01°C

Indication Channel No., measured temperature

(°C or °F)

Reference junction compensation for thermocouples

Self calibration

Automatic, accurate reference junction compensation is incorporated

for thermocouple ranges User facility incorporated. The instrument auto-calibrates on every

A/D cycle *

Sensor open circuit detection & indication

Ambient operating temperature

Upscale indication


0 to 50°C

Alarm/Control

Alarm modes Relay contacts High / Low / Band/ control x3 normally open*/common/

normally closed

The contact position when the relay is de-energised Rated 10A/250V, resisitive load. Relays (1to 8) can be assigned to any input and polarity (normal or Inverse) selected.



User interface Front panel keys for selecting channel

> number for display or auto-scan selection; front panel keys for relay configuration and alarm parameters. 8 x LED indicators for relay actuation.

Storage temperature

Display

Input Terminations

PC Interface

Power supply

Logging interval On-board memory PC software

-20°C to 70°C

LCD with backlight 8 x thermocouple: mini connectors

8 x Pt100, terminal blocks

Relay Terminations 4 x 6 way connector

USB

6Vdc (5.5-9.0V) via universal mains adaptor (supplied) 120-250V 50/60Hz

5 seconds to 1 hour

512 sets of readings

Supplied as standard on CD-ROM Remote control & measure:-

Log readings to file Download to PC

Logging, charting, alarm configuration

and calibration

* The integral, self-calibration facility for the thermocouple version is a rapid and convenient method for on-site calibration and does not require any additional equipment other than the special, external link (optional). Self-calibration of Pt100 ranges is quickly and conveniently performed using plug-in precision resistors (optional).

Traceable calibration can be achieved by the user conveniently and without recourse to a accredited Laboratory if there is access to a certified DVM; this can be used to measure the L200 internally generated calibrated Voltage via the "cal port" presented externally to the instrument case. Considerable time and cost saving are achieved by this method.

Ordering

Thermocouple input x8 L300-TC-00 Pt100 input x8 L300-PT-00

Custom calibration details on application

The L300 is supplied with a power Standard accessories

supply adaptor, USB lead, PC software, and instruction manual (on CD). L300-TC includes external link.

Specifications may be subject to change

.ABFACIL TEMPERATURE & PROCESS TECHNOLOGY

LABFACILITY LIMITED

www.labfacility.com

SOUTHERN UK & EXPORT DIVISION: Units 5,6 & 7, Block K, Southern Cross Industrial Estate, Shripney Road, Bognor Regis, West Sussex PO22 9SE Export Sales: tel: +44(0)1243 871287 fax: +44(0)1243 871281 email: exportsales@labfacility.co.uk Southern UK Sales: tel: +44(0)1243 871280 fax: +44(0)1243 871281 email: southernsales@labfacility.co.uk

NORTHERN UK DIVISION: Eden Place, Unit 3b Outgang Lane, Dinnington, Sheffield S25 3QT Northern UK Sales: tel: +44(0)1909 569446 fax: +44(0)1909 550632 email: northernsales@labfacility.co.uk

Data ref: 050115/DS/A