



SAFETY DATA SHEET

according to Regulation (EU) 2015/830

Page 1/4

QSW-NC601E-SN100e

Revision 0
Revision date 2018-03-27

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	QSW-NC601E-SN100e
--------------	-------------------

1.3. Details of the supplier of the safety data sheet

Company	Qualitek Europe Ltd
Address	Unit 9 Apex Court Bassendale Road Bromborough Wirral CH62 3RE
Web	www.qualitek.com
Telephone	+ 44(0)151 334 0888
Fax	+ 44(0)151 334 1408
Email address of the competent person	sales@qualitek-europe.com

1.4. Emergency telephone number

Emergency telephone number	+ 44(0)151 334 0888 9.00 am - 5.00 pm Mon -Fri
----------------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

2.1.2. Classification - EC 1272/2008	STOT SE 3: H335;
--------------------------------------	------------------

2.2. Label elements

Hazard pictograms	
Signal Word	Warning
Hazard Statement	STOT SE 3: H335 - May cause respiratory irritation.
Precautionary Statement: Prevention	P261 - Avoid breathing dust/fume/gas/mist/vapours/spray.
Precautionary Statement: Response	P312 - Call a POISON CENTER/doctor/ /if you feel unwell.
Precautionary Statement: Storage	Store in a dry place.
Precautionary Statement: Disposal	Dispose of in compliance with all Local and national regulations

SECTION 3: Composition/information on ingredients

QSW-NC601E-SN100e

Revision 0
Revision date 2018-03-27

3.2. Mixtures

EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Tin		7440-31-5	231-141-8	01-2119486474-28	90 - 100%	
organic acid		4767-03-7			<3%	STOT SE 3: H335;
Cobalt (Metal)		7440-48-4	231-158-0	01-2119488910-30	<1	
Copper (Copper dusts and mists (as Cu))					0.5 - 1%	Acute Tox. 4: H302; Skin Irrit. 2: H315; STOT SE 3: H335;

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Irritating to respiratory system. Inhalation may cause coughing, tightness of the chest and irritation of the respiratory system. Move the exposed person to fresh air. Seek medical attention.
Eye contact	Irritating to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	Irritating to skin. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention if irritation or symptoms persist.
Ingestion	Ingestion may cause nausea and vomiting. Seek medical attention if irritation or symptoms persist. DO NOT INDUCE VOMITING.

SECTION 5: Firefighting measures

5.1. Extinguishing media

	Carbon oxides.
--	----------------

5.2. Special hazards arising from the substance or mixture

	Burning produces irritating, toxic and obnoxious fumes.
--	---

5.3. Advice for firefighters

	Wear suitable respiratory equipment when necessary.
--	---

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

	Ensure adequate ventilation of the working area. Wear suitable protective equipment.
--	--

6.2. Environmental precautions

	No specific clean up requirements.
--	------------------------------------

6.3. Methods and material for containment and cleaning up

	Transfer to suitable, labelled containers for disposal.
--	---

SECTION 7: Handling and storage

7.1. Precautions for safe handling

	Avoid contact with eyes and skin. Ensure adequate ventilation of the working area. Adopt best Manual Handling considerations when handling, carrying and dispensing.
--	--

7.2. Conditions for safe storage, including any incompatibilities

	Keep in a cool, dry, well ventilated area.
--	--

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1. Exposure Limit Values

QSW-NC601E-SN100e

Revision 0

Revision date 2018-03-27

8.1.1. Exposure Limit Values

Copper (Copper dusts and mists (as Cu))	WEL 8-hr limit ppm: -	WEL 8-hr limit mg/m3: 1
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: 2
	WEL 8-hr limit mg/m3 total - inhalable dust:	WEL 15 min limit mg/m3 total - inhalable dust:
	WEL 8-hr limit mg/m3 total - respirable dust:	WEL 15 min limit mg/m3 total - respirable dust:

8.2. Exposure controls

8.2.1. Appropriate engineering controls	Ensure adequate ventilation of the working area.
8.2.2. Individual protection measures	Wear chemical protective clothing.
Eye / face protection	Approved safety goggles.
Skin protection - Handprotection	Chemical resistant gloves (PVC).
Respiratory protection	In case of insufficient ventilation, wear suitable respiratory equipment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Solid
Colour	Silver
Odour	Characteristic
Melting point	228 °C
Flash point	98 °C
Autoignition temperature	226 °C
Solubility	Slightly soluble in water

SECTION 10: Stability and reactivity

10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

SECTION 11: Toxicological information

11.1. Information on toxicological effects

	No Significant Hazard.
--	------------------------

SECTION 12: Ecological information

12.3. Bioaccumulative potential

	Does not bioaccumulate.
--	-------------------------

SECTION 13: Disposal considerations

General information

	Dispose of in compliance with all local and national regulations.
--	---

SECTION 14: Transport information

14.1. UN number

	The product is not classified as dangerous for carriage.
--	--

14.2. UN proper shipping name

	The product is not classified as dangerous for carriage.
--	--

14.3. Transport hazard class(es)

QSW-NC601E-SN100e

Revision 0

Revision date 2018-03-27

14.3. Transport hazard class(es)

The product is not classified as dangerous for carriage.

14.4. Packing group

The product is not classified as dangerous for carriage.

14.5. Environmental hazards

The product is not classified as dangerous for carriage.

14.6. Special precautions for user

The product is not classified as dangerous for carriage.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

The product is not classified as dangerous for carriage.

Further information

The product is not classified as dangerous for carriage.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****Regulations**

COMMISSION REGULATION (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC.

SECTION 16: Other information**Other information****Text of Hazard Statements in Section 3**

STOT SE 3: H335 - May cause respiratory irritation.
 Acute Tox. 4: H302 - Harmful if swallowed.
 Skin Irrit. 2: H315 - Causes skin irritation.

Further information

The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.