

# ROYALOHM

**C O N F I D E N T I A L   D O C U M E N T**

SPECIFICATION FOR APPROVAL

**RAPID ELECTRONICS LTD.**

Description : Coated Type Kit Resistors (MFR)

**Royalohm Part no.:**

Kit resistors (with resistors) 122 Values

MF0S4FFE024KIT (MF (KIT) 1/4W-S +/- 1% 50ppm E-24 series)

Approved by

**Parts corresponding to RoHS Compliant: 2005-Apr.-1**

Royal Electronic Factory (Thailand) Co., Ltd.

20/1-2 Moo 2 Klong-Na, Muang

Chachoengsao 24000, Thailand

Tel: +66-38-822404-8

Fax: +66 38-981190 / 823765

E-mail Address: Export sales: [Export@royalohm.com](mailto:Export@royalohm.com)

Local sales: [Local@royalohm.com](mailto:Local@royalohm.com)

<http://www.royalohm.com>

P.O. Box 251 Klongchan, Bangkok 10240, Thailand

Approved	Checked	Prepared
Mr. Jack Lin	Mr. S. Polthanasan	Ms. P. Supatta

Issued Date: 2014/09/19



<b>Customer: RAPID ELECTRONICS LTD.</b>	<b>Part No.: MF0S4FFE024KIT</b>
---	---------------------------------

1. Scope:

This specification for approval relates to Coated Type Kit Resistors (MFR) manufactured by ROYALOHM 's specifications.

2. Type designation:

The type designation shall be in the following form :

(Ex.)	<u>MF</u>	<u>1/4W-S</u>	<u>F</u>	<u>4.99KΩ</u>
	Type	Power Rating	Resistance Tolerance	Nominal Resistance

3. Ratings:

Ratings shall be shown in the table 1.

Table 1

Type	MF
Rated Power	0.25W at 70°C
Max. Working Voltage	200 V
Max. Overload Voltage	400 V
Dielectric Withstanding Voltage	400 V
Rated Ambient Temp.	70 °C
Operating Temp. Range	-55°C --- +155°C
Resistance Tolerance	± 1%
Resistance Range	0Ω / 10Ω ~ 1MΩ

3.1 Power rating:

Resistors shall have a power rating based on continuous full load operation at an ambient temperature of 70 °C . For temperature in excess of 70 °C , the load shall be derated as shown in the figure 1.

3.2 Voltage rating:

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercial-line frequency and waveform corresponding to the power rating , as determined from the following formula :

$$RCWV = \sqrt{P \times R}$$

Were : RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (volt)


P = Power Rating (watt)

R = Nominal Resistance (ohm)

### Coated Type Kit Resistors (MFR)

In no case shall the rated DC or RMS AC continuous working voltage be greater than the applicable maximum value


Figure 1.



3.3 Nominal resistance :

Effective figures of nominal resistance shall be in accordance with E-24 series, and resistance tolerance shall be shown by table 1.

4. Construction :



No.	Name	Material
1	Basic Body	Rod Type Ceramics
2	Resistance Film	Metal Film
3	End Cap	Steel (Tin plated iron surface)
4	Lead Wire	Annealed copper wire coated with tin
5	Joint	By Welding
6	Coating	Insulated epoxy resin ( Color : Apple Green )
7	Color Code	Epoxy Resin


<b>Coated Type Kit Resistors (MFR)</b>		
<b>5. Characteristics :</b>		
Characteristics	Limits	Test Methods ( JIS C 5201-1 )
DC. resistance	Must be within the specified tolerance	The limit of error of measuring apparatus shall not exceed allowable range or 1% of resistance tolerance (Sub-clause 4.5)
Insulation resistance	Insulation resistance is 10,000 MΩ Min	Resistors shall be clamped in the trough of a 90° metallic V-block or foil method use a metal foil shall be wrapped closely around the body of the resistor. After that shall be tested at DC potential respectively specified in the above list for 60 +10/-0 secs. (Sub-clause 4.6)
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down	Resistors shall be clamped in the trough of a 90° metallic V-block or foil method use a metal foil shall be wrapped closely around the body of the resistor. After that shall be tested at AC potential respectively specified in the table 1. for 60 +10/-0 secs. (Sub-clause 4.7)
Temperature coefficient	Within the temperature coefficient specified below : ± 50 PPM/°C Max.	Natural resistance change per temp. degree centigrade $\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \quad (\text{PPM}/^\circ\text{C})$ R1: Resistance value at room temperature (t1) R2: Resistance value at room temp. plus 100 °C (t2) (Sub-clause 4.8)
Short time overload	Resistance change rate is ± (0.5% + 0.05 Ω) Max. with no evidence of mechanical damage	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds (Sub-clause 4.13)
Terminal strength	No evidence of mechanical damage	<b>Direct load :</b> Resistance to a 2.5 kgs direct load for 10 secs. in the direction of the longitudinal axis of the terminal leads <b>Twist test :</b> Terminal leads shall be bent through 90 ° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about the original axis of the bent terminal in alternating direction for a total of 3 rotations (Sub-clause 4.16)
Solderability	95 % coverage Min.	The area covered with a new, smooth, clean, shiny and continuous surface free from concentrated pinholes. Test temp. of solder : 245°C ± 3°C Dwell time in solder : 2 ~ 3 seconds (Sub-clause 4.17)

Coated Type Kit Resistors (MFR)																	
Characteristics	Limits	Test Methods ( JIS C 5201-1 )															
Soldering temp. reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95 % coverage Min.)	The leads immersed into solder bath to 3.2 to 4.8 mm. from the body. Permanent resistance change shall be checked. <u>Wave soldering condition: (2 cycles Max.)</u> Pre-heat : 100 ~ 120 °C, 30 ± 5 sec. Suggestion solder temp.: 235 ~ 255 °C, 10 sec. (Max.) Peak temp.: 260 °C <u>Hand soldering condition:</u> Hand Soldering bit temp. : 380 ± 10 °C Dwell time in solder : 3 +1/-0 sec.															
Resistance to soldering heat	Resistance change rate is ± (1% + 0.05 Ω) Max. with no evidence of mechanical damage	Permanent resistance change when leads immersed to 3.2 to 4.8 mm from the body in 350°C ± 10 °C solder for 3 ± 0.5 seconds (Sub-clause 4.18)															
Temperature cycling	Resistance change rate is ± (1% + 0.05 Ω) Max. with no evidence of mechanical damage	Resistance change after continuous 5 cycles for duty shown below:															
		<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-55°C ± 3°C</td> <td>30 mins</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>10~15 mins</td> </tr> <tr> <td>3</td> <td>+155°C ± 2°C</td> <td>30 mins</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>10~15 mins</td> </tr> </tbody> </table>	Step	Temperature	Time	1	-55°C ± 3°C	30 mins	2	Room temp.	10~15 mins	3	+155°C ± 2°C	30 mins	4	Room temp.	10~15 mins
		Step	Temperature	Time													
		1	-55°C ± 3°C	30 mins													
		2	Room temp.	10~15 mins													
3	+155°C ± 2°C	30 mins															
4	Room temp.	10~15 mins															
(Sub-clause 4.19)																	
Vibration	Resistance change rate is ± (1% + 0.05 Ω) Max.	55Hz, 3 planes 2hrs each Total amplitude = 1.5mm (Sub-clause 4.22)															
Load life in humidity	<table border="1"> <thead> <tr> <th>Resistance value</th> <th>Δ R/R</th> </tr> </thead> <tbody> <tr> <td>Normal type</td> <td>± 1.5 %</td> </tr> </tbody> </table>	Resistance value	Δ R/R	Normal type	± 1.5 %	Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity test chamber controlled at 40 °C ± 2 °C and 90 to 95 % relative humidity (Sub-clause 4.24.2.1)											
	Resistance value	Δ R/R															
	Normal type	± 1.5 %															
<table border="1"> <thead> <tr> <th>Resistance value</th> <th>Δ R/R</th> </tr> </thead> <tbody> <tr> <td>Normal type</td> <td>± 1.5 %</td> </tr> </tbody> </table>	Resistance value	Δ R/R	Normal type	± 1.5 %	7.10 Permanent resistance change after 1,000 hours operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") at 70°C ± 2°C ambient (Sub-clause 4.25.1)												
Resistance value	Δ R/R																
Normal type	± 1.5 %																
Resistance to solvent	No deterioration of protective coatings and markings	Specimens shall be immersed in a bath of trichroethane completely for 3 minutes with ultrasonic (Sub-clause 4.30)															
Pulse overload	Resistance change rate is ± (1% + 0.05 Ω) Max. with no evidence of mechanical damage	Resistance change after 10,000 cycles (1 sec. "on" , 25 secs. "off" ) at 4 times RCWV (Sub-clause 5.8)															

### Coated Type Kit Resistors (MFR)

6. Dimension :


Unit : mm



Type	Power Rating	D (Max.)	L (Max.)	$d \pm 0.05$	$H \pm 3$
MF	1/4W-S	1.85 mm	3.5 mm	0.45 mm	28 mm

Painting method:


Welding point, terminal and lead wire, is permissible to be exposed without the outer coated cover. The extent should be within  $1/2$  of the arc angle.



7. Marking :

7.1 Resistor :

Resistors shall be marked with color coding colors shall be in accordance with JIS C 0802




### Coated Type Kit Resistors (MFR)

8. Kit resistors :


8.1 Insert for Coated Kit

Dimension (mm)



8.2 Album for Coated Kit

Dimension (mm)





**Part Number System**

**Explanation of Part Number System  
(Coated Type Kit Resistors (MFR))**

**1** **2** **3** **4** **5** **6** **7** **8** **9** **10** **11** **12** **13** **14**  
**M** **F** **0** **S** **4** **F** **F** **E** **0** **2** **4** **K** **I** **T**

**Product Type:**  
 MF = Metal Film  
 Fixed Resistor

**Tolerance:**  
 B = ± 0.1%  
 C = ± 0.25%  
 D = ± 0.5%  
 F = ± 1%  
 G = ± 2%  
 J = ± 5%

**Resistance Value:**  
 Boxes no 8, 9, 10, 11  
 For SMD Kit resistor  
 -E6 series: E006  
 -E12 series: E012  
 -E24 series: E024

**Special Feature:**  
 0 = Standard Product  
 F = Non-Flame  
 I = Non-Inductive Product

**PPM requirement:**  
 B = ± 15PPM  
 C = ± 25PPM  
 F = ± 50PPM  
 G = ± 100PPM  
 J = ± 200PPM

**Special Feature:**  
 Fill-in these 3 digits with the chip resistor types as follows:  
 - KIT: Kit resistor (with resistor)  
 - K0N: Album only (no resistor)  
 - KIL: Index Only  
 - KIN: Insert Only  
 - KIC: Insert and Album, Cover Lid (no resistor)

**Wattage:**

<b>Normal size:</b>	<b>Small size:</b>
W8 = 1/8W	S4 = 1/4W-S
W4 = 1/4W	S2 = 1/2W-S
W2 = 1/2W	06 = 0.6W-S
1W = 1W	M7 = 0.75W-S
2W = 2W	1S = 1W-S
3W = 3W	2S = 2W-S
	3S = 3W-S

**Extra Small size:**  
 U2 = 1/2W-SS  
 04 = 0.4W-SS

Sample: MF 1/4W-S +/- 1% 50ppm E-24 series KIT Resistors → MF0S4FFE024KIT

## Coated Type Kit Resistors (MFR)

### Environment Related Substance

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and Halogen free.

Ozone layer depleting substances.

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFCs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

### Storage Condition

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of  $25^{\circ}\text{C} \pm 5^{\circ}\text{C}$  and a relative humidity of  $60\%\text{RH} \pm 10\%\text{RH}$

Even within the above guarantee periods, do not store these products in the following conditions. Otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

1. In salty air or in air with a high concentration of corrosive gas, such as  $\text{Cl}_2$ ,  $\text{H}_2\text{S}$ ,  $\text{NH}_3$ ,  $\text{SO}_2$ , or  $\text{NO}_2$
2. In direct sunlight

**Coated Type Kit Resistors (MFR)**

**PRODUCT: MF 1/4W-S 1% (1.85x3.5) E24 Series (122 Values)**

NO.	Value
1	0R
2	10R
3	11R
4	12R
5	13R
6	15R
7	16R
8	18R
9	20R
10	22R
11	24R
12	27R
13	30R
14	33R
15	36R
16	39R
17	43R
18	47R
19	51R
20	56R
21	62R
22	68R
23	75R
24	82R
25	91R
26	100R
27	110R
28	120R
29	130R
30	150R
31	160R
32	180R
33	200R
34	220R
35	240R

NO.	Value
36	270R
37	300R
38	330R
39	360R
40	390R
41	430R
42	470R
43	510R
44	560R
45	620R
46	680R
47	750R
48	820R
49	910R
50	1K
51	1K1
52	1K2
53	1K3
54	1K5
55	1K6
56	1K8
57	2K
58	2K2
59	2K4
60	2K7
61	3K
62	3K3
63	3K6
64	3K9
65	4K3
66	4K7
67	5K1
68	5K6
69	6K2
70	6K8

NO.	Value
71	7K5
72	8K2
73	9K1
74	10K
75	11K
76	12K
77	13K
78	15K
79	16K
80	18K
81	20K
82	22K
83	24K
84	27K
85	30K
86	33K
87	36K
88	39K
89	43K
90	47K
91	51K
92	56K
93	62K
94	68K
95	75K
96	82K
97	91K
98	100K
99	110K
100	120K
101	130K
102	150K
103	160K
104	180K
105	200K

NO.	Value
106	220K
107	240K
108	270K
109	300K
110	330K
111	360K
112	390K
113	430K
114	470K
115	510K
116	560K
117	620K
118	680K
119	750K
120	820K
121	910K
122	1M