



Features:

Universal AC input / Full range

Protections: Short circuit / Overload / Over voltage

Cooling by free air convection LED indicator for power on 100% full load burn-in test

All using 105 long life electrolytic capacitors Withstand 300VAC surge input for 5 second

High operating temperature up to 70

Withstand 5G vibration test

No load power consumption<0.5W

High efficiency, long life and high reliability

3 years warranty





CBCE

SPECIFICATION

MODEL		RS-25-3.3	RS-25-5	RS-25-12	RS-25-15	RS-25-24	RS-25-48	
OUTPUT	DC VOLTAGE	3.3V	5V	12V	15V	24V	48V	
	RATED CURRENT	6A	5A	2.1A	1.7A	1.1A	0.57A	
	CURRENT RANGE	0 ~ 6A	0 ~ 5A	0 ~ 2.1A	0 ~ 1.7A	0 ~ 1.1A	0 ~ 0.57A	
	RATED POWER	19.8W	25W	25.2W	25.5W	26.4W	27.36W	
	RIPPLE & NOISE (max.) Note.2	80mVp-p	80mVp-p	120mVp-p	120mVp-p	120mVp-p	200mVp-p	
	VOLTAGEADJ. RANGE	2.85 ~ 3.6V	4.75 ~ 5.5V	10.8 ~ 13.2V	13.5 ~ 16.5V	22 ~ 27.6V	42 ~ 54V	
	VOLTAGE TOLERANCE Note.3	± 3.0%	± 2.0%	± 1.0%	± 1.0%	± 1.0%	± 1.0%	
	LINE REGULATION Note.4	± 0.5%	± 0.5%	± 0.5%	± 0.5%	± 0.5%	± 0.5%	
	LOAD REGULATION Note.5	± 2.0%	± 1.0%	± 0.5%	± 0.5%	± 0.5%	± 0.5%	
	SETUP, RISETIME	1800ms, 23ms/230VAC 4000ms, 30ms/115VAC at full load						
	HOLD UP TIME (Typ.)	80ms/230VAC 14ms/115VAC at full load						
INPUT	VOLTAGERANGE	88 ~ 264VAC 125 ~ 373VDC (Withstand 300VAC surge for 5sec. Without damage)						
	FREQUENCY RANGE	47 ~ 63Hz						
	EFFICIENCY(Typ.)	73.5%	78.5%	81.5%	83.5%	86%	85%	
	AC CURRENT (Typ.)	0.7A/115VAC 0.4A/230VAC						
	INRUSH CURRENT (Typ.)	COLD START 30A/230VAC						
	LEAKAGE CURRENT	<2mA / 240VAC						
PROTECTION		110 ~ 180% rated output power						
	OVERLOAD	Protection type: Hiccup mode, recovers automatically after fault condition is removed						
	OVER VOLTAGE	3.8 ~ 4.45V	5.75 ~ 6.75V	13.8 ~ 16.2V	17.25 ~ 20.25V	27.6 ~ 32.4V	55.2 ~ 64.8V	
	OVER VOLIAGE	Protection type : Shut off o/p voltage, clamping byzener diode						
ENVIRONMENT	WORKING TEMP.	-20 ~ +70 (Refer to "Derating Curve")						
	WORKING HUMIDITY	20 ~ 90% RH non-condensing						
	STORAGE TEMP., HUMIDITY	-40 ~ +85 , 10 ~ 95% RH						
	TEMP. COEFFICIENT	± 0.03%/ (0~50)						
	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, period for 60min. each along X, Y, Z axes						
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1 approved						
SAFETY &	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC						
EMC	ISOLATION RESISTANCE I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25 / 70% RH							
(Note 6)	EMC EMISSION	Compliance to EN55022 (CISPR22) Class B, EN61000-3-2,-3						
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, light industry level, criteriaA						
OTHERS	MTBF	309.7Khrs min. MIL-HDBK-217F (25)						
	DIMENSION	78*51*28mm (L*W*H)						
	PACKING	0.2Kg; 60pcs/13Kg/0	0.46CUFT					
NOTE	Ripple & noise are measured Tolerance : includes set up Line regulation is measured Load regulation is measured The power supply is conside EMC directives. For guidan	All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25 of ambient temperature. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. Tolerance: includes set up tolerance, line regulation and load regulation. Line regulation is measured from low line to high line at rated load. Load regulation is measured from 0% to 100% rated load. Load regulation is measured from 0% to 100% rated load. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)						



