

Conforms to Regulation (EC) No. 1907/2006 (REACH), Annex II, as amended by Commission Regulation (EU) 2015/830 - United Kingdom (UK)

# SAFETY DATA SHEET

Sn99Cu1 3.25mm

## SECTION 1: Identification of the substance/mixture and of the company/ undertaking

### 1.1 Product identifier

**Product name** : Sn99Cu1 3.25mm  
**Product code** : 20714  
**Product type** : Massive metal.

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses
Industrial applications.
Material uses
soldering
Uses advised against
Not applicable.

### 1.3 Details of the supplier of the safety data sheet

**e-mail address of person responsible for this SDS** : Europeanregulatory@macdermid.com

**Supplier** : Alpha Assembly Solutions Netherlands B.V.  
Energiestraat 21  
P.O. Box 5018  
1410 AA  
Naarden  
The Netherlands

**Information contact** : Tel. No.: +31 (0) 356955411  
Fax No.: +31 (0) 356948451  
E-Mail: salesEU@AlphaAssembly.com

**1.4 Emergency telephone number**

**National advisory body/Poison Centre**

**Telephone number** :  
**Supplier**  
**Telephone number** : Chemcare24: +44 1235 239670  
**Hours of operation** : 24/7

**SECTION 2: Hazards identification**

**2.1 Classification of the substance or mixture**

**Product definition** : Mixture  
**Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS] \***  
 Not classified.

The product is not classified as hazardous according to Regulation (EC) 1272/2008 as amended.  
 See Section 11 for more detailed information on health effects and symptoms.

**2.2 Label elements**

**Signal word** : No signal word.  
**Hazard statements** :  No known significant effects or critical hazards.  
**Precautionary statements**  
**Prevention** :  Not applicable.  
**Response** :  Not applicable.  
**Storage** :  Not applicable.  
**Disposal** :  Not applicable.  
**Supplemental label elements** : Not applicable.

**2.3 Other hazards**

**Other hazards which do not result in classification** : None known.

**SECTION 3: Composition/information on ingredients**

**3.2 Mixtures** : Mixture

Product/ingredient name	Identifiers	%	Regulation (EC) No. 1272/2008 [CLP] *	Type
<input checked="" type="checkbox"/> copper	REACH #: 01-2119486474-28 EC: 231-141-8 CAS: 7440-31-5	≥90	Not classified.	[2]
	REACH #: 01-2119480154-42 EC: 231-159-6 CAS: 7440-50-8	≤3	Not classified.	[2]

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

Type

- [1] Substance classified with a health or environmental hazard
- [2] Substance with a workplace exposure limit
- [3] Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII
- [4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII
- [5] Substance of equivalent concern

Occupational exposure limits, if available, are listed in Section 8.

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

- Eye contact** : Get medical attention if any damage to the eye is caused by the metal.
- Inhalation** : Not applicable.
- Skin contact** : Flush contaminated skin with plenty of water. Cuts should be treated promptly and covered.
- Ingestion** : Not applicable.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

### 4.2 Most important symptoms and effects, both acute and delayed

#### Potential acute health effects

- Eye contact** : Not applicable.
- Inhalation** : Not applicable.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : Not applicable.

#### Over-exposure signs/symptoms

- Eye contact** : No specific data.
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

### 4.3 Indication of any immediate medical attention and special treatment needed

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

### 5.2 Special hazards arising from the substance or mixture

- Hazards from the substance or mixture** : No specific fire or explosion hazard.
- Hazardous combustion products** : Decomposition products may include the following materials:  
metal oxide/oxides

### 5.3 Advice for firefighters

- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
- Special protective equipment for fire-fighters** : No special protection is required.



## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

**For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Put on appropriate protective equipment.

**For emergency responders** : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

**6.2 Environmental precautions** : No specific hazard.

### 6.3 Methods and material for containment and cleaning up

**Small spill** : Restack safely. Take care with items that are sharp or heavy.

**Large spill** : Restack safely. Take care with items that are sharp or heavy.

**6.4 Reference to other sections** : See Section 1 for emergency contact information.  
See Section 8 for information on appropriate personal protective equipment.  
See Section 13 for additional waste treatment information.

## SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 7.1 Precautions for safe handling

**Protective measures** : Put on appropriate personal protective equipment (see Section 8). Take care with items that are sharp or heavy.

**Advice on general occupational hygiene** : Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

### 7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations.

### 7.3 Specific end use(s)

Industrial applications.  
soldering

## SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker exposure or environmental releases.

### 8.1 Control parameters

#### Occupational exposure limits

Product/ingredient name	Exposure limit values
tin  copper	<p><b>EH40-OES (United Kingdom (UK), 2002).</b> TWA: 2 mg/m<sup>3</sup> 8 hours. STEL: 4 mg/m<sup>3</sup> 15 minutes.</p> <p><b>EH40/2005 WELs (United Kingdom (UK), 12/2011). Notes: as Cu</b> STEL: 2 mg/m<sup>3</sup>, (as Cu) 15 minutes. Form: Dusts and Mists TWA: 1 mg/m<sup>3</sup>, (as Cu) 8 hours. Form: Dusts and Mists TWA: 0.2 mg/m<sup>3</sup>, (as Cu) 8 hours. Form: Fume</p>

**Recommended monitoring procedures** : Not applicable.

#### DNELs/DMELs



**SECTION 8: Exposure controls/personal protection**

No DNELs/DMELs available.

**PNECs**

No PNECs available

**8.2 Exposure controls**

**Appropriate engineering controls** : No special ventilation requirements.

**Individual protection measures**

**Hygiene measures** : Wash thoroughly after handling.

**Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields. Recommended: safety glasses with side-shields

**Skin protection**

**Hand protection** : Use strong, cut-resistant gloves suitable for handling metals. < 1 hour (breakthrough time): disposable vinyl

**Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product. Recommended: overall

**Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Respiratory protection** : Not applicable. Recommended: None assigned.

**Environmental exposure controls** : Not applicable.

**SECTION 9: Physical and chemical properties****9.1 Information on basic physical and chemical properties****Appearance**

**Physical state** : Solid.

**Colour** : Silvery.

**Odour** : None.

**Odour threshold** : Not available.

**pH** : Not available.

**Melting point/freezing point** : 228 to 250°C

**Initial boiling point and boiling range** : Not available.

**Flash point** : [Product does not sustain combustion.]

**Evaporation rate** : Not available.

**Flammability (solid, gas)** : Not available.

**Upper/lower flammability or explosive limits** : Not available.

**Vapour pressure** : Not available.

**Vapour density** : Not available.

**Relative density** : 5.8 g/cm<sup>3</sup> [20°C]

**Solubility(ies)** : Insoluble in the following materials: cold water and hot water.

**Partition coefficient: n-octanol/water** : Not available.

**Auto-ignition temperature** : Not available.

**Decomposition temperature** : Not available.

**SECTION 9: Physical and chemical properties**

<b>Viscosity</b>	: Not available.
<b>Explosive properties</b>	: Not available.
<b>Oxidising properties</b>	: Not available.

**9.2 Other information**

<b>VOC content</b>	: 0 % (w/w)
--------------------	-------------

No additional information.

**SECTION 10: Stability and reactivity**

<b>10.1 Reactivity</b>	: No specific data.
------------------------	---------------------

<b>10.2 Chemical stability</b>	: The product is stable.
--------------------------------	--------------------------

<b>10.3 Possibility of hazardous reactions</b>	: Under normal conditions of storage and use, hazardous reactions will not occur.
--	---

<b>10.4 Conditions to avoid</b>	: No specific data.
---------------------------------	---------------------

<b>10.5 Incompatible materials</b>	: See Section 10.1.
------------------------------------	---------------------

<b>10.6 Hazardous decomposition products</b>	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.
--	--

**SECTION 11: Toxicological information****11.1 Information on toxicological effects****Acute toxicity**

<b>Conclusion/Summary</b>	: Not available.
---------------------------	------------------

**Acute toxicity estimates**

Not available.

**Irritation/Corrosion**

<b>Conclusion/Summary</b>	: Not available.
---------------------------	------------------

**Sensitisation**

<b>Conclusion/Summary</b>	: Not available.
---------------------------	------------------

**Mutagenicity**

<b>Conclusion/Summary</b>	: Not available.
---------------------------	------------------

**Carcinogenicity**

<b>Conclusion/Summary</b>	: Not available.
---------------------------	------------------

**Reproductive toxicity**

<b>Conclusion/Summary</b>	: Not available.
---------------------------	------------------

**Teratogenicity**

<b>Conclusion/Summary</b>	: Not available.
---------------------------	------------------

**Specific target organ toxicity (single exposure)**

Not available.

**Specific target organ toxicity (repeated exposure)**

Not available.

**Aspiration hazard**

Not available.



## SECTION 11: Toxicological information

**Information on likely routes of exposure** : Not available.

### Symptoms related to the physical, chemical and toxicological characteristics

**Eye contact** : No specific data.  
**Inhalation** : No specific data.  
**Skin contact** : No specific data.  
**Ingestion** : No specific data.

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

#### Short term exposure

**Potential immediate effects** : Not available.  
**Potential delayed effects** : Not available.

#### Long term exposure

**Potential immediate effects** : Not available.  
**Potential delayed effects** : Not available.

#### Potential chronic health effects

Not available.

**Conclusion/Summary** : Not available.  
**General** : No known significant effects or critical hazards.  
**Carcinogenicity** : No known significant effects or critical hazards.  
**Mutagenicity** : No known significant effects or critical hazards.  
**Teratogenicity** : No known significant effects or critical hazards.  
**Developmental effects** : No known significant effects or critical hazards.  
**Fertility effects** : No known significant effects or critical hazards.

**Other information** : Not available.

## SECTION 12: Ecological information

### 12.1 Toxicity

**Conclusion/Summary** : Not available.

### 12.2 Persistence and degradability

**Conclusion/Summary** : Not available.

### 12.3 Bioaccumulative potential

Not available.

### 12.4 Mobility in soil

**Soil/water partition coefficient (K<sub>oc</sub>)** : Not available.  
**Mobility** : Not available.

### 12.5 Results of PBT and vPvB assessment

**PBT** : Not applicable.  
**vPvB** : Not applicable.

## SECTION 12: Ecological information

**12.6 Other adverse effects** : No known significant effects or critical hazards.

## SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 13.1 Waste treatment methods

#### Product

**Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

**Hazardous waste** : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 2008/98/EC.

#### European waste catalogue (EWC)

Waste code	Waste designation
10 08 11	dross and skimmings other than those mentioned in 10 08 10

#### Packaging

**Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

**Special precautions** : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues.

## SECTION 14: Transport information

	ADR/RID	IMDG	IATA
<b>14.1 UN number</b>	Not regulated.	Not regulated.	Not regulated.
<b>14.2 UN proper shipping name</b>	-	-	-
<b>14.3 Transport hazard class(es)</b>	-	-	-
<b>14.4 Packing group</b>	-	-	-
<b>14.5 Environmental hazards</b>	No.	No. Not a pollutant.	No.
<b>Additional information</b>	-	-	The environmentally hazardous substance mark may appear if required by other transportation regulations.

**14.6 Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.



**SECTION 14: Transport information**

**14.7 Transport in bulk according to Annex II of Marpol and the IBC Code** : Not available.

**SECTION 15: Regulatory information****15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****EU Regulation (EC) No. 1907/2006 (REACH)****Annex XIV - List of substances subject to authorisation****Annex XIV**

None of the components are listed.

**Substances of very high concern**

None of the components are listed.

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

**Other EU regulations**

**Europe inventory** : All components are listed or exempted.

**Industrial emissions (integrated pollution prevention and control) - Air** : Listed

**Industrial emissions (integrated pollution prevention and control) - Water** : Listed

**Ozone depleting substances (1005/2009/EU)**

Not listed.

**Prior Informed Consent (PIC) (649/2012/EU)**

Not listed.

**Seveso Directive (2012/18/EU)**

This product is not controlled under the Seveso Directive.

**International regulations****Stockholm Convention on Persistent Organic Pollutants (850/2004)**

Not listed.

**International lists**

Mixture

**National inventory**

**Australia** : All components are listed or exempted.

**Canada** : All components are listed or exempted.

**China** : All components are listed or exempted.

**Japan** : **Japan inventory (ENCS)**: Not determined.  
**Japan inventory (ISHL)**: Not determined.

**Malaysia** : All components are listed or exempted.

**New Zealand** : All components are listed or exempted.

**Philippines** : All components are listed or exempted.

**Republic of Korea** : All components are listed or exempted.

**Taiwan** : All components are listed or exempted.



## SECTION 15: Regulatory information

- Turkey** : All components are listed or exempted.  
**United States** : All components are listed or exempted.

**15.2 Chemical safety assessment** : This product contains substances for which Chemical Safety Assessments are still required.

## SECTION 16: Other information

✔ Indicates information that has changed from previously issued version.

**Abbreviations and acronyms** :

- ATE = Acute Toxicity Estimate
- CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
- DMEL = Derived Minimal Effect Level
- DNEL = Derived No Effect Level
- EUH statement = CLP-specific Hazard statement
- PBT = Persistent, Bioaccumulative and Toxic
- PNEC = Predicted No Effect Concentration
- RRN = REACH Registration Number
- vPvB = Very Persistent and Very Bioaccumulative

### Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Not classified.	

### Full text of abbreviated H statements

Not applicable.

### Full text of classifications [CLP/GHS]

Not applicable.

**Date of printing** : 11/02/2019  
**Date of issue/ Date of revision** : 11/03/2018  
**Date of previous issue** : 08/08/2017  
**Version** : 3.2

### Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Alpha Assembly Solutions SDS CLP Europe