

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING**1.1 Product identifier**

Trade name : TSE 397C
REACH Registration No. : not applicable

1.2 Relevant identified uses of the substance or mixture and uses advised against

1.2.1 Usage : Silicone Elastomer
1.2.2 Uses advised against : None known.

1.3 Details of the supplier of the safety data sheet

Company: : Momentive Performance Materials GmbH
Chempark Leverkusen Gebaeude V7
DE - 51368 Leverkusen
Telephone : + 40 213044229
Information contact: : MomentiveEMEA.productsteward@momentive.com

1.4 Emergency telephone

24 Hour Emergency Telephone : Europe, Israel & All other: +44 (0) 1235239670; Middle East:+44 (0) 1235239671

2. HAZARDS IDENTIFICATION**2.1 Classification of the substance or mixture:****Classification according to Regulation (EC) No 1272/2008 as amended**

Chronic hazards to the aquatic environment Category 3; H412;

Classification according to Directive 67/548/EEC or 1999/45/EC as amended:

Dangerous for the environment; R52/53;

2.2 Label elements**GHS-Labeling Regulation (EC) No. 1272/2008:**

Hazard pictograms : No data available

Hazard statements

H412 Harmful to aquatic life with long lasting effects.

Precautionary Statement - Prevention:

P273 Avoid release to the environment.

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

Precautionary Statement - Disposal:

P501 Dispose of contents/container to an approved incineration

Labelling according to EC Directives

R-phrase(s)	: R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
S-phrase(s)	: S60	This material and its container must be disposed of as hazardous waste.

2.3 Other hazards

None known.

TSE 397CVersion 3.3
Revision date 12.12.2012Print Date 26.01.2015
M00000007078**3. COMPOSITION/INFORMATION ON INGREDIENTS****Product description / chemical characterization:** Mixture of polydimethylsiloxanes, fillers and cross-linkers.**Hazardous Component(s)**

Chemical name	CAS-No.; EC No.; REACH Registration No.	Concentration %	EU Classification	Regulation (EC) No. 1272/2008
CYCLOPENTYLSILAZANE-AMINOSILOXANE COPOLYMER, METHOXY TERMINATED	134759-20-9; -; Not Applicable	$\geq 0,000$ - $< 5,000$	Xi;R38, R41;	Category 1; Eye Dam.; H318; Category 2; Skin Corr.; H315;
gamma-Aminopropyltriethoxysilane	919-30-2; 213-048-4; 01-2119480479-24-XXXX;	$\geq 0,100$ - $< 1,000$	C;R34, R22, R43;	Category 4; Acute Tox.; H302; Category 1B; Skin Corr.; H314; Category 1; Skin Sens.; H317;
Dibutyltin Dilaurate	77-58-7; 201-039-8; 01-2119496068-27-XXXX;	$\geq 0,250$ - $< 0,500$	T, C, N;R48/25, R34, R43, R60, R61, R68, R50/53;	Category 1; Aquatic Acute; H400; Category 1; Aquatic Chronic; H410; Category 1; STOT SE; H370; Category 1; STOT RE; H372; Category 1B; Repr.; H360FD; Category 1C; Skin Corr.; H314; Category 2; Muta.; H341; Category 1; Skin Sens.; H317; Category 1; Eye Dam.; H318;

4. FIRST AID MEASURES**4.1 Description of first aid measures**

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

- Inhalation : Move to fresh air.
- Skin contact : After contact with skin, remove product mechanically. Wash area with soap and water.
- Eye contact : Rinse the eye with water immediately. If eye irritation persists: Get medical advice/attention.
- Ingestion : Rinse mouth. Consult a physician for specific advice.

4.2 Most important symptoms and effects, both acute and delayed

None known.

4.3 Indication of any immediate medical attention and special treatment needed

None known.

5. FIRE-FIGHTING MEASURES

5.1 Extinguishing media

- Suitable extinguishing media : All standard extinguishing agents are suitable.
- Unsuitable extinguishing media : None known.

5.2 Special hazards arising from the substance or mixture:

None known.

5.3 Advice for firefighters:

Use standard firefighting procedures and consider the hazards of other involved materials. Prevent runoff from fire control or dilution from entering streams, sewers, or drinking water supply.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures:

Provide adequate ventilation. Use personal protective equipment.

6.2 Environmental precautions:

Prevent runoff from entering drains, sewers, or streams.

6.3 Methods and material for containment and cleaning up:

Use mechanical handling equipment. Shovel up and place in a container for salvage or disposal.

TSE 397CVersion 3.3
Revision date 12.12.2012Print Date 26.01.2015
M00000007078**7. HANDLING AND STORAGE****7.1 Precautions for safe handling**

Handling : Methanol is formed during processing. Wear appropriate personal protective equipment.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a cool, well-ventilated place.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION**8.1 Control parameters****Occupational exposure limits**

Components	CAS-No.	Occupational exposure limits
SILICA	7631-86-9	Basis: EH40 WEL; Update: 2005; Time Weighted Average (TWA): 6 mg/m ³ ; Inhalable dust. Basis: EH40 WEL; Update: 2005; Time Weighted Average (TWA): 2,4 mg/m ³ ; Respirable dust.
DIBUTYLTIN DILAURATE	77-58-7	Basis: EH40 OES; Update: 2003; Time Weighted Average (TWA): 0,1 mg/m ³ Basis: EH40 OES; Update: 2003; Short Term Exposure Limit (STEL): 0,2 mg/m ³ Basis: EH40 OES; Update: 2003; Skin designation: ; Can be absorbed through the skin. Basis: EH40 WEL; Update: 2005; Time Weighted Average (TWA): 0,1 mg/m ³ Basis: EH40 WEL; Update: 2005; Short Term Exposure Limit (STEL): 0,2 mg/m ³ Basis: EH40 WEL; Update: 2005; Skin designation: ; Can be absorbed through the skin.

DNEL-Values:

No data available

PNEC-Values:

No data available

8.2 Exposure controls

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

Personal protective equipment (ppe)

- Hand protection : Advice: There is no risk to health due to contact with the chemical. Use hand protection to prevent mechanically injuries.
- Eye protection : Safety glasses with side-shields conforming to EN166
- Hygiene measures : Avoid contact with eyes, skin, and clothing.
Wash hands after handling.
When using do not eat or drink.
- Protective Measures : Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES**9.1 Information on basic physical and chemical properties**

- Appearance : Liquid
Colorless
- Odor : Faint
- Odor Threshold : No data available.
- pH : No data available.
- Melting Point : No data available.
- Boiling point/boiling range :
Flash Point : 198 °C
Evaporation Rate : No data available.
- Lower explosion limit : Not applicable
- Upper explosion limit : Not applicable
- Vapour pressure :
No data available.
- Vapor Density : No data available.
- Density : >1,04 g/cm³ at 23 °C
Solubility(ies) : Insoluble
- Solubility in Water : Insoluble
- Solubility in other solvents : No data available.
- Partition Coefficient: n-octanol/water : No data available.
- Autoignition Temperature : No data available.

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

Thermal decomposition : Note: No decomposition if stored and applied as directed.

Viscosity, dynamic : 50.000 mPa.s at 23 °C

Viscosity, kinematic : > 7 mm²/s
at 40 °C

Explosive properties : No data available.

Oxidizing properties : No data available.

10. STABILITY AND REACTIVITY**10.1 Reactivity:**

No data available

10.2 Chemical stability:

No data available

10.3 Possibility of hazardous reactions:

Reacts with water liberating small amounts of methanol.; No dangerous reaction if used as recommended.

10.4 Conditions to avoid:

None known.

10.6 Hazardous decomposition products:No data available

11. TOXICOLOGICAL INFORMATION**11.1 Information on toxicological effects**

Human experience : Our Experience shows that our Silicone Elastomer products can be handled without risk to health if used properly and if the usual precautions for industrial hygiene are observed.

12. ECOLOGICAL INFORMATION**12.1 Toxicity**

Product: No data available

12.2 Persistence and degradability

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

Elimination information (persistence and degradability)

Product: No data available

12.3 Bioaccumulation

Product: No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product: No data available

12.6 Other adverse effects

Additional ecological information : Ecotoxicological data for this product is not available.

13. DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Product : Can be incinerated when in compliance with local regulations.

Contaminated packaging : Dispose of as unused product.

14. TRANSPORT INFORMATION

Further Information : This product is not regarded as dangerous goods according to the national and international regulations on the transport of dangerous goods.
Protect from moisture.
Keep away from food, foodstuff, acids and bases.
keep away from odour sensitive materials

15. REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

None known.

15.2 Chemical safety assessment

Inventories

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

Australia Inventory of Chemical Substances (AICS)	q (quantity restricted)
Canada DSL Inventory	q (quantity restricted)
EU list of existing chemical substances	y (positive listing)
Japan Inventory of Existing & New Chemical Substances (ENCS)	y (positive listing)
China Inventory of Existing Chemical Substances	y (positive listing)
Korea Existing Chemicals Inventory (KECI)	y (positive listing)
Canada NDSL Inventory	n (Negative listing)
Philippines Inventory of Chemicals and Chemical Substances (PICCS)	y (positive listing)
TSCA list	y (positive listing)
New Zealand Inventory of Chemicals	n (Negative listing)

For inventories that are marked as quantity restricted or special cases, please contact Momentive.

16. OTHER INFORMATION**Wording of the R-phrases and H-statements in section 2 and 3**

H412: Harmful to aquatic life with long lasting effects.

H318: Causes serious eye damage.

H315: Causes skin irritation.

H302: Harmful if swallowed.

H314: Causes severe skin burns and eye damage.

H317: May cause an allergic skin reaction.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H370: Causes damage to organs.

H372: Causes damage to organs through prolonged or repeated exposure.

H360FD: May damage fertility. May damage the unborn child.

H314: Causes severe skin burns and eye damage.

H341: Suspected of causing genetic defects.

H317: May cause an allergic skin reaction.

H318: Causes serious eye damage.

TSE 397C

Version 3.3
Revision date 12.12.2012

Print Date 26.01.2015
M00000007078

R22	Harmful if swallowed.
R34	Causes burns.
R38	Irritating to skin.
R41	Risk of serious damage to eyes.
R43	May cause sensitisation by skin contact.
R48/25	Toxic: danger of serious damage to health by prolonged exposure if swallowed.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R60	May impair fertility.
R61	May cause harm to the unborn child.
R68	Possible risk of irreversible effects.

Momentive Products are intended for industrial application only.
They are not intended for specific medical applications, neither for long-lasting (> 30 days) implantation into the human body, injected or directly ingested, nor for the manufacture of multiple usable contraceptives.

Further Information

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.