


Insulation Film Type for Temperature Sensing/Compensation

Features


- 1. RoHS compliant
- 2. Halogen-Free (HF) series are available
- 3. Radial leaded insulation film coated
- 4. Operating temperature range: -40°C~+100°C
- 5. Agency recognition: UL / cUL

Recommended Applications


- 1. Home appliances
- 2. Computers
- 3. Battery packs



Part Number Code



Structure and Dimensions





Insulation Film Type for Temperature Sensing/Compensation

■ Electrical Characteristics

Part No.	Zero Power Resistance at 25°C	Tolerance of R ₂₅	B Value		Tolerance of B value	Max. Power Dissipation at 25°C	Dissipation Factor	Thermal Time Constant	Operating Temperature Range	Safety Approvals UL cUL	
	R ₂₅ (KΩ)	(±%)	((K)	(±%)	P _{max} (mW)	ð(mW/°C)	τ (Sec.)	TL~Tu(°C)	٦	"
TTF3A502[]34D*	5	1, 2, 3, 5	3, 25/85	3435	2, 3		Approx. 0.7	Approx. 5	-40 ~ +100	V	√
TTF3A103[]34D*	10			3435	1, 2, 3	3.5				1	√
TTF3A203[]34D*	20			3435						4	V
TTF3A223[]34D*	22			3435						1	√
TTF3A303[]39H*	30			3975						1	√
TTF3A104□34D*	100			3435	2,3					1	1


Note 1: ☐ = Tolerance of R₂₅

* = Tolerance of B value

Note 2: UL/cUL File No: E138827

Note 3: Special specifications are available upon request.

Max. Power Dissipation Derating Curve



Ambient temperature (℃)

T_U: Maximum operating temperature (℃)

 T_L : Minimum operating temperature (°C)

For example:

Ambient temperature(Ta) = 55℃


Maximum operating temperature(T_U) = 100°C

 $P_{Ta} = (T_U-Ta)/(T_U-25) \times Pmax = 60\% Pmax$




Insulation Film Type for Temperature Sensing/Compensation

R-T Characteristic Curves



Soldering Recommendation

Wave Soldering Profile



Recommended Reworking Conditions with Soldering Iron

ltem	Conditions		
Temperature of Soldering Iron-tip	360°C (max.)		
Soldering Time	3 sec. (max.)		
Distance from Coating	Do not touch film bottom		



Insulation Film Type for Temperature Sensing/Compensation

Reliability

Item	Standard	Test conditions / Methods	Specifications
Tensile Strength of Terminals	IEC 60068-2-21	Gradually apply the specified force and keep the unit fixed for 10±1 sec Terminal cross-sectional area Force (mm²) (Kg) 0.05 <s≤01 0.25<="" td=""><td>No visible damage</td></s≤01>	No visible damage
Bending Strength of Terminals	IEC 60068-2-21	Hold specimen and apply the force specified below to each lead. Bend the specimen to 90°, and then return to the original position Repeat the procedure in the opposite direction.	No visible damage
Solderability	IEC 60068-2-20	245 ± 3°€ , 3 ± 0.3 sec.	At least 95% of terminal electrode is covered by new solder
Resistance to Soldering Heat	IEC 60068-2-20	260 ± 3℃, 10 ± 1 sec.	No visible damage ∆R ₂₅ /R ₂₅ ≤ 3 %
High Temperature Storage	IEC 600C68-2-2	100 ± 5℃, 1000 ± 24 hrs	No visible damage △R ₂₅ /R ₂₅ ≤ 5 %
Damp Heat, Steady State	IEC 60068-2-78	40 ± 2℃, 90~95% RH, 1000 ± 24 hrs	No visible damage <u>△</u> Rz/R₂5 ≨ 3 %
Rapid Change of Temperature	IEC 60068-2-14	The conditions shown below shall be repeated 5 cycles. Step Temperature (*C) Period (minutes) 1 -40 ± 5 30 ± 3 2 Room temperature 5 ± 3 3 100 ± 5 30 ± 3 4 Room temperature 5 ± 3	No visible damage △R ₂₅ /R ₂₅ ≨ 3 %
Max. Power Dissipation	IEC 60539-1	25 ± 5℃, Pmax. , 1000 ± 24 hrs	No visible damage ∆R ₂₅ /R ₂₅ ≤ 5 %

Packaging

Bulk Packing: 500 pcs/ bag

Warehouse Storage Conditions of Products

• Storage Conditions:

1. Storage Temperature: -10°C ~+40°C

2. Relative Humidity: \leq 75%RH

3. Keep away from corrosive almosphere and sunlight.

Period of Storage: 1 year