

Features

- 1 & 2 Pole relay range 46.52 2 Pole 8 A 46.61 - 1 Pole 16 A
- Socket mount or direct connection via Faston connectors
- AC coils & DC coils
- Available with: lockable test button, mechanical indicator & LED indicator
- 8 mm, 6 kV (1.2/50 µs) isolation, coil-contacts
- Cadmium Free contacts




46.52

• 2 Pole CO, 8 A • Plug-in/Solder terminals



• 1 Pole CO, 16 A • Plug-in/Faston 187



Mechanical life AC/DC

Operate/release time


Electrical life at rated load AC1

Ambient temperature range

Environmental protection Approvals (according to type)

Insulation between coil and contacts (1.2/50 µs)kV

Dielectric strength between open contacts V AC





10 · 106

100 · 10³

15/5

6 (8 mm)

1,000

-40 ... +70

RT II

RINA CALOUS VOE

FOR UL HORSEPOWER AND PILO SEE "General technical inform			
Contact specification			
Contact configuration		2 CO (DPDT)	1 CO (SPDT)
Rated current/Maximum pe	ak current A	8/15	16/25
Rated voltage/Maximum swit	ching voltage V AC	250/440	250/440
Rated load AC1	VA	2,000	4,000
Rated load AC15 (230 V A	AC) VA	350	750
Single phase motor rating (230 V AC) kW	0.37	0.55
Breaking capacity DC1: 30)/110/220 V A	6/0.5/0.15	12/0.5/0.15
Minimum switching load	mW (V/mA)	300 (5/5)	300 (5/5)
Standard contact material		AgNi	AgNi
Coil specification			
Nominal voltage (U_N)	V AC (50/60 Hz)	12 - 24 - 48 - 110	- 120 - 230 - 240
	V DC	12 - 24 - 48	- 110 - 125
Rated power	VA/W	1.2/0.5	1.2/0.5
Operating range	AC	(0.81.1)U _N	(0.81.1)U _N
	DC	(0.731.1)U _N	(0.731.1)U _N
Holding voltage	AC/DC	0.8U _N /0.4U _N	0.8U _N /0.4U _N
Must drop-out voltage	AC/DC	0.2U _N /0.1U _N	0.2U _N /0.1U _N
Technical data			

10 · 106

100 · 10³

10/3

6 (8 mm)

1,000

-40 ... +70

RT II

(1)


cycles

cycles



Ordering information


Example: 46 series Miniature industrial relay, 1 CO (SPDT), 24 V DC coil, lockable test button and mechanical indicator.



Selecting features and options: only combinations in the same row are possible. Preferred selections for best availability are shown in **bold**.

Туре	Coil version	Α	В	С	D
46.52	AC - DC	0 - 5	0	2 - 4	0
	AC	0 - 5	0	54	/
	DC	0 - 5	0	74	/
46.61	AC - DC	0 - 4 - 5	0	2 - 4	0
	AC	0 - 4 - 5	0	54	/
	DC	0 - 4 - 5	0	74	/

Descriptions: Options







Lockable test button and mechanical flag indicator (0040, 0054, 0074)

The dual-purpose Finder test button can be used in two ways:

<u>Case 1</u>) The plastic pip (located directly below the test button) remains intact. In this case, when the test button is pushed, the contacts operate. When the test button is released the contacts return to their former state.

<u>Case 2</u>) The plastic pip is broken-off (using an appropriate cutting tool). In this case, (in addition to the above function), when the test button is pushed and rotated, the contacts are latched in the operating state, and remain so until the test button is rotated back to its former position. In both cases ensure that the test button actuation is swift and decisive.




Technical data


Insulation according to EN 6181	0-1					
		1	pole		2 pole	
Nominal voltage of supply system	m V AC	230/400		230/400	230/400	
Rated insulation voltage	V AC	250	400	250	400	
Pollution degree		3	2	3	2	
Insulation between coil and cont	act set					
Type of insulation		Reinforced (8 m	m)	Reinforced (8	3 mm)	
Overvoltage category		III		III		
Rated impulse voltage	kV (1.2/50 μs)	6		6		
Dielectric strength	V AC	4,000		4,000		
Insulation between adjacent cont	tacts					
Type of insulation		_		Basic	Basic	
Overvoltage category	Overvoltage category		_		III	
Rated impulse voltage	kV (1.2/50 μs)	_		4	4	
Dielectric strength V AC		_		2,000	2,000	
Insulation between open contacts	s					
Type of disconnection		Micro-disconnec	tion	Micro-discon	nection	
Dielectric strength	V AC/kV (1.2/50 μs)	1,000/1.5				
Conducted disturbance immunity	•			i i		
Burst (550)ns, 5 kHz, on A1 -	A2	EN 61000-4-4 level 4 (4 kV))		
Surge (1.2/50 µs) on A1 - A2 (differential mode)	EN 61000-4-5 leve		level 3 (2 kV	level 3 (2 kV)	
Other data	46	5.61		46.52		
Bounce time: NO/NC ms		2/6		1/4		
Vibration resistance (10150)H	lz: NO/NC g	20/12		20/15		
Shock resistance	g	20		20		
Power lost to the environment	without contact current W	0.6		0.6		
	with rated current W	1.6		2		
Recommended distance between	relays mounted on PCB mm	≥ 5				

Contact specification


F 46 - Electrical life (AC) v contact current Type 46.52



F 46 - Electrical life (AC) v contact current Type 46.61



H 46 - Maximum DC1 breaking capacity



- When switching a resistive load (DC1) having voltage and current values under the curve, an electrical life of ≥ 100·10³ can be expected.
- In the case of DC13 loads, the connection of a diode in parallel with the load will permit a similar electrical life as for a DC1 load.
 Note: the release time for the load will be increased.



Coil specifications


DC coil data

Nominal	Coil	Operating range		Resistance	Rated coil
voltage	code				consumption
U _N		U_{min}	U _{max}	R	I at U _N
V		V	V	Ω	mA
12	9 .012	8.8	13.2	300	40
24	9 .024	17.5	26.4	1,200	20
48	9 .048	35	52.8	4,800	10
110	9 .110	80	121	23,500	4.7
125	9 .125	91.2	138	32,000	3.9


AC coil data

Nominal	Coil	Operatir	ıg range	Resistance	Rated coil
voltage	code				consumption
U _N		U _{min}	U _{max}	R	I at U _N
٧		V	٧	Ω	mA
12	8 .012	9.6	13.2	80	90
24	8 .024	19.2	26.4	320	45
48	8 .048	38.4	52.8	1,350	21
110	8 .110	88	121	6,900	9.4
120	8 .120	96	132	9,000	8.4
230	8 .230	184	253	28,000	5
240	8 .240	192	264	31,500	4.1

R 46 - DC coil operating range v ambient temperature



R 46 - AC coil operating range v ambient temperature




- 1 Max. permitted coil voltage.
- 2 Min. pick-up voltage with coil at ambient temperature.
- 1 Max. permitted coil voltage.
- 2 Min. pick-up voltage with coil at ambient temperature.

Accessories



Flange mount adaptor for relays types 46.52 and 46.61





046.05 with relay

046.05

46

14.4

35 mm rail adaptor for relays types 46.52 and 46.61

18.1




046.05






046.07 with relay








046.07 with relay

046.05 with relay



060.72



060.72



97 Series - Sockets and accessories for 46 series relays



Approvals (according to type):

(§ © ()








Screw terminal socket panel or 35 mm rail (EN 60715) mount	97.01 (blue) 97.01.0 (black	97.02 (blue) 97.02.0 (black)	
For relay type	46.61	46.52	
Accessories			
Plastic retain and release clip	09	7.01	
(supplied with socket - packaging code SPA)			
Identification tag	095	5.00.4	
8-way jumper link	095.18 (blue)	095.18.0 (black)	
Modules (see table below)	99.02		
Timer modules (see table below)	86.30		
Technical data			
Rated current	16 A - 250 V AC	8 A - 250 V AC	
Dielectric strength	6 kV (1.2/50 μs) between coil and contacts		
Protection category	IP 20		
Ambient temperature °C	-40+70 (see diagram L97)		
⊕ Screw torque Nm	0.8		
Wire strip length mm	8		
Max. wire size for 97.01 and 97.02 sockets	solid wire	stranded wire	
mm ²	1x6 / 2x2.5	1x4 / 2x2.5	
ÄWG	1x10 / 2x14	1x12 / 2x14	

L 97 - Rated current vs ambient temperature

(for 46.61 relay / 97.01 socket combination)







68.4

19.2




8-way jumper link for 97.01 and 97.02 sockets	095.18 (blue)	095.18.0 (black)
Rated values	10 A - 250 V	

4 14

2 12

NO





86 series timer module	
(1224)V AC/DC; Bi-function: AI, DI; (0.05s100h)	86.30.0.024.0000
(110125)V AC; Bi-function: AI, DI; (0.05s100h)	86.30.8.120.0000
(230240)V AC; Bi-function: AI, DI; (0.05s100h)	86.30.8.240.0000

Approvals







Approvals (according to type):

C CAL US

DC Modules with non-standard polarity (+A2) on request.

accordi	ng to) ty	pe):	CE	Œ	c FU ®US		
~~ ~~		1.			E146	•	1.1	07

99.02 coil indication and EMC suppression	modules for 97.01 and 97.02	sockets
Diode (+A1, standard polarity)	(6220)V DC	99.02.3.000.00
LED	(624)V DC/AC	99.02.0.024.59
LED	(2860)V DC/AC	99.02.0.060.59
LED	(110240)V DC/AC	99.02.0.230.59
LED + Diode (+A1, standard polarity)	(624)V DC	99.02.9.024.99
LED + Diode (+A1, standard polarity)	(2860)V DC	99.02.9.060.99
LED + Diode (+A1, standard polarity)	(110220)V DC	99.02.9.220.99
LED + Varistor	(624)V DC/AC	99.02.0.024.98
LED + Varistor	(2860)V DC/AC	99.02.0.060.98
LED + Varistor	(110240)V DC/AC	99.02.0.230.98
RC circuit	(624)V DC/AC	99.02.0.024.09
RC circuit	(2860)V DC/AC	99.02.0.060.09
RC circuit	(110240)V DC/AC	99.02.0.230.09
Residual current by-pass	(110240)V AC	99.02.8.230.07



97 Series - Sockets and accessories for 46 series relays




Approvals (according to type):


























86	series	timer	modul	е
/10	2 411	1 10 /	DC. D: [

** ******	
(1224)V AC/DC; Bi-function: AI, DI; (0.05s100h)	86.30.0.024.0000
(110125)V AC; Bi-function: AI, DI; (0.05s100h)	86.30.8.120.0000
(230240)V AC; Bi-function: AI, DI; (0.05s100h)	86.30.8.240.0000









Approvals (according to type):



DC Modules with non-standard polarity (+A2) on request.

99.02 coil indication and EMC suppression modules for 97.51 and 97.52 sockets					
Diode (+A1, standard polarity)	(6220)V DC	99.02.3.000.00			
LED	(624)V DC/AC	99.02.0.024.59			
LED	(2860)V DC/AC	99.02.0.060.59			
LED	(110240)V DC/AC	99.02.0.230.59			
LED + Diode (+A1, standard polarity)	(624)V DC	99.02.9.024.99			
LED + Diode (+A1, standard polarity)	(2860)V DC	99.02.9.060.99			
LED + Diode (+A1, standard polarity)	(110220)V DC	99.02.9.220.99			
LED + Varistor	(624)V DC/AC	99.02.0.024.98			
LED + Varistor	(2860)V DC/AC	99.02.0.060.98			
LED + Varistor	(110240)V DC/AC	99.02.0.230.98			
RC circuit	(624)V DC/AC	99.02.0.024.09			
RC circuit	(2860)V DC/AC	99.02.0.060.09			
RC circuit	(110240)V DC/AC	99.02.0.230.09			
Residual current by-pass	(110240)V AC	99.02.8.230.07			



97 Series - Sockets and accessories for 46 series relays




Approvals (according to type):










(°C)

L 97 - Rated current vs ambient temperature

(for 46.61 relay / 97.11 socket combination)







97.12 Approvals (according to type):

















Copper side view

Packaging codes

How to code and identify retaining clip and packaging options for sockets.

Example:

