


### RTD Extension Cable – 4 core PTFE



- PTFE insulated cable for extending Platinum Resistance Thermometers
- High temperature to 260°C, PTFE wrapped tape construction
- Can be used to extend 2, 3 or 4 wire RTD configurations
- Commonly use for Pt100Ω thermometers, also suitable with other types such as Pt130, Pt500 & Pt1000Ω
- 4 core PTFE insulated 7/0.2mm silver plated copper conductors, twisted cores, mylar tape, silver plated copper braided screen with PTFE insulated outer jacket
- Cores colour coded 2 x Red / 2 x White to IEC-751 with black outer jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, steam, gasses etc.
- Insulation rating -75°C to 260°C
- Supplied in 10 & 25 metre reel lengths

<u>No. of Strands</u>	<u>Product Code</u>	<u>Manufacturer's Part Number</u>	<u>Rapid Part Number</u>
7/0.2 mm	10M - 4 CORE CU 7/0.2 SCR PTFE	XE-2757-010	<b>61-3254</b>
7/0.2 mm	25M - 4 CORE CU 7/0.2 SCR PTFE	XE-2757-025	<b>61-3255</b>

Overall sheath Dimension (approx.)

3.5mmØ