



7W Axial Ceramic Resistors


Features:

- Self extinguishing
- Excellent flame and moisture resistance
- Extremely small study and mechanically safe
- Non-inductive types available for all Cermet Resistors
- Too low or too high ohmic values on Wire-wound & Power Film types can be supplied on a case to case basis









Part No.	Power rating at 70°C	Dimensions (mm)					Resistance Range	
		W ± 1	D ± 1	L ± 1	d ± 0.05	H ± 5	Wire-wound	Power Film
SQP-7W-J-XXX	7W	10	9	35	0.75	35	0.1Ω to 680Ω	681Ω to 200KΩ
Notes: Max Working Voltage: 500V								

Notes: Max Working Voltage: 500V Max Overload Voltage: 1000V

Performance Specifications:

Temperature Coefficient: $<20\Omega$: $\pm400PPM/^{\circ}C$; $\geq20\Omega$: $\pm350PPM/^{\circ}C$

Short Time Overload: $\pm (5.0\% + 0.05\Omega)$ Max, with no evidence of mechanical damage

Dieiectric Withstanding Voltage: No evidence of flashover, mechanical damage, arcing or insulation breakdown

Terminal Strength: No evidence of mechanical damage

Resistance to Soldering Heat: $\pm (1.0\% + 0.05\Omega)$ Max, with no evidence of mechanical damage

Solderability: Min. 95% coverage

Temperature Cycling: $\pm (2.0\% + 0.05\Omega)$ Max, with no evidence of mechanical damage $\pm (5.0\% + 0.05\Omega)$ Max, with no evidence of mechanical damage

Load Life in Humidity: Wire-wound $\pm (5.0\% + 0.05\Omega)$ Max

Power Film ≥ 100 K Ω : $\pm (5.0\% + 0.05\Omega)$ Max

≥100K Ω : ±(10.0% + 0.05 Ω) Max

Load Life: Wire-wound $\pm (5.0\% + 0.05\Omega)$ Max

Power Film $\geq 100 \text{K}\Omega$: $\pm (5.0\% + 0.05\Omega)$ Max

≥100K Ω : ±(10.0% + 0.05 Ω) Max