


TSE397

silicone adhesive sealant

ENGINEERED MATERIALS - CONSUMER ELECTRONICS



TSE397 is a one-component, fast cure, non-corrosive silicone adhesive sealant that cures on exposure to atmospheric moisture to form an elastic silicone rubber. TSE397 has a pourable consistency and excellent corrosion-free adhesion to metals, including copper, plastics, ceramics, glass, etc. without the use of primers.

Key Features and Typical Benefits

- non-corrosive to metals: meets MIL-A-46146B corrosion test
- fast cure
- low odor; releases an alcohol vapor during cure
- primerless adhesion to many substrates
- excellent high and low temperature resistance: from -55°C to 200°C
- excellent weatherability, ozone, and chemical resistance
- excellent electrical insulation properties
- UL94 HB recognized (File No: E56745): TSE397-B, TSE397-C, TSE397-W
- simple and easy-to-use one-component system

Potential Applications

- insulating adhesive seal and fixing for electrical and electronic parts.
- waterproof sealant for electrical, electronic and communication equipment
- general adhesive for metals, glass, plastics, etc.

Typical Physical Properties (JIS K 6249)

UNCURED PROPERTIES		
Appearance		Flowable paste
Viscosity (23°C)	Pa·s {P}	50 {50}
Tack Free Time (23°C)	min	10
Corrosion (MIL-A-46146B)		None
CURED PROPERTIES (7 days @ 23°C / 50%RH)		
Appearance		Elastic rubber
Density (23°C)	g/cm ³	1.04
Hardness (Type A)		13
Tensile Strength	MPa {kgf/cm ² }	1.2 {12}
Elongation	%	360
Adhesive Strength ⁽¹⁾	MPa {kgf/cm ² }	1.0 {10}
Thermal Conductivity ⁽²⁾	W/m·K	0.18
Volume Resistivity	MΩ·m {Ω·cm}	2.0x10 ⁷ {2.0x10 ¹⁵ }
Dielectric Strength	kV/mm	22
Dielectric Constant (60Hz)		2.9
Dielectric Loss (60Hz)		0.005

(1) Aluminum lap shear


(2) In-house test method

Typical property data values should not be used as specifications.


TSE397 silicone adhesive sealant

Curing Properties

Short-term






Long-term



TSE397 silicone adhesive sealant

Heat Resistance



TSE397 silicone adhesive sealant

Adhesion Performance

TSE392 has excellent bonding properties and adheres to many materials without primers. However, for significantly better adhesion on difficult-to-bond substrates, use of a primer is suggested. The following list of materials shows the quality of adherence of TSE392 used with ME121, ME123, YP9341, XP80-A5363 or without a primer.

Primer Selection

SUBSTRATE	NO PRIMER	ME121	ME123	YP9341 / XP80-A5363
Metals				
Copper	O	O		
Steel	O	O		
Mild Steel	O	O		
Brass	O	O		
Stainless Steel	O	O		
Pure Aluminum	O	O		
Corrosion-resistant Aluminum	O	O		
Galvanized Sheet Iron	O	O		
Tin Plate	O	O		
Plastics				
Acrylic Resin	O		O	
Phenolic Resin	O		O	
Epoxy Resin	O		O	
Polycarbonate	O ⁽¹⁾		O ⁽¹⁾	
Soft Polyvinyl Chloride	O		O	
Rigid Polyvinyl Chloride	O		O	
Polyester Film	O		O	
Melamine Resin	O		O	
Polystyrene	Δ		O	
Polyacetal	X		O	
PPE	O		O	
Unsaturated Polyester Resin	O		O	
Polyimide	O		O	
Nylon66	O		O	O ⁽²⁾
PBT	O		O	X
PPS	O		O	O ⁽²⁾
ABS Resin	O		O	
Polypropylene	X		X	O ⁽³⁾
Polyethylene	X		X	Δ ⁽³⁾
Polytetrafluoroethylene	X		X	X
Silicone Varnish Laminate	O		O	
Silicone Varnish Coated Glass Cloth	O		O	
Rubbers				
Chloroprene	Δ		O	
Nitril	Δ		O	
Styrene Butadiene	Δ		O	
Ethylene Propylene	Δ		O	
Silicone	O		O	
Others				
Glass	O	O		
Ceramics	O	O		
Wood	Δ ~ O	Δ ~ O		

Note:

O: Excellent (Cohesive failure, 100%)

Δ: Insufficient

X: Poor (Cohesive failure, 0%)

(1): It shows good adhesion but solvent crack may occur depending on the application. A preliminary adhesion test is recommended to confirm.

(2): YP9341

(3): XP80-A5363

TSE397 silicone adhesive sealant

Handling and Safety

- wear eye protection and protective gloves as required while handling the product.
- maintain adequate ventilation in the work place at all times.

Storage

- store in a cool, dry place out of direct sunlight.
- keep out of the reach of children.

Packaging and Colors

COLOR SUFFIX	COLOR	PACKAGING
-B	Black	100g tube available in case of 20 333ml cartridge available in case of 10 1kg can available in case of 10 18kg pail available
-C	Clear	100g tube available in case of 20 333ml cartridge available in case of 10 1kg can available in case of 10 18kg pail available
-W	White	100g tube available in case of 20 333ml cartridge available in case of 10 18kg pail available

TSE397 silicone adhesive sealant

Patent Status

Nothing contained herein shall be construed to imply the nonexistence of any relevant patents or to constitute the permission, inducement or recommendation to practice any invention covered by any patent, without authority from the owner of the patent.

Product Safety, Handling and Storage

Customers considering the use of this product should review the latest Material Safety Data Sheet and label for product safety information, handling instructions, personal protective equipment if necessary, and any special storage conditions required. Material Safety Data Sheets are available at www.momentive.com or, upon request, from any Momentive Performance Materials representative. Use of other materials in conjunction with Momentive Performance Materials products may require additional precautions. Please review and follow the safety information provided by the manufacturer of such other materials.

Limitations

Customers must evaluate Momentive Performance Materials products and make their own determination as to fitness of use in their particular applications.

TSE397 silicone adhesive sealant

Emergency Service

Momentive Performance Materials maintains an around-the-clock emergency service for its products. The American Chemistry Council (CHEMTREC) and CareChem24 International also maintain an around-the-clock emergency service for all chemical products:

<u>Location</u>	<u>Momentive Performance Materials Products</u>	<u>All Chemical Products</u>
Mainland U.S., Puerto Rico	518.233.2500	CHEMTREC: 800.424.9300
Alaska, Hawaii	518.233.2500	CHEMTREC: 800.424.9300
Canada	518.233.2500	CHEMTREC: 800.424.9300
Europe	+518.233.2500 (Albanian, Czech, Danish, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Lithuanian, Norwegian, Polish, Portuguese, Romanian, Russian, Serbo-Croatian, Slovak, Spanish, Swedish, Turkish, Ukrainian)	+44.(0)208.762.8322 (UK)
Middle East, All countries, except Israel	+518.233.2500	+961.3.487.287 (Lebanon)
Middle East, Israel	+518.233.2500	+44.(0)208.762.8322 (UK)
Latin America, Asia/Pacific, all other locations worldwide	+518.233.2500	CHEMTREC: +1-703.527.3887 (collect)
At sea	Radio U.S. Coast Guard, which can directly contact Momentive Performance Materials at 518.233.2500 or CHEMTREC at 800.424.9300.	

DO NOT WAIT. Phone if in doubt. You will be referred to a specialist for advice.

CUSTOMER SERVICE CENTERS

North America	E cs-na.silicones@momentive.com		
	• Specialty Fluids	T +1.800.523.5862	F +1.304.746.1654
	• UA, Silanes and Specialty Coatings	T +1.800.334.4674	F +1.304.746.1623
	• RTVs and Elastomers	T +1.800.332.3390	F +1.304.746.1623
	• Consumer Sealants & Construction Sealants and Adhesives	T +1.877.943.7325	F +1.304.746.1654
Latin America	E cs-la.silicones@momentive.com		
	• Argentina & Chile	T +54.11.4862.9544	F +54.11.4862.9544
	• Brazil	T +55.11.4534.9650	F +55.11.4534.9660
	• Mexico & Central America	T +52.55.2169.7670	F +52.55.2169.7699
	• Venezuela, Ecuador, Peru, Colombia & Caribbean	T +58.212.285.2149	F +58.212.285.2149
Europe, Middle East, Africa and India	E cs-eur.silicones@momentive.com	T +00.800.4321.1000 T +40.21.3111848	
Pacific	E cs-ap.silicones@momentive.com		
	• China	T +1.800.820.0202 or T +86.21.3860.4892	F +86.21.5079.3725
	• Japan	T +0120.975.400 or T +81.276.20.6182	F +81.276.31.6259
	• Korea	T +82.2.6201.4600	F +82.2.6201.4601
	• Malaysia	T +60.3.9206.1532	F +60.3.9206.1533
	• Thailand	T +662.207.3456	F +66.2207.3488
Worldwide Hotline		T +1.607.786.8131 T +1.800.295.2392	F +1.607.786.8309

Visit us at Momentive.com



Momentive Performance Materials
22 Corporate Woods Boulevard
Albany, NY 12211

Momentive is a trademark of Momentive Performance Materials Holdings LLC.
Copyright 2009-2011 Momentive Performance Materials Inc. All rights reserved.

MOM-140-021-10E-GL 03/11 Printed in U.S.A.

THE MATERIALS, PRODUCTS AND SERVICES OF MOMENTIVE PERFORMANCE MATERIALS INC., MOMENTIVE PERFORMANCE MATERIALS USA INC., MOMENTIVE PERFORMANCE MATERIALS ASIA PACIFIC PTE. LTD., MOMENTIVE PERFORMANCE MATERIALS WORLDWIDE INC., MOMENTIVE PERFORMANCE MATERIALS GmbH, THEIR SUBSIDIARIES AND AFFILIATES DOING BUSINESS IN LOCAL JURISDICTIONS (collectively "SUPPLIERS"), ARE SOLD BY THE RESPECTIVE LEGAL ENTITY OF THE SUPPLIER SUBJECT TO SUPPLIERS' STANDARD CONDITIONS OF SALE, WHICH ARE INCLUDED IN THE APPLICABLE DISTRIBUTOR OR OTHER SALES AGREEMENT, PRINTED ON THE BACK OF ORDER ACKNOWLEDGMENTS AND INVOICES, AND AVAILABLE UPON REQUEST. ALTHOUGH ANY INFORMATION, RECOMMENDATIONS, OR ADVICE CONTAINED HEREIN IS GIVEN IN GOOD FAITH, SUPPLIERS MAKE NO WARRANTY OR GUARANTEE, EXPRESS OR IMPLIED, (i) THAT THE RESULTS DESCRIBED HEREIN WILL BE OBTAINED UNDER END-USE CONDITIONS, OR (ii) AS TO THE EFFECTIVENESS OR SAFETY OF ANY DESIGN INCORPORATING SUPPLIERS' PRODUCTS, MATERIALS, SERVICES, RECOMMENDATIONS OR ADVICE. AFOREMENTIONED EXCLUSIONS OR LIMITATION OF LIABILITY ARE NOT APPLICABLE TO THE EXTENT THAT THE END-USE CONDITIONS AND/OR INCORPORATION CONDITIONS CORRESPOND TO THE RECOMMENDED CONDITIONS OF USE AND/OR OF INCORPORATION AS DESCRIBED BY SUPPLIER IN ITS PRODUCT DATA SHEET AND/OR PRODUCT SPECIFICATIONS. EXCEPT AS PROVIDED IN SUPPLIERS' STANDARD CONDITIONS OF SALE, SUPPLIERS AND THEIR REPRESENTATIVES SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS RESULTING FROM ANY USE OF ITS MATERIALS, PRODUCTS OR SERVICES DESCRIBED HEREIN.

Each user bears full responsibility for making its own determination as to the suitability of Suppliers' materials, services, recommendations, or advice for its own particular use. Each user must identify and perform all tests and analyses necessary to assure that its finished parts incorporating Suppliers' products, materials, or services will be safe and suitable for use under end-use conditions. Nothing in this or any other document, nor any oral recommendation or advice, shall be deemed to alter, vary, supersede, or waive any provision of Suppliers' Standard Conditions of Sale or this Disclaimer, unless any such modification is specifically agreed to in a writing signed by Suppliers. No statement contained herein concerning a possible or suggested use of any material, product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Suppliers or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service or design in the infringement of any patent or other intellectual property right.