

MAGIX - SOLVENT WHITEBOARD CLEANER

Page: 1

Compilation date: 12/12/2011

Revision date: 19/06/2018

Revision No: 4

#### Section 1: Identification of the substance/mixture and of the company/undertaking

## 1.1. Product identifier

#### Product name: MAGIX - SOLVENT WHITEBOARD CLEANER

1.2. Relevant identified uses of the substance or mixture and uses advised against

## 1.3. Details of the supplier of the safety data sheet

Company name: Eastpoint

Rotterdam Rd Lowestoft NR32 2EX

Tel: +44(0)1502 525555

Email: info@eastpointglobal.com

## 1.4. Emergency telephone number

Emergency tel: +44(0)1502 525555 (office hours only)

## Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

Classification under CLP:	STOT SE 3: H336; Eye Irrit. 2: H319; Flam. Liq. 2: H225
Most important adverse effects:	Highly flammable liquid and vapour. Causes serious eye irritation. May cause
	drowsiness or dizziness.

## 2.2. Label elements

Label elements:

Hazard statements: H225: Highly flammable liquid and vapour.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

Signal words: Danger

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark



**Precautionary statements:** P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P241: Use explosion-proof electrical/ventilating/lighting/.. equipment.

#### MAGIX - SOLVENT WHITEBOARD CLEANER

P280: Wear protective gloves/protective clothing/eye protection/face protection.
P303+361+353: IF ON SKIN (or hair): Take off immediately all contaminated clothing.
Rinse skin with water/shower.
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

#### 2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

**PBT:** This product is not identified as a PBT/vPvB substance.

#### Section 3: Composition/information on ingredients

## 3.2. Mixtures

#### Hazardous ingredients:

#### **ETHANOL**

70-90%

## PROPAN-2-OL

200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319;	10-30%
			STOT SE 3: H336	

#### METHANOL

200-659-6	67-56-1	- Flam. Liq. 2: H225; Acute Tox. 3: H331;		1-10%
		Acute Tox. 3: H311; Acute Tox. 3: H301;		
			STOT SE 1: H370	

## Section 4: First aid measures

## 4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Page: 2

#### MAGIX - SOLVENT WHITEBOARD CLEANER

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

#### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate** / special treatment: Eye bathing equipment should be available on the premises.

#### Section 5: Fire-fighting measures

## 5.1. Extinguishing media

# **Extinguishing media:** Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

#### 5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture.

Vapour may travel considerable distance to source of ignition and flash back.

#### 5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

#### 6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

#### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

## 6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

## Section 7: Handling and storage

#### 7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

Do not handle in a confined space. Avoid the formation or spread of mists in the air.

Smoking is forbidden. Use non-sparking tools.

#### MAGIX - SOLVENT WHITEBOARD CLEANER

## 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from

sources of ignition. Prevent the build up of electrostatic charge in the immediate area.

**Respirable dust** 

Ensure lighting and electrical equipment are not a source of ignition.

#### 7.3. Specific end use(s)

Specific end use(s): No data available.

#### Section 8: Exposure controls/personal protection

8.1. Control parameters

#### Hazardous ingredients:

## ETHANOL

## Workplace exposure limits:

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1920 mg/m3	-	-	-

## **PROPAN-2-OL**

	UK	999 mg/m3 (400ppm)	1250 mg/m3 (500ppm)	-	-	
N	METHANOL					
	UK	266 mg/m3 (200ppm)	333 mg/m3 (250ppm)	-	-	

## **DNEL/PNEC** Values

DNEL / PNEC No data available.

## 8.2. Exposure controls

Engineering measures:	Ensure there is sufficient ventilation of the area. Ensure lighting and electrical
	equipment are not a source of ignition.
Respiratory protection:	Self-contained breathing apparatus must be available in case of emergency.
Hand protection:	Protective gloves.
Eye protection:	Safety glasses. Ensure eye bath is to hand.
Skin protection:	Protective clothing.

## Section 9: Physical and chemical properties

## 9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Alcoholic

Solubility in water: Soluble

Viscosity: Non-viscous

Boiling point/range °C: >35

Relative density: 0.79

#### MAGIX - SOLVENT WHITEBOARD CLEANER

Page: 5

## 9.2. Other information

Other information: No data available.

## Section 10: Stability and reactivity

#### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

## 10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

## 10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

#### 10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

## 10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

#### **10.6. Hazardous decomposition products**

Haz. decomp. products: In combustion emits toxic fumes.

## Section 11: Toxicological information

## 11.1. Information on toxicological effects

## Hazardous ingredients:

## ETHANOL

IVN	RAT	LD50	1440	mg/kg
ORL	MUS	LD50	3450	mg/kg
ORL	RAT	LD50	7060	mg/kg

## PROPAN-2-OL

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg
SCU	MUS	LDLO	6	gm/kg

## METHANOL

IVN RAT	LD50	2131	mg/kg	
---------	------	------	-------	--

## MAGIX - SOLVENT WHITEBOARD CLEANER

#### Page: 6

ORL	MUS	LD50	7300	mg/kg
ORL	RAT	LD50	5628	mg/kg

#### Relevant hazards for substance:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

## Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

#### Section 12: Ecological information

12.1. Toxicity

#### Hazardous ingredients:

#### METHANOL

ALGAE	72H IC50	8000	mg/l
DAPHNIA	48H EC50	24500	mg/l
FISH	96H LC50	10800	mg/l

#### 12.2. Persistence and degradability

## Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

#### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

#### Section 13: Disposal considerations

# MAGIX - SOLVENT WHITEBOARD CLEANER

	Pa	<b>ge:</b> 7		
13.1. Waste treatment methods	3			
Disposal operations:	Transfer to a suitable container and arrange for collection by specialised disposal			
	company.			
NB:	The user's attention is drawn to the possible existence of regional or national			
	regulations regarding disposal.			
Section 14: Transport information	lion			
14.1. UN number				
UN number:	UN1993			
14.2. UN proper shipping name				
Shipping name:	FLAMMABLE LIQUID, N.O.S.			
	(ETHANOL; PROPAN-2-OL)			
14.3. Transport hazard class(es	5)			
Transport class:	3			
14.4. Packing group				
Packing group:	Ι			
14.5. Environmental hazards				
Environmentally hazardous:	No Marine pollutant: No			
14.6. Special precautions for u	ser			
Special precautions:	No special precautions.			
Tunnel code:	D/E			
Transport category:	2			
Section 15: Regulatory information				
15.1. Safety, health and environ	nmental regulations/legislation specific for the substance or mixture			
15.2. Chemical Safety Assessn	nent			
Section 16: Other information				
Other information				
Other information:	This safety data sheet is prepared in accordance with Commission Regulation (EU) No			
	453/2010.			
	* indicates text in the SDS which has changed since the last revision.			
Phrases used in s.2 and s.3:	H225: Highly flammable liquid and vapour.			
	H301: Toxic if swallowed.			
	H311: Toxic in contact with skin.			
	H319: Causes serious eye irritation.			
	H331: Toxic if inhaled.			

## MAGIX - SOLVENT WHITEBOARD CLEANER

H336: May cause drowsiness or dizziness.

H370: Causes damage to organs <or state all organs affected, if known> <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.