

### Pt100 Heavy Duty Sensor Probe, Class B

6mm diameter, available in 50mm or 100mm probe lengths



- Heavy Duty Pt100 Probe to IEC751
- Suitable for general purpose industrial & commercial use
- Class B, 4-wire connection
- Rigid 316 stainless steel sheath, 6.0mm diameter
- Tough silicone rubber insulated lead, 2 metres long
- Sensor temperature rating -50°C to +200°C

#### Specifications

Sensor type: Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire  
Construction: 6.0mm diameter 316 stainless steel sheath.  
Probe temperature range: -50°C to +200°C  
Extension cable: 2 metres flexible silicone rubber insulated, 7/0.2mm  
Termination: 4-wire tails – allows connection to any PT100 instrument 2, 3 or 4 wire

Probe Diameter	Probe Length	Cable Length	Manufacturer's Part Number	Rapid Part Number
6mm	50mm	2 metres	XE-3630-001	61-1212
6mm	100mm	2 metres	XE-3631-001	61-3207