

### 2.1x0.6mm RIGHT ANGLE SURFACE LED **LAMP**

Part Number: KPA-2106SGC

Super Bright Green


#### **Features**


- 2.1mmX0.6mm right angle SMT LED, 1.0mm thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

### Description


The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.


## **Package Dimensions**











- 1. All dimensions are in millimeters (inches).
- 2.Tolerance is ±0.1(0.004") unless otherwise noted.
- 3.The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
  4. The device has a single mounting surface. The device must be mounted according to the specifications





SPEC NO: DSAA3918 APPROVED: WYNEC

**REV NO: V.14B CHECKED: Allen Liu** 

**DATE: FEB/29/2012** DRAWN: D.M.Su

PAGE: 1 OF 5 ERP: 1203000523

### **Selection Guide**

| Part No.    | Dice                     | Lens Type   | lv (mcd) [2]<br>@ 20mA |      | Viewing<br>Angle [1] |
|-------------|--------------------------|-------------|------------------------|------|----------------------|
|             |                          | -           | Min.                   | Тур. | 201/2                |
| KPA-2106SGC | Super Bright Green (GaP) | Water Clear | 5                      | 12   | 120°                 |

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
  2. Luminous intensity/ luminous Flux: +/-15%.
  3. Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

### Electrical / Optical Characteristics at TA=25°C

| Symbol | Parameter                | Device             | Тур. | Max. | Units | Test Conditions |
|--------|--------------------------|--------------------|------|------|-------|-----------------|
| λpeak  | Peak Wavelength          | Super Bright Green | 565  |      | nm    | IF=20mA         |
| λD [1] | Dominant Wavelength      | Super Bright Green | 568  |      | nm    | IF=20mA         |
| Δλ1/2  | Spectral Line Half-width | Super Bright Green | 30   |      | nm    | IF=20mA         |
| С      | Capacitance              | Super Bright Green | 15   |      | pF    | VF=0V;f=1MHz    |
| VF [2] | Forward Voltage          | Super Bright Green | 2.2  | 2.5  | V     | IF=20mA         |
| lR     | Reverse Current          | Super Bright Green |      | 10   | uA    | VR=5V           |


- 1.Wavelength: +/-1nm.
  2.Forward Voltage: +/-0.1V.
  3.Wavelength value is traceable to the CIE127-2007 compliant national standards.

#### Absolute Maximum Ratings at TA=25°C

| Absolute maximum Natings at TA-23 0 |                    |    |  |  |  |
|-------------------------------------|--------------------|----|--|--|--|
| Parameter                           | Super Bright Green |    |  |  |  |
| Power dissipation                   | 62.5               | mW |  |  |  |
| DC Forward Current                  | 25                 | mA |  |  |  |
| Peak Forward Current [1]            | 140                | mA |  |  |  |
| Reverse Voltage                     | 5                  | V  |  |  |  |
| Operating Temperature               | -40°C To +85°C     |    |  |  |  |
| Storage Temperature                 | -40°C To +85°C     |    |  |  |  |


1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAA3918 **REV NO: V.14B DATE: FEB/29/2012** PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: D.M.Su ERP: 1203000523





RELATIVE INTENSITY Vs. WAVELENGTH


Super Bright Green KPA-2106SGC











SPATIAL DISTRIBUTION


SPEC NO: DSAA3918 REV NO: V.14B
APPROVED: WYNEC CHECKED: Allen Liu

DATE: FEB/29/2012 DRAWN: D.M.Su PAGE: 3 OF 5 ERP: 1203000523

#### KPA-2106SGC

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.

  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.


  3.Number of reflow process shall be 2 times or less.

## **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)




## **Tape Dimensions** (Units : mm)

#### **Reel Dimension**




PAGE: 4 OF 5

ERP: 1203000523



SPEC NO: DSAA3918 **REV NO: V.14B DATE: FEB/29/2012** APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: D.M.Su

## **PACKING & LABEL SPECIFICATIONS** KPA-2106SGC USER DIRECTION OF FEED LABEL LABEL 2,000pcs / Reel 1 Reel / Bag OUTSIDE OUTSIDE LABEL LABEL **Kingbright Kingbright** 30K / 55# Box 60K / 56# BOX



SPEC NO: DSAA3918
APPROVED: WYNEC

REV NO: V.14B CHECKED: Allen Liu DATE: FEB/29/2012 DRAWN: D.M.Su PAGE: 5 OF 5 ERP: 1203000523