

TEMPERATURE & PROCESS TECHNOLOGY

Miniature Thermocouple Socket with Stainless Steel mounting bracket


Types K, J, T (IEC Colour Code)




- Miniature size in-line Thermocouple Socket with stainless steel panel mounting bracket
- Contacts are polarized to ensure correct connection
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with IEC specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
K	Green	+Nickel Chromium	-Nickel Alloy	XE-1108-001	61-3011
J	Black	+Iron	-Copper Nickel	XE-1168-001	61-3012
Т	Brown	+Copper	-Copper Nickel	XE-1198-001	61-3013

Schematic Drawing



Recommended aperture size and hole pitch for panel mounting



Drill and counter sink to suit M2.5*10 typical

