

Miniature Thermocouple Socket with Stainless Steel mounting bracket


Types K, J, T
(ANSI Colour Code)




- Miniature size in-line Thermocouple Socket with stainless steel panel mounting bracket
- Contacts are polarized to ensure correct connection
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (ANSI)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
K	Yellow	+Nickel Chromium	-Nickel Alloy	XE-1138-001	61-3061
J	Black	+Iron	-Copper Nickel	XE-9068-001	61-3062
T	Blue	+Copper	-Copper Nickel	XE-1228-001	61-3063

Schematic Drawing



Recommended aperture size and hole pitch for panel mounting



Drill and counter sink to suit M2.5*10 typical