

Features

Unregulated Converters

- High Efficiency up to 84%
- Low Deviation (10% ~ 100% Load)
- 1kVDC and 2kVDC Isolation Option
- Safety Certified
- -40°C to +100°C Operating Temperature Range
- 1W SIP4 Package

Description

The RO/E series is an unregulated DC/DC converter in standard SIP4 package style. This series has been designed to offer exceptionally high efficiency at low loads, an extended operating temperature range and low deviation (10% ~ 100% load). Uses include applications with restricted energy budget and industrial applications where a high efficiency level is required.

Selection Guide

Part Number SMD	Isolation Voltage (kVDC)	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (typ.)	Capacitive Load (max.)
RO-3.305S/E*	1	3.3	5	200	83%	2200µF
RO-0505S/E*	1	5	5	200	84%	2200µF
RO-1205S/E*	1	12	5	200	84%	2200µF
RO-2405S/E*	1	24	5	200	81%	2200µF

* add Suffix "/H" for 2kVDC Isolation Voltage - e.g. RO-3.305S/EH

* add Suffix "/P" for Continuous Short Protection - e.g. RO-3.305S/EHP, RO-3.305S/EP

Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)

Input Voltage Range				±10%
Output Voltage Accuracy				±5% max.
Line Voltage Regulation	low line to high line at full load			1.2% max.
Load Voltage Regulation	Load Deviation 10% to 100%			12% typ.
Output Ripple and Noise (20MHz BW)				50mVp-p typ., 100mVp-p max.
Operating Frequency (V_{in} =nominal input)				20kHz min. / 90kHz max.
Efficiency				see Selection Guide
Minimum Load = 0%	Specifications valid for 10% minimum load only			
Isolation Voltage	RO-xx05S/E	tested for 1 second		1000 VDC
	RO-xx05S/EH	tested for 1 second		2000 VDC
Isolation Capacitance				75pF max.
Isolation Resistance	(Viso=500V)			10GΩ min.
Short-Circuit Protection				1 second
Operating Temperature Range				-40°C to +100°C
Storage Temperature				-55°C to +125°C
Relative Humidity				95% RH
Package Weight				1.4g
MTBF (+25°C)	using MIL-HDBK 217F			3459 x 10 ³ hours
MTBF (+100°C)	using MIL-HDBK 217F			756 x 10 ³ hours

Note: Detailed Information see Application Notes chapter "MTBF"

ECONOLINE

DC/DC-Converter

with 3 year Warranty

RECOM

1 Watt SIP4 Single Output




EN-60950-1 (pending)

UL-60950-1 (pending)

RO/E

Derating-Graph


(Ambient Temperature)





Refer to Application Notes

Typical Characteristics

Tolerance Envelope





RO-xx05S/E





Package Style and Pinning

3rd angle projection



RO/E



Pin #	Pin Connections	Function
1	-Vin	4 Pins
2	+Vin	
3	-Vout	
4	+Vout	

Unit: mm
Tolerance: ± 0.25 mm