

velleman®

LABPS3005N

DC LAB POWER SUPPLY WITH DUAL LED DISPLAY

DC-LABVOEDING - DUBBELE LED-DISPLAY

ALIMENTATION DE LABORATOIRE DC À DOUBLE AFFICHEUR LED

ALIMENTACIÓN DC PARA LABORATORIO CON DOBLE DISPLAY LED

DC-LABORNETZGERÄT MIT LED-DOPPELANZEIGE

ZASILACZ LABORATORYJNY Z PODWÓJNYM WYŚWIETLACZEM LED

ALIMENTAÇÃO DC PARA LABORATÓRIO COM DUPLO VISOR LED



CE



USER MANUAL

1. Introduction

To all residents of the European Union

Important environmental information about this product



This symbol on the device or the package indicates that disposal of the device after its lifecycle could harm the environment. Do not dispose of the unit (or batteries) as unsorted municipal waste; it should be taken to a specialized company for recycling. This device should be returned to your distributor or to a local recycling service. Respect the local environmental rules.

If in doubt, contact your local waste disposal authorities.

Thank you for choosing Velleman! Please read the manual thoroughly before bringing this device into service. If the device was damaged in transit, do not install or use it and contact your dealer.

2. Safety Instructions

	Keep this device away from children and unauthorized users.
	Indoor use only. Keep this device away from rain, moisture, splashing and dripping liquids. Never put objects filled with liquids on top of or close to the device.
	DO NOT disassemble or open the cover under any circumstances. Touching live wires can cause life-threatening electroshocks. There are no user-serviceable parts inside the device. Refer to an authorized dealer for service and/or spare parts. Always connect the device to an earthed power socket.
	Caution: device heats up during use. Make sure the ventilation openings are clear at all times. For sufficient air circulation, leave at least 1" (± 2.5 cm) in front of the openings. Place the device on a flat, heat-resistant surface; do not place the device on carpets, fabrics...
	Always disconnect mains power when device not in use or when servicing or maintenance activities are performed. Handle the power cord by the plug only.
	Keep this device away from dust and extreme temperatures.
	Protect this device from shocks and abuse. Avoid brute force when operating the device.
	Do not use the device when damage to housing or cables is noticed. Do not attempt to service the device yourself but contact an authorised dealer.

3. General Guidelines

Refer to the **Velleman® Service and Quality Warranty** on the last pages of this manual.

- Familiarise yourself with the functions of the device before actually using it.
- All modifications of the device are forbidden for safety reasons. Damage caused by user modifications to the device is not covered by the warranty.
- Only use the device for its intended purpose. Using the device in an unauthorised way will void the warranty.
- Damage caused by disregard of certain guidelines in this manual is not covered by the warranty and the dealer will not accept responsibility for any ensuing defects or problems.
- Keep this manual for future reference.
- The device enjoys optimal protection thanks to the short-circuit protection and the current-limiting point. The power loss in case of short circuit is limited thanks to the protection circuit that controls the power loss of the transistors in the power supply. This feature keeps the device from being damaged. The device will automatically go into the current-limiting mode, which means that the current-limiting point (max. ± 12 A) is installed. Nevertheless, the short circuit should be repaired as

soon as possible in order to prevent wear and unnecessary power consumption.

- The output will be cut off if the short-circuit occurs between the positive and the negative output terminal, which prevents power loss. The device will resume normal operation when the problem has been solved.
- This device is a large power source. The device should be well-ventilated when working at max. power in order to avoid overheating. Keep in mind that the surface of the heat sink is too hot to touch when the device is being used at max. power.
- Improper operation of the device and an excessive ambient temperature may cause certain internal components to fail. When this happens, the actual output voltage may exceed the rated output voltage. Proceed with caution when using this device and avoid unnecessary damage to the load.

4. Features

- dual LED display for voltage and current
- coarse and fine adjustments of voltage and current
- voltage or current-limiting
- output connectors: insulated safety plugs
- low noise temperature controlled fan
- 4 digit display
- setting lock function
- constant voltage / constant current
- 10 mV / 1 mA setting resolution
- protection modes:
 - fuse 3.15 A / 250 V
 - over-current protection
 - over-temperature protection (95 °C)
- fuse-protected

5. Overview

Refer to the illustrations on page 2 of this manual.

1	current indication
2	current adjustment knob
3	power switch
4	output terminal (-)

5	grounding terminal
6	output terminal (+)
7	voltage adjustment knob
8	voltage indication

6. Operation

1. Connect a load (electrical equipment, etc.) to the power supply output, and pay attention to the polarity. Do not reverse the polarity!
2. Plug the AC input power cord into a suitable AC power jack.
3. Place the power switch to the ON position. The power indicator lights and the power has been turned on.
4. Make sure the load current is less than the rated output current of the power supply. 80 % of the rated output current is recommended as the maximum current.

7. Cleaning and Maintenance

- Disconnect the device from the mains prior to maintenance activities.
- The power supply cables must not show any damage. Have a qualified technician maintain the device.
- Wipe the device regularly with a moist, lint-free cloth. Do not use alcohol or solvents.
- There are no user-serviceable parts, apart from the fuse. Contact your dealer for spare parts if necessary.
- Store the device in a dry, well-ventilated, dust-free room.

8. Technical Specifications

input voltage	220 V~ ($\pm 10\%$), 50/60 Hz
output	
voltage	0-30 VDC
current	0-5 A
power	150 W max.
cos Phi.....	0.82
ripple voltage	≤ 1.0 mV (rms)
ripple current	3 mA (rms)
operating temperature.....	0 °C to +40 °C, < 90 % relative humidity
max. hours continuous at full load.....	8 hours
dimensions.....	117 x 190 x 270 mm
weight	4.8 kg
colour.....	grey

Use this device with original accessories only. Velleman nv cannot be held responsible in the event of damage or injury resulting from (incorrect) use of this device. For more info concerning this product and the latest version of this manual, please visit our website www.velleman.eu. The information in this manual is subject to change without prior notice.

© COPYRIGHT NOTICE

The copyright to this manual is owned by Velleman nv. All worldwide rights reserved. No part of this manual may be copied, reproduced, translated or reduced to any electronic medium or otherwise without the prior written consent of the copyright holder.