

Proximity Switches



Order code	Manufacturer code	Description
78-1670	CTI016	SECURITY PROXIMITY SWITCH (RC)

Proximity Switches	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

PRODUCT DATA SHEET

Proximity – Reed Switch – Cylindrical – Metal


CTI 016CA



Drawings not to scale
All dimensions in mm nominal

SPECIFICATION

CONTACT FORM		Normally Open
SWITCHING VOLTAGE	Max. Vac	48
SWITCHING CURRENT	Max. A	0.5
SWITCHING CAPACITY (resistive)	Max. VA	10
CONTACT RESISTANCE	Max. m ohms	200
SWITCHING DISTANCE	Min. mm	12
OPERATING TEMPERATURE	Deg. °C	-10 + 70
STORAGE TEMPERATURE	Deg. °C	-25 + 80
CASE MATERIAL		A.B.S. Plastic



Designed for use in control circuits or security systems.
These switches are strongly constructed and fitted with reed switch contacts.

Rev. No.	Revision Note	Date
A	Web Site 2002	1-2-02



Active Switch & Sensor Limited