

Part Number: PRB 130/30 (Alternate Part No: S1479C)
Proximity Switch - Reed Switch based
Cylindrical - Normally Closed Contacts - Suggested Magnet: PRM

PICTURE



✓RoHS Compliant


APPLICATIONS INCLUDE

- Position and limit sensing
- Linear actuators
- Security system switch
- Door Switch

FEATURES

- Custom cable lengths, strip lengths, cable types, terminations.
- If you do not see what you need, just ask, as there is a strong possibility we can do it !
- Device is intended to be mounted in an enclosure under UL recognition.

DIMENSIONS



Drawings not to scale.
 All dimensions in inches (mm) nominal.

SPECIFICATION

Contact Form / Style	Normally Closed
Switching Capacity (Resistive)	5 W/VA MAX
Switching Voltage	100 VAC MAX
Switching Current	0.5 A MAX
Carry Current	1.0 A MAX
Breakdown Voltage	150 VDC MIN
Contact Resistance	100 mOhms MAX
Switching Distance	3 mm MIN
Operating Temperature Range	-20°C to +85°C
Storage Temperature	-25°C to +90°C
Case Materials	Black Nylon 66
Cable	2 x Round 0.12mm ² PTFE insulated black Other cable sizes available

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: (1) 973 777 6900

www.comus-intl.com

Fax: (1) 973 777 8405

Belgium: + 32 (0)12 390400 - Comus Europe Ltd (Assemtch) UK: +44 (0) 1255 862236 - Germany: +49 (0)911 923 15 943 - Netherlands: +31(0)45 54 39 345 - India: +(91) (44) 43219090

©2015 Copyright Comus International, 454 Allwood Road, Clifton NJ 07012, USA