


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		G2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



- 1 TONGUE MATERIAL THICKNESS = 0.79±0.05 [.031±.002]
- 2 FOR 2.67[.105] TO 3.56[.140] WIRE INSULATION DIA
- 3 MARKING 22-18 FOR MILITARY COMMERCIAL RANGE 22-16
- 4 APPLIES FROM METAL EDGE OF BARREL TO CENTERLINE OF STUD

QTY	DESCRIPTION	MATERIAL & FINISH	PART NO
100	LOOSE PIECE, BOX	BODY: COPPER (ASTM-B152) TIN PL (ASTM-B545)	8-326861-1
1	326861 ON TAPE	SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545)	2-326861-1
1	WIRE TERMINAL	INSULATION: NYLON COLOR: RED	326861

**CUSTOMER SERVICE SYSTEMS**

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS  
 PRODUCT INFORMATION CENTER  
 1-800-522-6752

FOR APPLICATION TOOLING INFORMATION  
 TOOLING ASSISTANCE CENTER  
 1-800-722-1111

FOR ORDER ENTRY  
 1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:  
 105°C [221° F]

VOLTAGE RATING:  
 300V MAX

CIRCULAR MIL AREA:  
 1.04-2.62mm² [2,050-5,180]  
 SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -  
 1 PLC ± -  
 2 PLC ± -  
 3 PLC ± 0.20[.008]  
 4 PLC ± -  
 ANGLES ± .5°

MATERIAL: SEE TABLE  
 FINISH: SEE TABLE

DWN JR RUTH 15JUL09  
 CHK TOM MICHIELUTTI 15JUL09  
 APVD TOM MICHIELUTTI 15JUL09

**STE** TE Connectivity

NAME: WIRE-TERMINAL  
 PIDG-SPADE WIRE SIZE: 22-16

PRODUCT SPEC: -  
 APPLICATION SPEC: -

SIZE: A3 CAGE CODE: 00779 DRAWING NO: C-326861 RESTRICTED TO: -

WEIGHT: -

CUSTOMER DRAWING SCALE: 5:1 SHEET: 1 OF 1 REV: G2