

4

3


2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	02	P	LTR	DESCRIPTION	DATE	DWN	APVD
		J3		REVISED PER ECO-11-004820	11MAR11	RK	HMR

AMP WIRE RANGE	AMP INSULATION RANGE
22-16 AWG 0.3-1.5 mm ²	.140 MAX DIA 3.5 MAX DIA



△1 ASTERISK * FOR PHOS BRONZE VERSION ONLY
 △2 OBSOLETE W/O REPLACEMENT



△2	OBSOLETE	TIN-LEAD	PHOS BRONZE	165566-7	
△2	OBSOLETE	GOLD	PHOS BRONZE	165566-6	
△2	OBSOLETE	GOLD	BRASS	165566-5	
		SILVER	PHOS BRONZE	165566-4	
△2	OBSOLETE	SILVER	BRASS	165566-3	
		TIN	PHOS BRONZE	165566-2	
		TIN	BRASS	165566-1	
		PN ON TAPE	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	jr_ruth	15APR05	STE TE Connectivity		
CHK	T MICHIELUTTI	15APR05			
APVD	T MICHIELUTTI	15APR05			
PRODUCT SPEC	NAME				
APPLICATION SPEC	RECEPTACLE, FASTON, PIDG, .110 SERIES		RESTRICTED TO		
WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	
CUSTOMER DRAWING		A3	00779	C-165566	
SCALE		1:1	SHEET		1 OF 1
REV		J3			

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	± -
1 PLC	± 0.2
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± 5°
MATERIAL	FINISH
-	-